

imageCLASS MF269dw/MF267dw/MF264dw

Black and White | Compact | Multifunction

Print up to 30 ppm

Print up to 8-1/2" x 14"

250-sheet maximum paper capacity

Standard one-year warranty

Designed for small and home offices, the imageCLASS MF269dw/MF267dw/MF264dw models balance speedy performance and minimal maintenance, and the LCD panel delivers an intuitive user experience.



USABILITY

- Six-line touch LCD for easy navigation (MF269dw/MF267dw only).
- Create Wi-Fi® Direct hotspot from the printer to establish direct connection to mobile device(s) without the need for an external router.



QUALITY AND RELIABILITY

- Canon's signature reliability and engine technologies help keep productivity high and help minimize the impact on support resources.
- Canon GENUINE supplies help ensure enhanced quality, performance, and life cycle of your Canon equipment.



WORKFLOW EFFICIENCY

- Supports mobile solutions³ for printing and scanning.
- Scan and convert documents to searchable digital files.
- Designed for smaller print jobs with first-print time as fast as 5.1 seconds.



SUSTAINABILITY

- A combination of fusing technologies and low-melting-point toner minimizes power requirements and helps achieve low-energy consumption.
- Encourage environmentally conscious work practices by enabling multiple settings that can help save paper and energy.
- ENERGY STAR® certified and currently rated EPEAT® Silver.¹



COST EFFICIENCY

- Out-of-the-box, standard two-sided printing plus the ability to print multiple pages onto one page helps to reduce paper consumption.
- Available high-capacity cartridge helps reduce overall supply costs.



SECURITY FEATURES

- Helps mitigate risk of confidential information loss, as documents are only stored in short-term memory.
- Security settings can be set behind an administrator log-in.



MOBILE-FRIENDLY DEVICE ACCESS

From application-based to cloud-based to device native, the imageCLASS MF269dw/MF267dw/MF264dw models offer a variety of methods for printing from a mobile phone or tablet across iOS and Android devices. The Canon PRINT Business application, which supports both platforms, offers access to additional device settings as well as the ability to scan from the printer to a mobile phone or tablet.



EFFICIENT DOCUMENT SCANNING

The imageCLASS MF269dw/MF267dw/MF264dw leverage a document feeder for scanning, as well as the ability to convert files into multiple formats, including Hi-compression PDF and Searchable PDF (OCR). All three models offer the ability to do color scanning while the MF269dw offers two-sided scanning through the feeder.



100% U.S.-BASED SERVICE AND SUPPORT

From cutting-edge technology to industry-leading response times, Canon U.S.A. takes pride in delivering complete customer satisfaction. Canon's award-winning, 100% U.S.-based, friendly, and knowledgeable Customer Service team provides expert assistance for every level of experience, giving you the support, peace of mind, and value your business deserves.



GENUINE® CONSUMABLES

Always look for the Canon anti-counterfeiting hologram on your Canon GENUINE product packaging.

Use of Canon GENUINE toner cartridges helps provide longer equipment life, high yields, reliable performance, high-quality output, and minimal jamming or issues.

SPECIFICATIONS

FEATURES	imageCLASS MF269dw	imageCLASS MF267dw	imageCLASS MF264dw
MAIN UNIT			
Functions	Print/Scan/Copy/Fax		Print/Scan/Copy
Control Panel	6-line LCD		5-line LCD
Memory	256 MB		
Standard Interface Connection	USB Device 2.0 High-Speed, 10/100 Base-T Ethernet (Network), Wi-Fi 802.11 b/g/n, Wi-Fi Direct Connection		
Paper Input/Output Capacity (Letter, 20 lb. Bond)	250/50 Sheets		
Paper Sources (Letter, 20 lb. Bond)	250-sheet Paper Cassette, 1-sheet Stack Bypass		
Supported Media Types	Cassette/Bypass: Plain, Recycled, Thick, Bond, Label, Envelope		
Supported Media Sizes	Cassette/Bypass: Letter, Legal, Statement, Executive; Envelope: COM10, Monarch, C5, DL; Custom (Min. 3" x 5" to Max. 8.5" x 14")		
Supported Media Weights	Cassette/Bypass: 16 lb. Bond to 43 lb. Bond (60 to 163 g/m²)		
Warm-up Time	From Power On: 15 Seconds or Less; From Sleep Mode: 1.6 Seconds or Less		
Dimensions (W x D x H)	15.4" x 16.0" x 14.8" (390 mm x 405 mm x 375 mm)		
Weight (Machine Only/Boxed Weight)	29.3 lb. (13.3 kg)/37.4 lb. (17.0 kg)	27.3 lb. (12.4 kg)/35.2 lb. (16.0 kg)	
PRINT SPECIFICATIONS			
Printing Method	Laser Beam Printing		
Print Speeds ²	Up to 30 ppm (Letter); Up to 24 ppm (Legal)		
First-Print-Out Time	Approx. 5.1 Seconds		
Recommended Monthly Page Volume	250 - 2,500 Pages		
Print Resolution (dpi)	600 x 600		
Standard Page Description Languages	UFR II-LT, PCL [®] 6, PCL [®] 5e		
Two-Sided Printing	Automatic (Standard)		
Printing from Mobile and Cloud-based Services ³	Canon PRINT Business, Apple [®] AirPrint [®] , Mopria [™] Print Service, Google Cloud Print [™] ⁴		
Operating Systems (Print/Scan)	Windows [®] 10/8.1/7, Windows Server [®] 2016/2012 R2/2012/2008 R2/2008; Mac OS 10.8.5 and Up. Drivers Available For Download From www.usa.canon.com/support		
COPY SPECIFICATIONS			
Copy Speed	Up to 30 ppm (Letter); Up to 24 ppm (Legal)		
First-Copy-Out Time (Letter)	8 Seconds or Less		
Copy Resolution (dpi)	Up to 600 x 600		
Copy Size	Platen: Up to Letter; ADF: Up to Legal		
Presets	Magnifications: 25% - 400% (1% Increments)/Reductions: 25%, 50%, 64%, 78%/Enlargements: 129%, 200%, 400%		
SCAN SPECIFICATIONS			
Type	Duplexing Automatic Document Feeder	Automatic Document Feeder	
Document Feeder Paper Capacity (20 lb. Bond)	50 Sheets	35 Sheets	
Document Feeder Supported Media Sizes	Legal, Letter		
Document Feeder Supported Media Weights	Single-sided Scanning: 13 - 28 lb. Bond (50-105 g/m²) Two-sided Scanning: 16 - 28 lb. Bond (60-105 g/m²)	Single-sided Scanning: 13 - 28 lb. Bond (50-105 g/m²)	
Scan Resolution (dpi)	600 x 600		
Scan-to-Mobile Devices	Canon PRINT Business		
Scan Speed (Letter) (ipm)	Single-sided (Color/BW): 7.7/11.6 Two-sided (Color/BW): 2.4/4	Single-sided (Color/BW): 8 /10.6 Two-sided (Color/BW): N/A	
SEND SPECIFICATIONS			
Destination	Email (SMTP), SMB, Super G3 FAX		NA
Address Book	Local (50)		
Send Resolution (dpi)	300 x 300		
Communication Protocol	File: SMB; Email: SMTP, POP3		
File Format	TIFF, JPEG, PDF (Compact, Searchable)		
FAX SPECIFICATIONS			
Modem Speed	Super G3: 33.6 Kbps; G3: 14.4 Kbps		NA
Resolution (dpi)	200 x 400, 200 x 200, 200 x 100		
Sending/Recording Size	Statement to Letter		
Fax Memory	Up to 256 Pages		
Speed Dials	Max. 104		
Group Dials/Destinations	Max. 50 Dials		
Sequential Broadcast	Max. 114 Addresses		
Fax Features	Rx Mode, Resolution, Two-sided Original, Density, Sharpness, Duplex Fax		
SECURITY SPECIFICATIONS			
Network	IP/MAC Address Filtering, TLS Encrypted Communication, SNMP V3.0, IEEE 802.1X, IPv6, SMTP Authentication, POP Authentication Before SMTP		
Wi-Fi [®] Authentication Methods	WEP 64/128 bit, WPA-PSK (TKIP/AES), WPA2-PSK (AES)		
ENVIRONMENTAL SPECIFICATIONS			
Operating Environment	Temperature: 50 to 86° F; Humidity: 20 to 80% RH (no condensation)		
Power Consumption	Maximum: Approx. 1080 W or Less; Average: Approx. 340 W; Sleep Mode: Approx. 0.7 W; Typical Electricity Consumption (TEC) Rating: 0.9 kWh		
Standards	ENERGY STAR [®] Qualified, Rated EPEAT Silver ¹		

CONFIGURATION AND ACCESSORIES



Extended Service Plans Available For Purchase

If service is required, you may receive a replacement model⁶ via advanced exchange. In this case, you'll be instructed to return the damaged unit to Canon in the replacement packaging, which also includes a prepaid shipping label. Or you may choose to carry your existing equipment to a local Authorized service facility for repair.

Canon eCarePAK (Exchange/Carry-In)

Canon extended service plans extend standard, one-year warranty⁵ support to cover an additional one to four years.

One-Year: 5707B042

Two-Year: 5707B043

Three-Year: 5707B044

Four-Year: 5707B045

Item Codes

imageCLASS MF269dw: 2925C006

imageCLASS MF267dw: 2925C010

imageCLASS MF264dw: 2925C020

Cartridge 051: 2168C001 (Yields 1,700 Pages)

Cartridge 051 H: 2169C001 (Yields 4,100 Pages)

Drum Cartridge 051: 2170C001 (Yields up to 23,000 Pages)

Standard Toner Cartridge 051 yielding 1,700 pages included with purchase.

¹ For current EPEAT ratings (Gold/Silver/Bronze), please visit epeat.net.

² Print speed is based on internal testing. Print speed may vary, depending on the number of copies selected as well as the settings for size, type, and orientation of paper.

³ Canon PRINT Business is a free app available on the App Store[®] and Google Play[™] Store. For more information, including compatibility, please visit usa.canon.com/mobile-app. Please see the respective websites for Apple AirPrint and Mopria Print Service for compatibility and additional information.

⁴ Subscription to a third-party cloud service required. Subject to third-party cloud service providers' terms and conditions.

⁵ Warranty program is subject to certain conditions and restrictions. See warranty card for details.

⁶ Replacement model may be new or refurbished quality.

USA.CANON.COM



As an ENERGY STAR partner, Canon U.S.A., Inc. has qualified these models as meeting the ENERGY STAR energy efficiency criteria through an EPA recognized certification body. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. Canon, imageCLASS, and the GENUINE logo are registered trademarks of Canon Inc. in the United States and may also be registered trademarks or trademarks in other countries. Canon products offer certain security features, yet many variables can impact the security of your devices and data. Canon does not warrant that use of these features will prevent security issues. Nothing herein should be construed as legal or regulatory advice concerning applicable laws; customers must have their own qualified counsel determine the feasibility of a solution as it relates to regulatory and statutory compliance. All other referenced product names and marks are trademarks of their respective owners. Specifications and availability subject to change without notice. Not responsible for typographical errors.

©2018 Canon U.S.A., Inc. All rights reserved.

0213W954

0818-iCMF269/267/264-PDF-IH

