



## IK-KV-13.3W

### 13.3-INCH IKEYVISION FLAT PANEL TOUCH SCREEN DISPLAY

The IK-KV-13.3W is a 13-inch iKeyVision monitor that provides you with a wide view display and a two-point capacitive touch screen. Formed from molded aluminum it is built to hold up in any environment and boasts a 1000-nit display. In addition, the IK-KV-13.3 has a standard VESA pattern for mounting in a vehicle. Features: Two-Point Capacitive Touch Screen 4 USB 2.0 ports Anti-glare coating

### Product Code IK-KV-13.3W

I/O	Line In, HDMI, VGA, Display port, Power, USB type B, 4 USB 2.0 ports
Power	12-16 volt DC
Compatability	Windows
Mounting Compatability	VESA 75; M6 bolts
Temperature Range	OPERATING: -30C to +80C (-22F to 176F)
Resolution	1280 x 800
Aspect Ratio	16:9
Brightness Control	8 to 1000 nits
OSD Buttons	Emergency, Windows, Blackout, Menu, Exit, Brightness +/-, Volume +/-, Power
Warranty	1 Year Limited Warranty
Dimensions	12.75" x 9.4" x 1.6" (w-h-d) 323.85 mm x 238.76 mm x 40.64 mm