



Galil 6-CO

6.5Inch, 2Way OpenBack Ceiling Speakers

| Speakers



The Galil 6CO is a pair of twoway openback 8 speakers designed for mounting in the ceiling. The speakers feature a multitap power transformer for selecting direct 8 (bypassing the transformer) or 70V/100V power settings suitable for array installation

FEATURES

- Type - 2way coaxial round openback ceiling speaker with infinite baffle design
- Woofer - 6.5" polypropylene cone with rubber surround
- Tweeter - 0.5" Mylar
- Frequency Response - 60Hz to 20kHz
- Impedance - 8
- Sensitivity - (SPL) 87dB (1W @1m with 1kHz)
- Recommended Power - RMS 30W, 80W max
- Grill - White baffle aluminum grills
- Package - 2 speakers (1 pair), template and user manual
- Mounting Bracket (Optional) - SKIC6



KRAMER

TECHNICAL SPECIFICATIONS

DESCRIPTION:	2way openback ceiling speakers
HIGH FREQUENCY DRIVER:	0.5" Mylar dome tweeter
LOW FREQUENCY DRIVER:	6.5" polypropylene cone with rubber surround woofer
IMPEDANCE:	8
DISPERSION COVERAGE:	120° @2kHz
CROSSOVER FREQUENCY:	3kHz
NOMINAL SENSITIVITY:	87dB SPL @1m, 1W
COVERAGE ANGLE:	104°
DIRECTIVITY FACTOR (Q):	8.5 (averaged 100Hz to 10kHz)
DIRECTIVITY INDEX (DI):	9.2dB (averaged 100Hz to 10kHz)
FREQUENCY RESPONSE:	60Hz to 20kHz
INPUT POWER:	30W RMS, 80W continuous program
TRANSFORMER:	70V – 3.7W/7.5W/15W/30W; 100V – 7.5W/15W/30W
RECOMMENDED AMPLIFIER POWER:	30W
INPUT CONNECTOR:	Springtype push terminal block
WEIGHT PER SINGLE SPEAKER:	1.55kg (3.41lbs) approx
SHIPPING WEIGHT (FOR PAIR):	4.05kg (8.91lbs) approx
DIMENSIONS (OD):	23cm (9.06")
CUTOUT SIZE (MOUNT DIMENSION):	19.5cm (7.68")
MOUNT DEPTH:	7.5cm (2.95")
OPTIONAL:	SKIC6 installation bracket