

4 Port Dual Monitor DVI KVM Switch - Dual Screen Display Compact USB KVM Switch with Integrated USB 3.0 Hub & Audio - Dual View KVM - Dell HP Apple Lenovo - TAA Compliant

**Product ID:** SV431DD2DU3A



The TAA compliant Dual-Monitor DVI KVM Switch controls four multimedia computer systems from one dual-DVI monitor workstation.

The KVM switch supports four separate multimedia computer systems and the use of a dual DVI-D single-link monitor workstation, increasing productivity by enabling you to access more information at once.

The 2-port hub that's built into the USB 3.0 KVM switch shares two additional peripherals (in addition to keyboard and mouse) among attached computers as if they were directly connected while supporting high-performance peripherals such as flash drives and video capture devices.

With support for separate stereo audio and microphones, the KVM switch box connects everything you need directly to your systems, saving you money and desk space.

The front-panel push-buttons make it easy to switch between systems and activate the auto-scan feature. The hotkey functionality makes accessing each system quickly, while an optional buzzer sound confirms the switch.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice, and monitors. This 4-port DVI USB KVM switch is backed by a 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Small office
- Back office

- Medical office
- Repair shop

## Features

- **IMPROVE EFFICIENCY:** 4 Port Dual Monitor DVI KVM Switch with hotkey and manual switching, to access 4 workstations or servers with USB and DVI video from a single keyboard, monitor, and mouse
- **WORK SMARTER:** Combines dual DVI displays and a high-speed 2-Port USB 3.0 hub to share USB devices between connected computers seamlessly; OS independent and works with video cards from NVIDIA and AMD
- **TECH SPECS:** 4 Port KVM Dual Screen DVI Single Link 2048x1536 Analog 1920x1200 Digital 2-Port USB 3.0 Hub Hotkey, Push Button OS Independent Audio Dual DVI + USB Console TAA
- **USER-FRIENDLY:** Dual view KVM switch with compact & durable housing features easily accessible large push buttons on the front panel in addition to hotkey support; also provides audio and mic switching
- **THE STARTECH.COM ADVANTAGE:** This KVM is TAA compliant, and StarTech.com offers a 2-year warranty and free lifetime 24/5 multilingual technical support based in North America

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB 3.0
PC Video Type	DVI
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

---

### Performance

On-Screen Display	No
DVI Support	Yes - Single Link
IP Control	No



Hot-Key Selection	Yes
Maximum Data Transfer Rate	5 Gbps
Maximum Analog Resolutions	2048 x 1536 @ 85Hz
Maximum Digital Resolutions	1920 x 1200 @ 60Hz
Supported Resolutions	Minimum 640 x 480
Wide Screen Supported	Yes
Auto Scan	10, 20, 30, 40, 50, and 60 seconds
Port Selection Support	Push Button and Hotkeys

---

#### Connector(s)

Console Interface(s)	DVI-I (29 pin)
	USB Type-A (4 pin; HID Port) USB 1.1
	USB 3.1 USB Type-A (9 pin, Gen 1, 5 Gbps)
	3.5 mm Mini-Jack (3 Position)
	3.5 mm Mini-Jack (3 Position)
Host Connectors	DVI-I (29 pin)
	3.5 mm Mini-Jack (3 Position)
	3.5 mm Mini-Jack (3 Position)
	USB 3.1 USB Type-B (9 pin, Gen 1, 5 Gbps)

---

#### Indicators

LED Indicators	Red
	Green

---

#### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A



Output Voltage	9V DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	18 W

---

#### Environmental

Operating Temperature	0~40 degree C
Storage Temperature	-20~60 degree C
Humidity	0~90% RH, Non-condensing

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	0.0 in [0.0 mm]
Product Width	10.0 in [25.3 cm]
Product Height	2.6 in [66.0 mm]
Product Depth	3.9 in [100 mm]
Weight of Product	2.9 lb [1.3 kg]

---


#### Packaging Information

Package Length	10.6 in [26.8 cm]
Package Width	6.3 in [16.0 cm]
Package Height	7.5 in [19.2 cm]
Shipping (Package) Weight	10.6 oz [300.0 g]

---

#### What's in the Box

Included in Package	KVM switch
---------------------	------------



universal power adapter (NA/JP, EU, UK, ANZ)

quick-start guide

---

***\*Product appearance and specifications are subject to change without notice.***

