



# Danby 20" Free Standing Gas Range

## DR202WGLP



### SPECIFICATIONS

GENERAL			
<b>Brand</b>	Danby	<b>Color</b>	White
<b>Fuel</b>	Natural Gas	<b>ADA Compliant</b>	Yes
<b>Country of Sale</b>	USA	<b>UPC</b>	067638015219
COOKTOP			
<b>Surface Finish</b>	Porcelain Enamel	<b>Lift-up cooktop</b>	No
<b>Backsplash</b>	Yes	<b>Backsplash Color</b>	White
<b>Backsplash Height</b>	5.24"	<b>Cooktop Color</b>	White
<b>Burner Type</b>	Sealed	<b>Burner Type/Power</b>	Vision (new design)-Sealed
<b>Left Front</b>	9,500 / (9,500)	<b>Right Front</b>	12,000 / (12000)
<b>Left Rear</b>	9,500 / (9,500)	<b>Right Rear</b>	5,000 / (5,000)
<b>Ignition System</b>	Electronic Spark	<b>Grates</b>	2 pc Black Porcelain Wire
<b>Oven Vent Cover</b>	Hidden	<b>Hot surface indicator</b>	No
<b>Valve / Control</b>	140 deg		
MANIFOLD			
<b>Knob Type Brand</b>	5 (Indicator Silver 40)	<b>Knob Color</b>	White
<b>Front Panel Color</b>	White	<b>Oven Control Method</b>	Thermostat
<b>Oven Light Switch</b>	No	<b>Oven "On" Indicator Lamp</b>	No
<b>Surface Unit ON Lamp</b>	No		
OVEN			
<b>Overall Oven Volume</b>	2.3	<b>Bake Power</b>	
<b>In-Oven Broil</b>	2.3	<b>Broil Power</b>	N/A
<b>Cleaning</b>	Standard	<b>Oven Cooking Method</b>	Thermal
<b>Ignition System</b>	Electronic/Glow Bar	<b>Oven Interior Color</b>	Pirolytic blue
<b>Oven Light Activation</b>	No	<b>Racks</b>	2 Nickel
<b>Rack Positions</b>	4	<b>Bodyside Color</b>	White
DOOR / DRAWER			
<b>Door Construction</b>	Metal (blind door)	<b>Window</b>	No
<b>Door Color</b>	White	<b>Handle Style</b>	New design
<b>Handle Color</b>	White	<b>Drawer</b>	Broil Drawer (Drop down door)
<b>Drawer Color</b>	White	<b>Drawer Handle (if Drawer)</b>	Front pocket (White)
WEIGHTS & DIMENSIONS			
<b>Dimensions (WxDxH)</b>	20" x 23.7" x 41.75"	<b>Package Dimensions (WxDxH)</b>	22.34" x 29.05" x 42.65"
<b>Installation Cutout (WxDxH)</b>	20 x 25 x 36	<b>Product Weight Net/Box</b>	48.4kg / 54.75kg
<b>Adjustable Height to Cookup (in)</b>	36"	<b>Voltage Rating</b>	120V
MISC			
<b>Grid and Broil Pan</b>	Yes	<b>Anti-tip Bracket</b>	Yes
<b>Broil Drawer Rack</b>	Yes	<b>LP Kit Supplied</b>	Yes
<b>Warning Languages</b>	English / Spanish	<b>Leveling Feet</b>	4
<b>Agency Listing</b>	CSA	<b>Warranty</b>	12 months

### FEATURES

- Compact solution for small space living: 20" free standing gas range with a large 2.3 cu. ft. oven capacity
- Manual, easy to clean pyrolytic blue oven
- ADA Compliant: meets requirements set out by Standards for Accessible Design for people with disabilities
- New Sealed burners: (12,000/9,500/5,000/9,500 BTU)
- Powerful 13,000 BTU for maximum baking power
- In drawer broiler drawer: drop down door and front pocket
- Flexibility: two oven racks with four adjustable positions and safety stops for optimal cooking

Danby Products Limited. PO Box 1778, Guelph, Ontario Canada N1H 6Z9 (519) 837-0920 FAX: (519) 837-0449

Danby Products Inc., PO Box 669, Findlay, OH USA, 45840 (419) 425-8627 FAX: (419) 425-8629

Continuing research results in steady improvement. Therefore, this information and these specifications are subject to change without notice.