



VZ-191RCR ADVANTAGES

- 19" LED Display Rack Mount (8U) CCTV Monitor
- 2 AV (CVBS) Input / 1 AV(CBVS) Output (Loop-through), HDMI, VGA
- 16:9 / 4:3 Available, 3D Comb-filter, De-interlace, Built-in Speakers
- Auto Source & Power Recovery
- Built to run 24/7/365
- 3-Year Warranty

DIMENSIONS



INTERFACE



- | | |
|----------------|-----------------|
| 1. DC 12V IN | 5. AV(CVBS) OUT |
| 2. HDMI IN | 6. AUDIO IN/OUT |
| 3. VGA IN | |
| 4. AV(CVBS) IN | |

Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.



MODEL # VZ-191RCR	
VIDEO	
Screen Size	19"
Max. Resolution	1280 x 1024 @60Hz
Pixel Pitch	0.294 mm x 0.294 mm
Brightness	380 cd/m²(Typical)
Contrast Ratio	1000:1
Aspect Ratio	5:4
Viewing Angle (H/V)	170° / 160°
Display Color	16.2 Million
Response Time	< 10ms
Video System	NTSC / PAL
INTERFACE	
AV (CVBS) In / Out	2 / 1
HDMI In	1
RGB In (15Pin D-Sub)	1
AUDIO In / Out	1 / 1
AUDIO	
Built in speaker	2W X 2
SPECIAL FEATURES	
Filter Type	3D Comb-filter / De-Interlace
Multi-lingual Language	English, Spanish, French, German, Italian
DIMENSIONS & WEIGHT	
Outline Dimension (W x H x D)	18.97" x 13.89" x 3.26" 482.0 mm x 353.0 mm x 83.0 mm
Net Weight / Gross Weight	12.55 lb (5.69 kg) / 15.6 lb (7.07 kg)
MOUNT	
Form Factor	8U Rack Mounting
Mount Type	Tilt-able Rack Mount
VESA	100mm x 100mm (M4 x L8 screws)
GENERAL	
Power	Electrical Ratings
	Consumption (Typ/Max)
Warranty	Parts/ Labor
Operating Temperature	