

plantronics®



## Savi 8200 Series

Simply better  
conversations.

Wireless DECT audio headset system.

Enterprise-grade audio

# Savi 8200 Series

Connect in confidence by managing PC, mobile and desk phone calls with ease. The Savi 8200 Series wireless headset system also gives you long-range roaming while enjoying the outstanding quality of enterprise-quality DECT audio.

## KEY FEATURES



### SAVI 8220

- A** Noise-canceling microphone
- B** Flexible microphone boom
- C** Manage your PC, mobile and desk phone calls
- D** Ringer conveniently located in the base
- E** Charging cradle



### SAVI 8210

For more information about the Savi 8200 Series or other products, please visit [plantronics.com](http://plantronics.com).

## PLANTRONICS CUSTOMER CARE

Backed by Plantronics industry-leading global service and support. [plantronics.com/contactsupport](http://plantronics.com/contactsupport).



## TOP FEATURES

- Ideal for enterprise and contact center professionals who use multiple devices and require premium sound quality for their business communications
- Enjoy an enterprise-quality audio experience by listening to music and media in premium hi-fi DECT stereo (W8220)
- Active noise canceling (ANC) tunes out background noise, ensuring great audio quality and fewer interruptions (W8220)
- DECT Security certified; uses the latest standards in DECT wireless security
- Adaptive power system allows you to automatically downshift to low power when the headset is close to the base to save battery life and maximize density
- Conference two of your three devices together — PC to desk phone or mobile to PC
- Ringer in the base with volume controls (off, low, medium, high)
- Limit the transmission of nearby conversations with the close conversation limiting feature (configurable in Plantronics Hub)
- Plantronics Manager Pro, software-as-a-service that is sold separately, enables your IT team to gain insight into every Plantronics headset being used company-wide

## SPECIFICATIONS

Talk/standby time	Up to 13 hours talk, up to 50 hours standby time
Headset wireless range	Up to 590 ft/180 m (line of sight); 180 ft/55 m (typical office environment)
Battery capacity	Mono 490 mAh; Stereo 700 mAh
Battery type	Rechargeable, replaceable, lithium ion polymer
Charge time	3 hours
Wireless technology	DECT 6.0 and Bluetooth v4.2
Audio profiles	Advanced Audio Distribution Profile (A2DP); AVRCP; Bluetooth Hands-Free Profile (HFP); Bluetooth Headset Profile (HSP)
Codecs	G726, G722, Broadvoice32, OPUS/CELT 16kS, OPUS/CELT 48kS
Receive audio performance	ANC (W8220)
Receive frequency response	Fullband stereo media audio 20 Hz-20 kHz; Wideband stereo telephony 100 Hz-6.8 kHz
Hearing protection	SoundGuard DIGITAL: protects against sound levels above 118dBA; G616 anti-startle (during calls) detects and eliminates any large sudden increase in signal level; Time-weighted average prevents average daily noise exposure from exceeding 85dBA. (Note, Plantronics Hub software required to enable SoundGuard DIGITAL features).
Microphone technology	Noise canceling
Microphone frequency response	Wideband: 100 Hz–6.8 kHz
Headset weight	Mono: .25 lbs/115 g; Stereo: .35 lbs/160 g
Call controls	Call answer/end, mute, volume +/-, ANC on/off, power on/off

## Models

**W8210-M** and **W8220-M**: Certified for Skype for Business.  
**W8210** and **W8220**: Built for UC applications and soft phones from Avaya, Cisco, Skype and others. See software compatibility guide at [plantronics.com/us/support/supported-softphones](http://plantronics.com/us/support/supported-softphones).