



WYSE 3040 THIN CLIENT

Quad-core performance on a budget

Equipped with twice the number of CPU cores, the Wyse 3040 is capable of supporting light multitasking and basic productivity. This cost-effective endpoint features hardened, optimized Wyse ThinLinux as well as virus-resistant Wyse ThinOS.

Remarkably compact, the Wyse 3040 is Dell's smallest and lightest thin client* and comes with flexible mounting options for space constrained environments. It is also the most power efficient thin client, within its class. It consumes less than 4 watts of energy and is adept at offering many years of efficient, secure and highperformance service.

Flexible connectivity

The Wyse 3040 can connect to a variety of virtual desktop brokers including Citrix XenDesktop and XenApp, VMware Horizon, and Microsoft RDS right out of the box. It offers great multimedia capabilities, and essential protocol and peripheral support including optional PCoIP that enables connection to Amazon WorkSpaces (AWS). The Wyse 3040 includes a range of connectivity options including two DisplayPort interfaces, four USB ports, one of which is USB 3.1, as well as wired and wireless network connections.

Easy to manage, highly scalable

The Wyse 3040 thin client is highly manageable through Wyse Device Manager (WDM) and Wyse Management Suite. Administration easily scales from just a few to tens of thousands of thin clients.

With Wyse thin clients, customers get a complete services portfolio including Deployment Services, ProSupport¹ and Accidental Damage Service², and end-to-end support throughout the product lifecycle.

* Based on Dell internal analysis, March 2017.

WYSE 3040 THIN CLIENT SPECIFICATIONS

OPERATING SYSTEM	Wyse ThinOS, Wyse ThinOS with PCoIP Wyse ThinLinux		
CPU	Intel® Atom x5-Z8350 (Quad Core 1.44 GHz)		
GRAPHICS	Built-in Graphics controller. Three independent frame buffers. DirectX 11.1 compatible, OpenGL 4.3, OpenCL 1.2, OpenGL ES 3.0		
MEMORY ³	2GB DDR3L 1600MHz, soldered down		
STORAGE ⁴	ThinOS: 8GB eMMC FLASH, soldered down ThinLinux:16GB eMMC FLASH, soldered down		
I/O PERIPHERAL SUPPORT	3 x USB 2.0 (1 front/ 2 rear) 1 x USB 3.1 Gen 1 (front) 1 x Audio-mic combo jack 2 x DisplayPort™ 1.2 1 x 1Gb/s RJ45		
SECURITY	Built-in chassis security lock slot (cable sold separately)		
NETWORKING	Integrated Realtek® Ethernet LAN 10Mb/100Mb/1Gb Copper RJ45, Optional Azurewave AW-CM389MA Dual band 802.11 a/b/g/n/ac wireless with Bluetooth 4.0, internal antennas ⁶		
MULTIMEDIA	3.5 mm Audio-mic combo jack		
DISPLAY	Up to two WQXGA (2560x1600) resolution digital displays @ 60Hz		
POWER	External 15 Watt AC Adapter with local Type Duck Head Power Cord. Worldwide auto-sensing 100-240 VAC, 50-60 Hz Power consumption: 3.3 watts (idle)		
DIMENSIONS	Height 101.6 mm x Width 27.94 mm x Depth 101.6 mm		
NET WEIGHT	0.24 kg (0.53 lbs.)		
SHIPPING WEIGHT	1.47kg/ 3.24 lbs. (Americas and APJ) 0.80 kg/ 1.76 lbs. (EMEA)		
TEMPERATURE RANGE	Operating: 22^{9} to 104^{9} E (10% to 40^{9} C)		
HUMIDITY	20% to 80% condensing. 10% to 95% non-condensing		
WARRANTY	Three-year Limited Hardware Warranty⁵		
SUPPORT AND DEPLOYMENT	Complete services portfolio including Deployment Services, Optional Dell ProSupport for premium support from expert technicians and 24x7 availability ¹ and Accidental Damage Service ² .		
ENVIRONMENTAL, ERGONOMIC, & REGULATORY STANDARDS	Environmental Standards (eco-labels): ENERGY STAR 6.1 qualified, EPEAT Registered ⁷ , WEEE, EU RoHS ⁸ . Please see your local representative or www.dell.com for specific details		

¹

Dell ProSupport availability and terms vary by region. See <u>dell.com/servicecontracts/global</u>. Accidental Damage Service excludes theft, loss, and damage due to fire, flood or other acts of nature, or intentional damage. Customer must return damaged unit. Limit of 1 qualified incident per contract year. See <u>dell.com/servicecontracts</u>. System memory may be used to support graphics, depending on system memory size and other factors. Hard Drive capacity varies with preloaded material and will be less. Limited Hardware Warranty available by writing Dell USA LP, Attn: Warranties One Dell Way, Round Rock, TX 78682 or See <u>dell.com/warranty</u>. Offoring and qualibility mount by urgine Some iteme available of the production o 2.

^{3.} 4.

^{5.}

^{6.} 7. Offering and availability may vary by region. Some items available after product introduction.

Please refer to www.epeat.net for specific country registration rating and participation

8. For a complete listing of declarations and certifications, refer to the Dell Regulatory and Environmental Datasheet found in the Manuals section of Product Support information http://www.dell.com/support/home/us/en/1

WYSE 3040 SOFTWARE FEATURE

OS OPTION	ThinOS	ThinOS with PCoIP	ThinLinux
ENVIRONMENT:			
MICROSOFT	RemoteFX (RDP 8.1)	RemoteFX (RDP 8.1)	RemoteFX (RDP 8.1)
CITRIX	Citrix Receiver 4.0.x	Citrix Receiver 4.0.x	Citrix Receiver 13.5
• VMWARE	VMware (RDP)	VMware (RDP & PCoIP)	VMware (RDP, PCoIP and Blast Extreme)
LOCAL BROWSER	N/A	N/A	Firefox Browser Chrome Browser
CERTIFICATIONS	CITRIX HDX READY, CITRIX HDX PREMIUM, CITRIX HDX 3D PRO	CITRIX HDX READY, CITRIX HDX PREMIUM, CITRIX HDX 3D PRO	coming soon

WYSE 3040 THIN CLIENT RECOMMENDED OPTIONS & ACCESSORIES

SOFTWARE MAINTENANCE	Wyse ThinOS software maintenance 1, 2 or 3-year option		
	Dell Wyse Device Manager Workgroup		
MANAGEMENT SOFTWARE	Dell Wyse Device Manager Entreprise		
	Dell Wyse Management Suite		
MONITORS	Dell 19 Monitor E1916H	Dell 19 Monitor P1917S	
	Dell 20 Monitor E2016H	Dell 20 Monitor P2017H	
	Dell 22 Monitor E2216H	Dell 22 Monitor P2217H	
	Dell 24 Monitor E2416H	Dell 24 Monitor P2417H	
DISPLAY ADAPTORS	DisplayPort to Single Link DVI (1920x1200) Adapter		
	Dell DisplayPort to VGA Adapter		
MOUNTING OPTIONS	Wyse 3040 mount (wall mount and behind the Monitor Mount for E-		
	series Monitors)		
	Wyse behind the Monitor Mount for P-series 2017 Monitors		
	Dell Dual Monitor Stand		
	Dell MSA14 Single Monitor Arm Stand		
KEYBOARDS	Dell Multimedia Keyboard-KB216 (default configuration)		
	Dell Wireless Keyboard KM636		
	Dell Smartcard Keyboard KB813		
MOUSE	Dell MS116 Wired Mouse Black (default configuration)		
AUDIO	Dell Pro Stereo Headset UC300		
SECURITY	Dell Premium Keyed Lock		
	Dell Combination Lock LC300		

ESSENTIAL ACCESSORIES



Dell 24 Monitor P2417H (dual setup)



Wyse behind the monitor mount for P-series 2017 monitors (with 3040 mount)



Wyse 3040 mount (wall mount and E-series Monitors)



Dell Wireless Keyboard and Mouse KM636

Dell Pro Stereo Headset UC300 – Skype for Business