

## **Cutting Edge Thin & Zero Clients**

# **V1206-PDS** Zero Client for VMware and Amazon WorkSpaces

TERA2 PCoIP® Portal Processor

Model Numbers: V1206-PDSS, V1206-PDSSF

#### **Industry Leading VDI Performance**

The 10ZiG V1206-PDS is part of our V1200 Tera2 PCoIP® Zero Client Series optimized for VMware and Amazon WorkSpaces environments. With no operating system and no local storage, the V1200 Series line provides an ultra-secure yet powerful and easy to manage endpoint that eliminates the chance of viruses and provides extensive USB security and authentication features. With options ranging from dual through quad screen, PoE, Fiber, DVI-I, DVI-D, DisplayPort and Integrated SIPRNet Smart Card Reader with up to 6 USB 2.0 ports as well as standard TAA Compliance on all V1200 Series Zero Clients, you can be confident in finding a device that will fit your ideal use case environment.

The V1206-PDS model highlighted below comes equipped with 1 x DisplayPort, 1 x DVI, 6 x USB 2.0 along with an Integrated SIPRNet Smart Card Reader and optional Fiber support (SFP Ready). All 10ZiG V1200 Series PCoIP® Zero Clients receive a one-year, free subscription to the Teradici Desktop Access Plan. The Desktop Access Plan includes the Teradici Management Console with a subscription to firmware and security updates as well as tech support.







► TERA2 PCoIP Portal Processor, Tera2321 PCoIP Chipset ▶ 1 x DisplayPort and 1 x DVI-I ▶ 6 x USB 2.0 ► Integrated SIPRNet Smart Card Reader Optional Fiber support (SFP Ready) ► TAA Compliant ► Optional VESA Mount ▶ 1 year free subscription to the Teradici Desktop Access Plan

**vm**ware



E: info@10ZiG.com



**Microsoft** 



### V1206-PDS Zero Client

# **10ZiG**®

#### Tera2 PCoIP Zero Client Series





#### **SPECIFICATIONS**

- 1. Integrated SIPRNet Smart Card Reader
- 2. Line Out
- 3. Mic In
- 4. USB 2.0 (4)
- 5. Power Switch
- 6. Power / PCoIP Session LEDs
- **7.** USB 2.0 (2)
- 8. RJ45 LAN Port (optional SFP Ready)
- **9.** DVI-I
- 10. DisplayPort
- 11. DC Jack
- 12. Kensington Lock

System Specifications	
Management Utility	Teradici Management
Form Factor	Slim Line
Processor	Teradici PCoIP® Portal Processor - TERA2
Chipset	TERA2321 PCoIP®
Dimensions	
Device	1.29"(H) x 4.96"(D) x 6.49"(W) - 33mm x 126mm x 165mm
Weight	1.49 lbs (.68 kg)
Connections	
Ports	$6 \times \text{USB } 2.0, 1 \times \text{DVI-I}, 1 \times \text{DisplayPort}, 1 \times \text{Mic In}, 1 \times \text{Line Out}, \text{RJ-45 LAN (optional SFP Ready)}, 1 \times \text{DC Jack}, 1 \times \text{Integrated SIPRNet Smart Card Reader}$
Video Resolution	1 Monitor at 2560 x 1600 or 2 Monitors at 1920 x 1200
Networking	
Ethernet	10/100/1000 Base-T
Fiber	Optional SFP Fiber Connector (100/1000Mbps) - V1206-PDSSF
Environmental	
Operating Temp.	32-104F (0-40C), 10-90% non-condensing humidity
Power	6 Watts, DC-12V/3A External Power Adapter
Certifications	
CE, FCC, CAN ICES-3/NMB-3	3, VCCI, UL, TUV-GS, C-Tick, GOST, BSMI, RoHS











