



Help save time with Smart Tasks shortcuts.[1] Get automatic two-sided scanning and ink savings.[4]

A revolutionary smart printer that works the way you need. Help save time with Smart Tasks shortcuts,[1] and get automatic two-sided scanning, easy mobile printing,[1] seamless connections,[2] and best-in-class security.[6] Save up to 50% on ink.[4]



Designed to save you time

Eliminate steps in repetitive tasks, using Smart Tasks.[1] Scan to the cloud, email, and more – in a tap.[1]

Freedom to work anywhere


Connect to cloud-based printing with Wi-Fi™ or your cellular network to print from anywhere.[1]

Save up to 50% on ink

Save on ink and get it automatically delivered to your door.[4,5]

Featuring

Customizable shortcuts on your phone or printer



Create editable, searchable documents

Two-sided. Hands-free. Auto-fed

Ready when you are

Printing just got more productive

Amazing scanning, now on your smartphone

Specifications

Print Resolution Technologies	HP Thermal Inkjet
Print quality black (best)	1200 x 1200 rendered dpi
Print quality color (best)	Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
Print speed black (ISO, A4)	Up to 22 ppm
Print speed black (ISO, letter)	Up to 22 ppm
Print Speed Color (ISO)	Up to 18 ppm
Print speed color (ISO)	Up to 18 ppm
Print speed	Print speed up to 22 ppm (black) and 18 ppm (color)
Functions	Print, copy, scan, fax
Duplex printing	Automatic (standard)
Duty cycle (monthly, A4)	Up to 25,000 pages
Duty cycle (monthly, letter)	Up to 25,000 pages ^[7]
Printer smart software features	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On;
Scanner advanced features	OCR (Optical Character Recognition); Smart Tasks shortcuts: 1-click customizable scan to cloud destinations, email, and print, create editable, searchable documents by scanning from phone or printer; Smart Tasks destinations: Dropbox, Google Drive, One drive, email recipients, print
Fax smart software features	Digital Fax; Fax to PC is available with Windows. Visit http://www.hp.com/support to download the latest software
Energy savings feature technology	Schedule On and Schedule Off
Replacement cartridges	HP 962 Black Original Ink Cartridge (~1,000 pages) 3HZ99A; HP 962 Cyan Original Ink Cartridge (~700 pages) 3HZ96A; HP 962 Magenta Original Ink Cartridge (~700 pages) 3HZ97A; HP 962 Yellow Original Ink Cartridge (~700 pages) 3HZ98A; HP 962XL Black Original Ink Cartridge (2,000 pages) 3JA03A; HP 962XL Cyan Original Ink Cartridge (1,600 pages) 3JA00A; HP 962XL Magenta Original Ink Cartridge (1,600 pages) 3JA01A; HP 962XL Yellow Original Ink Cartridge (1,600 pages) 3JA02A. Actual yield varies considerably based on content of printed pages and other factors. For details see http://www.hp.com/go/learnaboutrcartridges
Supplies feature	HP Instant Ink eligible
Connectivity, standard	1 USB 2.0; 1 Host USB; 1 Ethernet; 1 Wireless 802.11b/g/n; 2 RJ-11 modem ports
Connectivity, optional	No
Network capabilities	Yes, via built-in Ethernet, wireless 802.11b/g/n
Wireless capability	Yes
Mobile printing capability	Apple AirPrint™; Mobile Apps; Wi-Fi® Direct Printing; Mopria™ Certified; HP Smart
Network protocols, supported	9100; LPR; SNMP; SLP; Internet Printing Protocol (IPP); WS-Print, Wireless
Software included	HP Printer Software, Shop for Supplies Online
Compatible Operating Systems	Windows 10, 8.1, 8, 7, Windows Server 2008 R2 64-bit, Windows Server 2008 R2 64-bit (SP1), Windows Server 2012 64-bit, Windows Server 2012 R2 64-bit, Windows Server 2016 (Windows XP and Windows Vista not supported)
ENERGY STAR® certified	Yes
Copy speed black (best, A4)	Up to 5 cpm
Copy speed black (best, letter)	Up to 5 cpm
Copy speed color (best, A4)	Up to 4 cpm
Copy speed color (best, letter)	Up to 4 cpm
Digital sending standard features	Scan-to E-mail; Scan to network folder; scan to SharePoint; Scan to thumb drive
Fax Resolution Black (best)	Up to 300 x 300 dpi
Faxing	Yes, color
Scan speed (normal, A4)	Up to 8 ipm (200 ppi, b&w); Up to 8 ipm (200 ppi, color)
Scan speed (normal, letter)	Up to 8 ipm (200 ppi, b&w); Up to 8 ipm (200 ppi, color)
Scan file format	JPG, BMP, TIFF, PDF, RTF, TXT, PNG
Scan input modes	Front-panel scan; copy; fax; Software; Mobile apps

Scan technology	Contact Image Sensor (CIS)
Scanner type	Easy slide-off glass, 2-sided ADF
Display	2.65 in (6.75 cm) Touchscreen CGD (color graphics)
Minimum dimensions (W x D x H)	439.3 x 342.5 x 278 mm
Minimum dimensions (W x D x H)	17.3 x 13.48 x 10.94 in
Weight	8.95 kg
Weight	16.69 lb
Power consumption	Up to 30 watts (printing), 5.80 watts (ready), 1.20 watts (sleep), 0.08 watts (manual-off) ^[3]
Power supply type	Internal (Built-in) Universal Power Supply
What's in the box	HP OfficeJet Pro 9015 All-in-One Printer; HP 962 Setup Black Ink Cartridge; HP 962 Setup Cyan Ink Cartridge; HP 962 Setup Magenta Ink Cartridge; HP Setup 962 Yellow Original Ink Cartridge; No CD Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide. ^[8]
Warranty	One-year limited hardware warranty; 24-hour, 7 days a week Web support; business hour phone support within warranty period

Accessories and services

No Recommended Accessories and Services

Messaging Footnotes

[1] Requires the HP Smart app download. For details on local printing requirements see <http://hp.com/go/mobileprinting>.

[2] Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at <http://hp.com/go/mobileprinting>. Wi-Fi is a registered trademark of Wi-Fi Alliance®.

[4] FOR U.S.: Based on monthly subscription cost using only all pages in plan vs. cost per page of most color inkjet cartridge printers < \$400. Share of New Inkjet Unit Shipments (< \$400) for 2018Q1 period in the US from IDC 2018Q1 Final Release. Standard cartridge CPP from gap intelligence 7/24/18. FOR CAN: Based on monthly subscription cost using only all pages in plan vs. cost per page of most color inkjet cartridge printers <\$400 CAD. Standard cartridge CPP from internal research. Share of New Inkjet Unit Shipments (< \$400) for 2018Q1 period in Canada from IDC 2018Q1 Final Release.

[5] Based on plan usage, Internet connection to eligible HP printer, valid credit/debit card, email address, and delivery service in your geographic area.

[6] Compared to the majority of competing in-class consumer color desktop inkjet all-in-ones <\$299 USD. Keypoint Intelligence - Buyers Lab 2018 research study commissioned by HP based on research survey of printer manufacturers' published specifications, sustainability reports, and press releases as of 12/15/2018 and not confirmed by lab testing. Market share as reported by IDC CYQ3 2018 Hardcopy Peripherals Tracker, 2018Q3 Release. AiO with best in-class security features based on review of published embedded security features of competitive in-class models and defined as offering business-class, multi-point security, including but not limited to: encryption at the level of data, device, network, document; enterprise-class Wi-Fi security; and secure printing. For more details, see <http://www.keypointintelligence.com/HPOfficeJetPro>.

Technical Specifications Footnotes

[3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.

[7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement

[8] For more information about page yields for replacement cartridges see <http://hp.com/go/learnaboutsupplies> for setup cartridges click on Setup supplies link on the same page.

