


Key Features

SuperClear IPS | Seamless Viewing Experience | A More Comfortable Workspace | Environmentally Friendly Packaging | Convenient & Versatile Stand



Product Description

Designed for the modern day office, the ViewSonic® VG2755-2K monitor delivers an efficient end-to-end enterprise experience. USB 3.1 Type-C connectivity provides charging power, data, video, and audio over a single connector for convenience and reduced cable clutter. SuperClear® IPS panel technology delivers wide-angle viewing and incredibly vivid colors, while 3-sided thin bezel design provides a seamless viewing experience for multi-monitor setups. For enhanced productivity, an advanced ergonomic design offers a wide range of customizable adjustments for maximum comfort including pivot, swivel, height adjustment, and tilt. With the ability to tilt an impressive 40-degrees, this 27" monitor is ideal for users who prefer to work while standing up, as well as for those who like to use their screen for group discussions. Along with USB 3.1 Type-C, additional connectivity options include HDMI, DisplayPort, and USB 3.0. This monitor is also shipped in eco-friendly biodegradable packaging, along with an easy-to-install quick release stand that makes for simple out-of-the-box setup. The quick release stand also includes an integrated client mount and cable management features.



27"
DISPLAY



IPS
PANEL



2560 x 1440
RESOLUTION

Contact Sales

- call: 888.881.8781
- email: salesinfo@viewsonic.com
- visit: viewsonic.com

Display:

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS
Resolution:	2560 x 1440
Resolution Type:	1440p
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	80,000,000:1
Light Source:	WLED
Brightness:	250 cd/m2
Colors:	16.7M
Color Space Support:	True 8 bit
Aspect Ratio:	16:9
Response Time (Typical GTG):	15ms
Response Time (GTG w/OD):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30,000
Panel Surface:	Anti-glare, Hard coating (3H)

Compatibility:

PC Resolution (max):	2560x1440
Mac® Resolution (max):	2560x1440

Connector:

USB 3.0 Type A(3), USB 3.0 Type B(1), USB 3.1 Type C(1), HDMI 1.4(1), Display Port(1)

Audio:

Internal Speakers:	2W (x2)
--------------------	---------

Power:

Eco Mode (Conserve):	18.7 W
Eco Mode (optimized):	22.6 W
Consumption (typical):	27.7 W
Consumption (max):	57.7 W
Voltage:	AC 100-240V (universal), 50-60Hz
Stand-by:	0.3 W
Power Supply:	Internal

Additional Hardware:

Kensington Lock Slot:	1
-----------------------	---

Controls:

Physical Controls:	1, 2, 3, 4, 5, 6 (Power)
On Screen Display:	Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Advanced Image Adjust, Setup Menu, Memory Recall (See user guide for complete OSD functionality)

Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

Mount:

VESA Compatible:	100 x 100 mm
------------------	--------------

Video Signal:

Frequency Horizontal:	15 ~ 90 KHz
Frequency Vertical:	49 ~ 75 Hz

Video Input:

Digital Sync:	TMDS for HDMI (v1.4), PCI-E for DisplayPort (v1.2), Micro-Packet for USB Type C
---------------	---

Ergonomics:

Height Adjust (mm):	130
Swivel:	120°
Pivot (Right/Left):	90° / 90°
Tilt (Forward/Back):	40° / 5°

Weight (Imperial):

Net (lbs):	15.2
Net Without Stand (lbs):	9.9
Gross (lbs):	22.5

Weight (metric):

Net (kg):	6.9
Net Without Stand (kg):	4.5
Gross (kg):	10.2

Dimensions (Imperial) (WxHxD):

Packaging (in.):	27.2 x 8.6 x 16.9
Physical (in.):	24.1 x 16.0 x 8.0
Physical Without Stand (in.):	24.1 x 14.3 x 2.0

Dimensions (metric) (WxHxD):

Packaging (mm):	692.0 x 218.0 x 430.0
Physical (mm):	613.0 x 406.0 x 202.0
Physical Without Stand (mm):	613.0 x 363.0 x 52.0

General:

Regulations: cTUVus, FCC-B, ICES003, Energy Star, EPEAT, MX-CoC, Mexico Energy

PACKAGE CONTENTS: VG2755-2K, Power Cable, DP to DP Cable, USB Upstream Cable, Quick Start Guide

Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.

Warranty: Three-year limited warranty on parts, labor and backlight

UPC: 766907992014

Accessories:

CB-00008948, CB-00009950, CB-00010684, CB-00010958, LCD-CMK-001, LCD-WMK-001