



## Looks great. Performs even better.

Enjoy a big screen experience with this stylish HP display. Advanced IPS technology provides up to 178° ultra-wide viewing angles with consistent detail and vibrant color. This ultraslim, nearly borderless design with FHD[1] comes at a great value and gives you the connections you need to easily hook up your laptop or desktop.



### More screen in less space

Enjoy more desk space than you thought possible with this ultraslim HP display. The attractive, micro-edge design adds stylish beauty to any environment.

### Remarkable viewing experience

This FHD[1] display gives you IPS technology and ultra-wide viewing angles that combine to give you an amazing view up to 178°. Seeing is definitely believing.

### Easy connectivity

Get the picture quality you're looking for without the need for additional dongles. Conveniently connect your devices with VGA and HDMI ports and enjoy a crisp, clear picture in FHD.[1]

### Featuring

#### Step up to the best

No matter where you stand, an HP IPS monitor delivers clear, vivid images. IPS technology ensures image accuracy and consistency across the ultra-wide viewing spectrum. Enjoy the same wide viewing experience as premium tablets and mobile devices.

#### FHD display / 1080p display


Be prepared for brilliant visuals and crisp images with the unforgettable quality of this stunning FHD display. [1]

#### Low blue light

Using the Low Blue Light mode subtly shifts your display's colors to a warmer spectrum, while making whites more natural and putting less strain on your eyes.

#### Adjust your view

Adjust the screen to your personal preference with a 5-degree forward or 23-degree backward tilt.



## Specifications

<b>Display size (diagonal)</b>	21.5"
<b>Panel technology</b>	IPS
<b>Display size (diagonal)</b>	54.6 cm (21.5")
<b>Aspect ratio</b>	16:9 <sup>[1]</sup>
<b>Native resolution</b>	FHD (1920 x 1080)
<b>Resolutions supported</b>	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
<b>Pixel pitch</b>	0.247 mm
<b>Brightness</b>	250 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	14 ms gray to gray <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	49.17 x 3.75 x 30.22 cm (Head only.)
<b>Minimum dimensions (W x D x H)</b>	19.36 x 1.48 x 11.9 in (Head only.)
<b>Dimensions With Stand (W x D x H)</b>	49.17 x 16.9 x 39.08 cm
<b>Weight</b>	2.4 kg (Head only.)
<b>Weight</b>	5.29 lb (Head only.)
<b>Display features</b>	Anti-glare; Language selection; On-screen controls; Plug and Play; User controls; User programmable
<b>Display Input Type</b>	1 HDMI 1.4 (with HDCP support); 1 VGA
<b>Onscreen controls</b>	Brightness; Color control; Contrast; Exit; Image control; Input control; Language; Management; Menu control; Power control
<b>Display scan frequency (horizontal)</b>	30-80 KHz
<b>Display scan frequency (vertical)</b>	50-60 Hz
<b>Camera</b>	No integrated camera
<b>Power</b>	Input voltage 100 to 240 VAC
<b>Power consumption</b>	20 W (maximum), 18 W (typical), < 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% non-condensing
<b>Sustainable impact specifications</b>	Arsenic-free display glass; Low halogen; Mercury-free display backlights
<b>Certifications and compliances</b>	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CEL Grade 1; C-Tick; cTUVus; EAC; Energy Star; E-standby; EUP Lot-6; FCC; ICES; ISO 9241-307; KC/KCC; MEPS; Microsoft WHQL Certification (Windows 10, Windows 8.1 and Windows 7); TUV Bauart; VCCI; Vietnam MEPS; WEEE; ISC; Low blue light; UkrSEPRO; South Africa MEPS; Ukraine Energy label
<b>Physical security</b>	Security lock-ready <sup>[3]</sup>
<b>Management Software</b>	Auto adjustment pattern utility
<b>UPC number</b>	(A2N) 192545212786; (AB1) 192545212670; (ABA) 193015563759; (ABB) 192545212700; (ABG) 192545212687; (ABJ) 192545212694; (ABT) 192545212748; (ABU) 192545212717; (ABV) 192545212762; (ABY) 192545212731; (ACQ) 192545212755; (UUF) 192545212663; (UUG) 192545212779; (UUZ) 192545212724
<b>What's in the box</b>	Monitor; HDMI cable; Documentation; Power adapter

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## **Messaging Footnotes**

[1] Full high-definition (FHD) content required to view FHD images.

## **Technical Specifications Footnotes**

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[3] Lock is sold separately.

---

© Copyright 2018 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR® and the ENERGY STAR® mark are registered trademarks of the U.S. Environmental Protection Agency.

