



HD-TVI Vandal Resistant Corner Mount Color Camera

CVC607CMT 3.6mm lens - optional lenses available, grey housing

Features

- Supports up to Full HD 1080p @ 30fps
- Full HD resolution over coax
- Vandal resistant 90° corner mount camera
- Heavy duty housing is built to withstand blows from a 10 lb. sledgehammer
- 12VDC operation
- Additional analog output for 960H
- 5 year warranty

**HD
TVI**



Specifications

Image Sensor	1/3" Progressive Scan CMOS, 2MP
Resolution.....	1920 x 1080
Effective Pixels	1984 (H) x 1105 (V)
Total Pixels	2000 (H) x 1121 (V)
Electronic Shutter	1/30 sec. – 1/30,000 sec.
S/N Ratio	More than 50dB
Video Output.....	1.0Vp-p / 75 ohms
Power Consumption	200mA
Power Supply	12VDC (power supply not included)
Operating Temperature.....	14° F – 122° F
Housing	16 gauge steel
Dimensions.....	5.1" (W) x 3.3" (H)
Weight	1.5 lbs.
Communication.....	UTC

Optional Accessory



PSW5
12VDC
Power Supply

Optional Lenses

CVC607CMT2.2	2.2mm lens
CVC607CMT2.5	2.5mm lens