



KRAMER

VIACast

Miracast Enabled USB Dongle for VIA Devices



VIACast transforms your VIA GO, VIA Connect PRO and VIA Connect PLUS into a true BYOD presentation solution. Laptops and smartphones, Android and Apple can all display simultaneously to the same presentation screen. Simply plug the USB dongle into your VIA and select your display device to begin presenting.

When downloading and installing apps isn't an option and navigating networks and passwords takes time you don't have, VIACast is the ultimate hassle-free presentation solution.

Note: Supported by VIA Connect PRO 2017 edition only

FEATURES

USB dongle for VIA GO, VIA Connect PRO and VIA Connect PLUS (firmware V2.4 required)

No network infrastructure required

Windows® 10 native support

Compatible with Android devices that support Miracast®

Up to 1080p resolution



TECHNICAL SPECIFICATIONS

STANDARDS COMPLIANCE	Standards: IEEE 802.11a, 802.11b, 802.11g, 802.11n, 802.11ac Certifications: FCC, CE, IC, RoHS, WEEE, IDA, C-Tick, Wi-Fi A/B/G/N/AC
Connector:	USB 3.0
User Interface	Indicator: Communication LED
Antenna:	2 internal, dual-band
Security Features:	Up to 128-bit encryption
Operating Frequency Range (Mhz) 1	Low Frequency (MHz): 2400, High Frequency (MHz): 2483.5, Power (Watt): 0.1, Bandwidth (Khz): 40,000.00, Type of Modulation: OFDM
Operating Frequency Range (Mhz) 2	Low Frequency (MHz): 5150, High Frequency (MHz): 5350, Power (Watt): 0.1, Bandwidth (Khz): 40,000.00, Type of Modulation: OFDM, DSSS
Environmental Conditions	Operating Temperature 0° to +40°C (32° to 104°F) Storage Temperature: -20° to +70°C (-4° to 158°F) Operating Humidity: 10% to 85%, RHL non-condensing Storage Humidity 5% to 90%, RHL non-condensing
Product Dimension	11.80cm x 11.50cm x 4.00cm (4.65" x 4.53" x 1.57") W, D, H
Product Weight	0.0kg (0.0lbs) approx
Shipping Dimension	12.60cm x 8.40cm x 4.10cm (4.96" x 3.31" x 1.61") W, D, H
Shipping Weight	0.1kg (0.1lbs) approx