




2-Port Dual Monitor DVI KVM Switch

TK-232DV (v1.0R)

- Dual Monitor DVI-I KVM switch
- Designed for use with Dual DVI-I systems
- 3.5mm speaker and microphone connections
- Supports digital resolutions up to 1920 x 1200
- Supports analog resolutions up to 2048 x 1536
- 2-Port USB 2.0 hub for storage devices and printers
- Required cabling sold separately (TK-CD06, TK-CD10, TK-CD15)
- No CD installation required

TRENDnet's 2-Port Dual Monitor DVI KVM Switch, model TK-232DV, allows you to control two computers with one set of console controls. Experience HD resolutions with no driver installation required. The TK-232DV is designed for dual monitor systems with USB mouse and keyboard connections. This dual monitor KVM switch also features a two-port USB hub to share storage devices or printers between computers.




DVI-I Monitor

Dual monitor KVM switch designed to connect to two DVI-I monitors.



HD Resolution


Supports digital resolutions up to 1920 x 1200, and analog resolutions up to 2048 x 1536.



USB 2.0 Hub

Two additional USB ports to connect storage devices and printers.

Networking Solution



2-Port KVM Switch

Dual monitor KVM switch controls up to 2 computers



USB Mouse & Keyboard

True Transparent USB (TTU) emulation technology supports most keyboard and mouse designs



Hot Keys

Hot Key command shortcuts



HD Resolution

Supports digital resolutions up to 1920 x 1200, and analog resolutions up to 2048 x 1536



DVI-I Monitor

Dual monitor KVM switch designed to connect two DVI monitors with active sync replication for maximum video compatibility



Audio

Features 3.5mm speaker and microphone connections for full audio support



USB 2.0 Hub

Two additional USB ports to connect storage devices and printers

Specifications

Console Port Connectors	<ul style="list-style-type: none"> • Keyboard: USB Type A • Mouse: USB Type A • Monitors: 2 x DVI-I • 2-port USB 2.0 Hub • Speaker jack: 3.5 mm • Microphone jack: 3.5 mm
KVM Port Interface (up to 2)	<ul style="list-style-type: none"> • Keyboard/Mouse: USB Type B • Monitors: 2 x DVI-I • Speaker jack: 3.5 mm • Microphone jack: 3.5 mm
Computer Interface (up to 2)	<ul style="list-style-type: none"> • Keyboard/Mouse: USB Type A • Monitors: 2 x DVI-I • Speaker jack: 3.5mm • Microphone jack: 3.5mm
Monitor Resolution	<ul style="list-style-type: none"> • Digital: up to 1920 x 1200 • Analog: up to 2048 x 1536
Switching Control	<ul style="list-style-type: none"> • Front panel push buttons • Keyboard hot key commands
Operating Temperature	<ul style="list-style-type: none"> • 0° – 40° C (32° – 104° F)
Operating Humidity	<ul style="list-style-type: none"> • Max. 90 % non-condensing

Power	<ul style="list-style-type: none"> • Input: 100 - 240V AC, 50/60Hz, 0.8A • Output: 9V DC, 2A external power adapter • Max. consumption: 0.7W
Dimensions	<ul style="list-style-type: none"> • 163 x 100 x 66 mm (6.4 x 3.9 x 2.6 in.)
Weight	<ul style="list-style-type: none"> • 760g (1.675 lbs.)
Certifications	<ul style="list-style-type: none"> • CE • FCC
Warranty	<ul style="list-style-type: none"> • 2 year

PACKAGE CONTENTS

- TK-232DV
- Quick Installation Guide
- Power adapter (9V DC, 2A)

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.