



NRP Series

4K H.265 NVR A Premium Smart NVR with PoE

N8NRP

8 Channel NVR with 8 Built-In PoE Ports

N16NRP

16 Channel NVR with 16 Built-In PoE Ports



STORAGE
2TB - 16TB

N8NRP2TB	N8NRP8TB	N16NRP2TB	N16NRP8TB
N8NRP4TB	N8NRP12TB	N16NRP4TB	N16NRP12TB
N8NRP6TB	N8NRP16TB	N16NRP6TB	N16NRP16TB



Front panel



Rear panel

N16NRP (Shown)



Key Features

EZ Wizards - For ease of use and setup

- Camera: quickly discover and install all Speco IP cameras
- Setup: for quick setup of general settings
- Network: network setup and port forwarding
- Record: quickly setup recording resolutions and recording type
- Search: quickly search for events from thumbnails
- Copy: quickly copy what you are playing onto a USB flash drive

- Real time recording up to 8MP resolution (4K) at 30fps
- H.265 compression - Store up to 2x more than H.264!
- Built-in PoE ports for all channels for easy installation
- 2 SATA ports for up to 16TB of storage
- 4K HDMI out and VGA monitor output
- Object and line crossing detection and alerts*
- Smart Search - Specify a region on the camera view and search on changes in that area*
- 2-way audio communication
- Free US-based DDNS and P2P services
- Remote viewing via web browser or your mobile device
- Easy video exporting via USB
- Up to 16TB storage
- 5 year limited warranty¹

*with Speco Smart Analytic Cameras

Additional Features

- Plug & play feature with isolated traffic on the PoE ports with Speco's IP cameras
- Find and install IP cameras on the local network without needing to locate the cameras manually
- Supports different recording types: Continuous, Motion, Analytics, and Sensor
- Create bookmark pins on playback for easy reference
- Instant playback for individual channels directly from the live view screen
- Customizable channel view placement
- Remote monitoring, recording, playback, configuration, upgrades, and PTZ control via the internet
- Simultaneous HDMI & VGA video output
- Built-in S.M.A.R.T technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- Supports 2-way audio communication (speaker required)
- Works with a majority of cameras that are conformant with ONVIF Profile S

Optional Accessory



ERS1V
Vented Rack Shelf

¹Limited Warranty/Hard drives excluded. Check www.specotech.com for more details. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 9/11/18



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com





Technical Specifications:
4K H.265 NVR A Premium Smart NVR with PoE

Model		NRP			
Video	Input	Max. IP Channels	8	16	
		IP Camera	H.264/H.265 Auto Detection (Max 8MP)		
	Output	Main Monitor	HDMI (Max. 4K) and VGA (Max. Full HD)		
		Sub Monitor	n/a		
Audio	Local Input/Output		0/1		
	Codec		G.711A/G.711U		
	Audio Input		1ch, RCA, 8CH IPC input	1ch, RCA, 16CH IPC input	
Recording	Encoding Resolutions		8MP/5MP/4MP/3MP/1080P/720P		
	Codec		H.264/H.265 (Auto Detection)		
	Max Frame Rate per Channel		Any Resolution @30fps		
	Recording Mode		Analytics/Continuous/Motion/Sensor/Schedule/Manual		
	Pre-Recording		Max. 5 seconds		
	Post Recording		Max. 10 minutes		
Search & Playback	Search		EZ Search, Motion, Specific Date/Time, Event, Museum, Bookmarks, Snapshots, Log		
	Multi-Decoding		1, 4, 8	1, 4, 9, 16	
	Playback Resolutions		8MP/5MP/4MP/3MP/1080P/720P		
	Playback Functions		Play, pause, FF, FB, digital zoom, etc.		
Backup	Media		USB drive, USB Portable HDD, Network		
	Format		JPG, AVI, ZIP (Player+Proprietary Data)		
Storage	HDD	Capacity of 1 HDD	8TB		
		Internal HDDs	2		
	USB	Front	1		
		Rear	1		
Alarm	Input/Output		Supports IPC Alarm In/IPC Alarm Out		
	Trigger Events		Recording, PTZ, Alarm Out, Pop-up alarm preview, Email, FTP, Snapshot, Buzzer and Screen Tips		
User I/F	Input Method		IR Remote, Mouse		
Network	Port		100Mbps + 8PoE	1Gbps + 16PoE	
	P2P/Dynamic DNS		Free US-Based Speco P2P and DDNS Service		
	Network Protocols		TCP/IP, PPPoE, DHCP, DNS, UPnP, NTP, SMTP		
Network Access	Mobile		iOS/Android via Speco Blue App		
	Web Viewer		Windows IE		
	VMS		SecureGuard®		
	Max. User Access		Max 10 users online (web client)		
Features	Digital Zoom		Live and Playback, Free Size		
	Smart Analysis		Abandoned object detection, Missing object detection, Line Crossing		
	ONVIF Support		ONVIF 2.6		
	S.M.A.R.T		Temperature, Power On Time, Bad Sectors and Health		
Power	Input Voltage		DC48V		
	Power Consumption		≤ 5W (without HDD)	≤ 15W (without HDD)	
Environment	Operating Temperature		-10°C ~ 50°C		
	Operating Humidity		10% ~ 90% humidity (Non-condensing)		
Dimensions	Unit		380mm x 268mm x 52mm (15.0" x 10.5" x 2.0")		

Please note that specifications and unit exterior design are subject to change without notification. Rev. 9/11/18



800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

