

## USB-C Multiport Adapter - 4K HDMI, USB 3.x (5Gbps) Hub Port, Self-Storing Cable, 100W PD Charging, Black

MODEL NUMBER: U444-T6N-H4UBC



4K USB-C adapter connects an HDMI monitor and USB device to the USB-C or Thunderbolt 3 port on your smartphone, MacBook or Chromebook.

### Features

**USB 3.1 Type-C Adapter Connects an HDMI Monitor to Your USB-C or Thunderbolt 3 Device** This USB 3.1 C adapter helps you transmit digital audio and 4K video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to an HDMI-enabled television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video for digital signage in crystal-clear 4K. **Supports USB-C DisplayPort Alternate Mode for Transmitting Audio/Video Signals**

By connecting the self-storing USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers.

**Transmits Crystal-Clear 4K HDMI Video and Digital Audio** To send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (such as P568-Series cables, sold separately). The USB to HDMI 4K adapter supports video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz. It's backward compatible with 1080p displays, allowing you to use it with older equipment.

**PD Charging Port Charges Connected Device via AC Wall Charger** The USB-C Power Delivery 3.0 port provides power output up to 5 amps (100 watts), which is more than sufficient for charging and powering the connected source device, such as a MacBook or Chromebook. Just connect the device's AC wall charger to the USB-C PD port. **Note: USB-C PD port does not support Quick Charge (QC).**

**Connects USB Peripherals and Transfers Data at Fast USB 3.1 Gen 1 Speeds** The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer, and provides up to 1.5 amps (7.5 watts) for charging and powering mobile devices. Like the USB-C PD port, it transfers data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB Type-C adapter is backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note: Host must support USB OTG (On-the-Go).**

**Self-Storing USB-C Cable Connects in Either Direction** Connect the reversible USB-C plug to your

### Highlights

- Transmits video signals from sources supporting USB-C DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Power Delivery cable provides 5A (100W) power output for charging connected device
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use

### Applications

- Play video from your MacBook or Chromebook on a large-screen HDTV
- Give a video presentation at a meeting, training session or conference
- Write and edit multiple documents on a bigger monitor
- Stream 4K video for digital signage at a trade show
- Charge and power a USB-C or Thunderbolt 3 device
- Connect a USB peripheral, such as an external hard drive, printer or hub

### System Requirements

- Source device with USB-C or Thunderbolt 3 output that supports USB DisplayPort Alternate Mode
- Display device with HDMI input

### Package Includes

- U444-T6N-H4UBC USB-C Multiport Adapter, Black
- Owner's manual

source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. The six-inch cable wraps into the adapter when not in use, making the unit easy to carry in a briefcase or laptop bag for connecting on the go.

**Ready to Use Right Out of the Package** The plug-and-play USB 3.1 Type-C adapter is specifically designed for the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power.

## Specifications

OVERVIEW	
UPC Code	037332232779
Product Type	USB-C Multiport Adapter
Technology	HDMI; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE)
Video Ports Details	HDMI 1.4; HDCP 1.4
Resolutions Supported	HDMI: 4K 30Hz (3840 x 2160)
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 3840x2160 (4K)
Max Supported Video Resolution	3840 X 2160 (4K X 2K) @ 30HZ
Extended Mode	Yes
Extended Mode Details	Extends a 4K video resolution to a connected HDMI display
Mirror Mode	Yes
Mirror Mode Details	Mirror a desktop to a connected 4K display
3D Video Supported	Yes
DATA	
Data Ports	USB A (FEMALE); USB C (FEMALE)
Data Ports Details	USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.45
Built-In Cable Length (m)	0.14
Built-In Cable Length (in.)	5.37

Built-In Cable Length (cm)	13.7
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	Yes
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	100W; 3.0
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Amps	5
Total Charging Watts	100
Charging Method	USB
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports	USB-A: 5V 1.5A (7.5W); USB-C: 100W (20V 5A) Power Delivery (PD 3.0)
Charging Ports Details	Provides up to 100W (20V/5A) of power to the host device via the PD Charging portCharge a peripheral device with up to 7.5W (5V/1.5A) of power via the USB-A port
Charging Ports / Amps	1.5A; 5A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	TPE, ABS
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.80 x 5.50 x 3.40
Shipping Dimensions (hwd / cm)	2.03 x 13.97 x 8.64
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
Unit Dimensions (hwd / in.)	0.550 x 1.570 x 2.320
Unit Dimensions (hwd / cm)	1.4 x 4 x 5.9

Unit Packaging Type	Box
Unit Weight (lbs.)	0.07
Unit Weight (kg)	0.03
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	100W (20/5A)
<b>CONNECTIONS</b>	
Number of Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
HDCP Specification	1.4
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); UKCA
<b>WARRANTY &amp; SUPPORT</b>	



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.