



2MP HD-TVI All-in-One Intensifier® Motorized Dome Camera

HTiD21™

2.8-12mm motorized varifocal lens, dark gray housing



Features

- Supports four video signal outputs
- Full HD 1080p @30FPS
- Built-in Dip switch for signal changes
- Superior low-light performance
- Chameleon Cover™ - snaps on and can be painted to match any décor!
- UL Listed
- Dual Voltage
- 5 year warranty



Shown with included paintable, snap-on Chameleon Cover™



Camera Specifications

Image Sensor	1/2.8" CMOS, 2.1MP
Filter	Removable IR Cut Filter
Minimum Illumination	0.005 lux
Supported Resolution	1920 x 1080
Horizontal Resolution	1080p
Vertical Frequency	NTSC: 60Hz, PAL: 50Hz
Scanning System	Progressive
S/N Ratio	≥ 54dB
Electronic Shutter	NTSC: 1/30-1/50, 000S PAL:1/25-1/50, 000S
White Balance	ATW
Backlight Compensation	Off
Auto Gain Control	On
Defog	Off/On
3D/2D	On
DWDR	Off/On
Day / Night	Auto/Color/BW/Ext
Video Output	HD-TVI default (AHD / CVI / CVBS)

Operating & Unit Specifications

Power	12VDC (power supply not included), 24VAC 150mA
Power Consumption	680mA max.
Operating Temperature	-22°F - 104°F
Storage Temperature	-22°F - 140°F
Unit Dimensions	5.96" (H) x 4.3" (W)
Unit Weight	2.64 lbs.

Optional Accessories



PSW5
12VDC
Power Supply



PSW4
24VAC
Power Supply

¹Camera is defaulted to HD-TVI. ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/23/19