



A compact and powerful 4K camcorder

The Legria HFG50 advanced amateur camcorder achieves high mobility which is required for enthusiasts and advanced amateur videographers. The Legria HFG50 is capable of capturing 4K video while the compact and lightweight product realizes superb mobility and operability.

The Legria HFG50 features a 1/2.3-inch CMOS sensor, a 20x optical zoom lens and a DIGIC DV 6 image processor, all in a compact and lightweight body measuring approximately 115 x 84 x 231 mm and weighing approximately 735 g. In addition to 4K/30p video capture across the entire zoom range of 29.3 mm at the wide-angle end to 601 mm at the telephoto end, the Legria HFG50's Over Sampling HD Processing function effectively utilizes data acquired by the 4K imaging sensor to record full HD video at an even higher image quality.



no one sees it like you

Canon

Technical Specifications

Sensor		1/2.3-inch 4K UHD CMOS sensor
Lens	Zooming ratio, focal length (35 mm camera equivalents)	20x optical zoom, approx. 29.3 - 601mm (4K UHD vibration control off/standard IS on)/ approx. 30.5 - 627mm (FHD vibration control off/standard IS on)
	Aperture	8-bladed circular aperture
	Image Stabilizer	Optical + electronic correction
Infrared camera supported		NO
Monitor		3.0-inch (approx. 0.46 million dots), LCD, Capacitive touch panel
EVF		0.24-inch (equivalent to approx. 1.56 million dots)
Movie recording	Video formats	MP4
	Simultaneous Recording	YES
Recording media		SD card (2 slots) (no built in memory)
Terminals for commercial applications	SDI terminal	NO
	GENLOCK, TC(In/Out)	NO
	XLR terminal	NO
Manual control ring		YES: Lens ring (function switched between zoom and focus)
Detachable Handle		YES (Mini Advanced Shoe)
Wi-Fi		NO
GPS		NO (Accessories supported)
Lens hood		YES (with barrier)
Dimensions (lens hood and eye-cup included; grip strap not included)		115 x 84 x 231 mm
Weight	Body only	Approx. 735 g
	Lens hood, BP-820 and memory card (1 pc) included	Approx. 870 g

no one sees it like you



Accessories



**Tele Converter
TL-H58**



**Wide
Attachment
WA-H58**



**Filter (58mm)
PROTECT
ND8xL
ND4xL**



**Video Light
VL-5**



**GPS Receiver
GP-E2**



**Shoulder Strap
SS-600/SS-650**



**Battery Pack
BP-828**



**Directional
Microphone
DM-100***



**Wrist Strap
WS-20**



**Soft Carrying
Case
SC-2000**



**USB Cable
IFC-400PCU**



**High Speed HDM
Cable
HTC-100**



**Remote
Controller
RC-V100**



**Battery Charger
CG-800D**



**Battery Pack
BP-820**

no one sees it like you

Canon