

Print on the go with the CMP-20

Powerful portable printing



Simple design

The CMP-20II printers are designed like all Citizen printers to be simple to use and easy to operate.

Intuitive operation

This, combined with the durable, strong plastic case which is designed to take the occasional knock, means our printers keep running and running.

High capacity media rolls

The CMP printers can accept media rolls with a diameter of approximately two inches.

CMP-20II

Mobile

Applications

- Ticketing
- Retail
- Law Enforcement
- Courier



Portable printers for all your receipt and labelling needs

TOMORROW'S PRINTING TODAY

CITIZEN

Specifications

Model	CMP-20II
Resolution	203 dpi
Print Speed (maximum)	80 mm/sec.
Print Width (maximum)	48 mm
Media Width (min to max)	58 mm
Roll Size (max), Core Size	Diameter 1.88 inches (48 mm)
Media Sensor	Paper end
Main Interface	Dual Interface Serial (RS-232 /mini DIN connector), USB (mini B connector)
Interface	Bluetooth Class 2 , Bluetooth with Apple™ MFi compatibility, Compact Wireless LAN, Bluetooth 4.2
Environmental rating, drop test	Exceeds IP42. Survives multiple drops of 1.5 metres
Battery type and capacity	Li-Ion, 7.4 volt, 1800 mAh
Emulations (Languages)	ESC/POS™ , CPCL™ compatibility, Zebra® ZPL-II®
Size (W x D x H) and Weight	96 x 136 x 58 mm, 0.42 Kg

All product names are trademarks of the respective manufacturers. Zebra®, ZPL and EPL are trademarks of ZIH Corp. Datamax® is a trademark of Datamax-O'Neil Corporation. Designs, specifications and availability are subject to change without notice. Errors and omissions excluded. © Citizen Systems Europe GmbH, V.1.0

CMP-20II

Mobile

Features & Benefits

- Paper load: Quick and easy media changing - drop-in paper loading
- Printing Speed: High speed printing - up to 80 mm per second
- Mobile-POS ready
- Powerful - High capacity batteries for a full day's operation (status indicated by LED)
- Standard clip-in battery
- Car adapter option
- Additional extra batteries
- External battery charger
- Soft cases and shoulder straps
- USB and Serial cables

Memory Stick Reader Factory option. ISO
back (1+2+3),
Factory Option.
1-channel



For Apple, Android and Windows Mobile