



4K Flexible Intensifier® Technology H.265 Bullet IP Camera with Junction Box

O8FB7M 3.6-11 mm motorized lens, dark gray housing



Features

- Flexible Intensifier® Technology to fit any lighting application
- Intensifier® mode allows for a vivid color image without IR LEDs in low light
- Supports ultra HD 4K resolution
- Motorized lens with auto focus for easy installation
- Adaptive high power IR LEDs for a vivid image with no saturation in darkness
- IR range: 130' (depending on scene reflection)
- Built-in standard PoE (IEEE 802.3af)
- True WDR (wide dynamic range) operation
- Supports H.265, H.264, and MJPEG codecs
- 2-way audio communication
- Micro SD card slot (card not included)
- Built-in heater
- Sensor input and relay output
- IP67 compliant, weather resistant
- Conformant with ONVIF Profile S
- Junction Box included for convenience
- 5 year warranty



Included Junction Box



Camera Specifications

Image Sensor	Progressive scan 1/2.5" CMOS, 8.5MP
Effective Pixels	3864(H)x2218(V)
Maximum Resolution	3840 x 2160
Minimum Illumination	0 lux (IR LED on)
White Balance	Auto / Presets
Compensation	WDR / ATR
Day/Night	IR cut filter
Electronic Shutter Speed	1/30 ~ 1/10000 sec
DNR	3D

Video Specifications

Main Resolution	3840x2160 / 3200x1800 / 2560x1440 / 1920x1080 @ 25fps
Compression	H.265, H.264 (HP/MP), MJPEG (sub stream)
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams
Image Settings	Privacy mask, Corridor mode

Audio Specifications

Mono Input	G.711
Mono Output	G.711

External Terminal Specifications

Ethernet	10/100 Mbps
Alarm	1 sensor input, 1 relay output
Audio	1 mic in, 1 line out (RCA)
Power	DC jack
Storage	Micro SD slot

Network Specifications

Protocols	IPv4, TCP, UDP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, UPnP, DNS, NTP, SNMP
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password Protection, IP address filtering, digest authentication
User Access	Max. 8 simultaneous users (actual number of users may vary depending on bandwidth)

System Specifications

PoE	Standard (IEEE 802.3af)
Alarm Triggers	Motion detection, sensor input
Alarm Events	FTP upload, email upload, micro SD card recording, relay output

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Client (iPhone® and Android™)
Embedded Recorder	Speco NVRs/Hybrid, ONVIF Profile S conformant recorders

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	8W (max)
Operating Temperature	-4°F - 140°F
Operating Humidity	0% - 90% RH
Unit Dimensions	3.5" (W) x 3" (H) x 10.5" (D); Base: 3.8" (Diam.)
Unit Weight	2.3 lbs.
Certifications	FCC, RoHS

Optional Accessories



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply



INTCM
Corner/Pole
Mount



INTJBS
Square
Junction Box

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/7/19