

GW4K30GH60

Ultra-Fast 60GHz Wireless 4K UHD Video Extender

- Wirelessly send 4K UHD video from one HDMI source to one HDMI TV/Projector
- Extends signals up to 60 Ft. line-of-sight
- Uncompressed audio and video at near-zero latency - ideal for gaming and streaming
- Resolutions up to 3840 x 2160 @30Hz
- Minimal interference with existing Wi-Fi devices via 60GHz wireless frequency



4K Ultra HD Without Wires


The Ultra-Fast 60GHz Wireless 4K UHD Video Extender (GW4K30GH60) is an ultra-high-performance wireless AV solution that enables you to transmit 4K Ultra High Definition video and high-quality digital 7.1 surround sound audio from an HDMI source over distances up to 60 feet with near-zero latency.

Enjoy Flexible TV or Projector Placement

Eliminate the time and expense required to run costly, unsightly cable. Enjoy the flexibility to place your video source and display equipment wherever it is most convenient in the same large room, such as in a home theater or conference room.

- Wirelessly send 4K UHD video from one HDMI source to one HDMI TV/Projector
- Extends signals up to 60 Ft. line-of-sight
- Uncompressed audio and video at near-zero latency - ideal for gaming and streaming
- Resolutions up to 3840 x 2160 @30Hz
- Minimal interference with existing Wi-Fi devices via 60GHz wireless frequency
- Support 7.1 surround sound audio, Dolby® True HD and DTS-HD® Master audio format
- Plug-n-Play - Transmitter and receiver come pre-paired from factory
- Dedicated closed wireless system - Requires no Wi-Fi network
- Advanced wireless technology speeds to 18 Gbps
- LED status lights for source/display connections and wireless link
- Supports dual power option via USB or included AC adapter
- Compact mountable design for easy placement
- HDMI 2.0 & HDCP 2.2 compliant
- Supports 4K UHD High Dynamic Range (HDR) TVs and content





Requirements

- Video source with HDMI output
- Video display with HDMI input
- AC power outlets or power USB port

Package Contents

- 1 x GW4K30GH60 Transmitter
- 1 x GW4K30GH60 Receiver
- 2 x 3 Foot 2.0 HDMI Cables
- 2 x 5VDC/2A Switching Power Supply
- 1 x Quick Start Guide
- 1 x Warranty Card

Specifications

Function	GW4K30GH60	Dimensions	GW4K30GH60
Connectors		Unit Dimensions	
Video Input	HDMI 2.0/ HDCP 2.2	Height	3"
Video Output	HDMI 2.0/ HDCP 2.2	Depth	4"
Power	5V/1A	Length	1.125"
Video Resolution	3840 x 2160 @ 30Hz	Unit Package Dimensions	
Video Streaming	Uncompressed	Height	5.25"
Audio		Depth	8"
Audio Output	Dolby TrueHD, DTS-HD Master Audio and LPCM digital audio streaming up to 7.1 channels HBR lossless audio	Length	6"
Frequency Band	60 GHz	Master Carton	
Antenna Type	Printed Circuit Board	Width	17"
Environment		Height	14.5"
Operation Temperature	32-122°F (0-50°C)	Depth	6.75"
Storage Temperature	14-158°F (-10-70°C)	Master Carton Qty.	6
Humidity	10 - 90%	Weight	
Power Adapter	5 VDC/1A	Master Carton Wt.	13.60 lb
Housing		Unit Pack Wt.	2.10 lb
Case	Aluminum	Unit Wt.	0.50 lb (x2)
Warranty	1-Year		
Power Consumption	3W		