



# HP OfficeJet Pro 9020 All-in-One Printer

A revolutionary smart printer – even for high-volume jobs. Help save time with Smart Tasks shortcuts,<sup>1</sup> rapid speeds, full-ream paper capacity. Print and scan from your phone,<sup>1</sup> and count on seamless connections and enhanced security.<sup>2</sup>



**Dynamic security enabled printer. Intended to be used with cartridges using only HP original electronic circuitry. Cartridges with modified or non-HP electronic circuitry may not work, and those that work today may not work in the future.**  
<http://www.hp.com/go/learnaboutsups>

**ISO Speed:** Black: Up to 24 ppm; Color: Up to 20 ppm  
**Print Resolution:** Black (best): 1205 x 1200 rendered dpi; Color (best): 4800 x 1200 dpi  
**Scan Resolution:** Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi  
**Copy Resolution:** Black (text & graphics): Up to 600 dpi; Color (text & graphics): Up to 600 dpi  
**Standard Connectivity:** 1 USB 2.0; 1 Host USB (print from JPEG, TIFF, DPOF 1.1, Exif 2.3, PNG); 1 Ethernet; 1 Wireless 802.11b/g/n; 2 RJ-11 modem ports  
**Mobile Printing Capability:** HP Smart; Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified  
**Duty Cycle:** Monthly (letter): Up to 30,000 pages  
**Display:** 2.65 in (6.75 cm) Touchscreen CGD (color graphics)  
**Paper Handling:** 250-sheet input tray, 250-Sheet Multipurpose Tray; Up to 100 sheets with Smart output management

## Designed to save you time

- Eliminate steps in repetitive tasks, using Smart Tasks.<sup>1</sup> Scan to the cloud, email, and more – in a tap.<sup>1</sup>
- Create editable, searchable documents scanning from your phone or printer, using Smart Tasks.<sup>1</sup>
- Work fast and hands-free with the 35-page auto-feeder. Up to two times faster scanning speeds than 9010 series.
- Take on high-volume jobs with confidence, using two 250-sheet paper trays that fit a full ream of paper.

## Freedom to work anywhere

- Connect to cloud-based printing with Wi-Fi or your cellular network to print from anywhere.<sup>1</sup>
- Quickly access and print documents and images on your smartphone, from Dropbox and Google Drive.<sup>1</sup>
- Get high-quality scanning to share to Dropbox, Google Drive, email, or the cloud – from virtually anywhere.<sup>1</sup>
- Get notifications when printing, scanning, or copying from your smartphone.<sup>1</sup>

## Enhanced security, reliable connections

- Reduce interruptions with self-healing Wi-Fi that keeps you connected.<sup>2</sup>
- Get security essentials to help maintain privacy and control.
- Count on chatbot support and helpful notifications with the HP Smart app.<sup>1</sup>
- Extend your printer coverage with HP's 2-Year Next-Business-Day Exchange Care Pack.<sup>5</sup>

## Ordering ink has never been easier

- Print more pages and change cartridges less often with Original HP high-yield cartridges.<sup>4</sup>
- Create vibrant, professional-quality color graphics, ideal for office use and presentations.
- Get rich black text for all your business documents.
- With HP Smart app, you'll get notifications when you are running low on ink, and can easily order new ink.<sup>1</sup>



<sup>1</sup> Requires the HP Smart app download. For details on local printing requirements see <http://hp.com/go/mobileprinting>. <sup>2</sup> Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at <http://hp.com/go/mobileprinting>. Wi-Fi is a registered trademark of Wi-Fi Alliance®. <sup>3</sup> Compared to majority of OEM mobile printing apps for inkjet & laser printers & all-in-ones for home & home office, priced less than or equal to \$429.99 USD. Market share as reported by IDC CYQ2 2018 Hardcopy Peripherals Tracker. Claim based on lab testing and research of printer manufacturer's mobile print apps and Keypoint Intelligence - Buyers Lab study commissioned by HP. See Sept 2018 report at <http://www.keypointintelligence.com/HPSmartApp>. <sup>4</sup> Based on HP 962XL High Yield Black and color Original Ink Cartridges. High-yield ink cartridges not included; purchase separately. For more information, see <http://hp.com/go/learnaboutsups>. Less cost per page compared with manufacturer recommended street price and published page yield of standard-yield HP 962 Original Ink Cartridges. Actual pricing may vary. <sup>5</sup> Visit [www.hp.com/go/extendmywarranty](http://www.hp.com/go/extendmywarranty) within 60 days of your purchase to register and receive your complementary HP Care Pack. To receive this offer you must include proof of purchase. Offer expires after 60 days of printer purchase. Visit the link to learn more about terms and conditions.

## HP OfficeJet Pro 9020 All-in-One Printer Specifications Table

<b>Functions / Multitasking supported</b>	Print, copy, scan, fax / Yes	<b>Media Sizes Supported</b>	Letter; Legal; Government Legal; Executive; Statement; 3 x 5 in; 4 x 6 in; 5 x 7 in; 13 x 18 cm; 8 x 10 in; 10 x 15 cm; L; Photo 2L; Envelope (#10, Monarch, 5.5 bar); Card (3 x 5 in, 4 x 6 in, 5 x 8 in)
<b>Print Speed<sup>5,6</sup></b>	<b>Letter:</b> Up to 24 ppm; <b>Black (ISO):</b> Up to 24 ppm; <b>Color (ISO):</b> Up to 20 ppm; <b>First Page Out Black:</b> As fast as 9 sec; <b>First Page Out Color:</b> As fast as 10 sec; <b>Black (Draft):</b> Up to 39 ppm; <b>Color (Draft):</b> Up to 39 ppm	<b>Media Sizes Custom</b>	Tray 1: 3 x 5 to 8.5 x 14; 5 x 8.3 to 8.5 x 14 in
<b>Print Resolution</b>	<b>Black (best):</b> 1205 x 1200 rendered dpi; <b>Color (best):</b> Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input	<b>Paper Handling</b>	250-sheet input tray; 250-Sheet Multipurpose Tray; Up to 100 sheets with Smart output management; <b>Duplex Options:</b> Automatic (standard); <b>Auto Document Feeder Capacity:</b> Standard, 35 sheets; <b>Envelope Feeder:</b> No; <b>Standard Paper Trays: 2; Input Capacities:</b> Up to 250 sheets standard; Up to 30 envelopes; Up to 50 sheets; Up to 50 sheets labels; Up to 250 sheets legal; <b>Output Capacities:</b> Up to 100 sheets standard; Up to 10 envelopes; Up to 30 cards; Up to 30 sheets labels; Up to 100 sheets legal
<b>Print Technology</b>	HP Thermal Inkjet	<b>What's in the box</b>	<b>1MR78A</b> HP OfficeJet Pro 9020 All-in-One Printer; HP 962 Setup Black Ink Cartridge; HP 962 Setup Cyan Ink Cartridge; HP 962 Setup Magenta Ink Cartridge; HP Setup 962 Yellow Original Ink Cartridge; No CD Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide; HP Extra Warranty Flyer
<b>Printer Drivers Included</b>	HP PCL3 GUI	<b>Replacement Cartridges</b>	HP 962 Black Original Ink Cartridge (~1,000 pages) 3HZ99A; HP 962 Cyan Original Ink Cartridge (~700 pages) 3HZ96A; HP 962 Magenta Original Ink Cartridge (~700 pages) 3HZ97A; HP 962 Yellow Original Ink Cartridge (~700 pages) 3HZ98A; HP 962XL Black Original Ink Cartridge (2,000 pages) 3JA03A; HP 962XL Cyan Original Ink Cartridge (1,600 pages) 3JA00A; HP 962XL Magenta Original Ink Cartridge (1,600 pages) 3JA01A; HP 962XL Yellow Original Ink Cartridge (1,600 pages) 3JA02A; HP 966XL Black Original Ink Cartridge (3,000 pages) 3JA04A. Actual yield varies considerably based on content of printed pages and other factors. For details see <a href="http://www.hp.com/go/learnaboutsupplies">http://www.hp.com/go/learnaboutsupplies</a>
<b>Print Cartridges Number</b>	4 (1 each black, cyan, magenta, yellow)	<b>Product Dimensions<sup>1</sup></b>	<b>W x D x H:</b> 17.20 x 15.60 x 12.53 in; <b>Maximum:</b> 17.20 x 21.54 x 12.53 in
<b>Borderless Printing</b>	Yes, on photo and brochure paper only, up to 8.5 x 11 in (US letter), 210 x 297 mm (A4)	<b>Product Weight<sup>2</sup></b>	26.44 lb
<b>Standard Print languages</b>	HP PCL3 GUI	<b>Warranty Features</b>	Two-year limited hardware warranty and Next Business Day Exchange; For more info please visit us at <a href="http://www.hp.com/go/extendmywarranty">www.hp.com/go/extendmywarranty</a>
<b>Printer Smart Software Features</b>	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On	<b>Energy Efficiency Compliance</b>	ENERGY STAR <sup>®</sup> qualified
<b>Printer Management</b>	Embedded Web Server	<b>Control Panel</b>	2.65" (6.75 cm) touchscreen control panel with CGD (color graphic display); 3 buttons: (home, help, back)
<b>Scan Type / Technology</b>	Easy slide-off glass, ADF / Contact Image Sensor (CIS)	<b>Display Description</b>	2.65 in (6.75 cm) Touchscreen CGD (color graphics)
<b>Scan Resolution</b>	<b>Hardware:</b> Up to 1200 x 1200 dpi; <b>Optical:</b> Up to 1200 dpi	<b>Software Included</b>	HP Printer Software, Shop for Supplies Online
<b>Scan File Format</b>	JPG, BMR, TIFF, PDF, RTF, TXT, PNG	<b>Compatible Operating Systems</b>	Windows 10, 8.1, 8, 7, Windows Server 2008 R2 64-bit, Windows Server 2008 R2 64-bit (SP1), Windows Server 2012 64-bit, Windows Server 2012 R2 64-bit, Windows Server 2016
<b>Scan Input Modes</b>	Front-panel scan, copy, fax; Software; Mobile apps	<b>Compatible Network Operating Systems</b>	Windows 10, 8.1, 8, 7; 32-bit or 64-bit, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer. 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer 8. Any Intel Pentium III, Celeron or 233 MHz compatible processor, 850 MB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer 8; Linux (For more information, see <a href="http://hplipopensource.com/hplip-web/index.html">http://hplipopensource.com/hplip-web/index.html</a> )
<b>Scan Size</b>	<b>ADF:</b> 8.5 x 14 in Maximum; 5 x 5 in Minimum <b>Flatbed:</b> 8.5 x 11.7 in	<b>Minimum System Requirements</b>	<b>PC:</b> Windows 10, 8.1, 8, 7: 1 GHz 32-bit (x86) or 64-bit (x64) processor, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer; <b>MAC:</b> OS X v10.11 El Capitan; macOS Sierra v10.12 (previously OS X); macOS High Sierra v10.13 macOS Mojave v10.14; 1.5 GB HD; internet; USB
<b>Scan Speed</b>	Up to 15 ipm (200 ppi, b&w); Up to 8 ipm (200 ppi, color)	<b>Power<sup>3</sup></b>	<b>Power Supply Type:</b> Internal (Built-in) Universal Power Supply; <b>Power Requirements:</b> Input voltage: 100 to 240 VAC (+/- 10%), 50/60 Hz; <b>Power Consumption:</b> 0.13 watts (Manual-Off), 5.80 watts (Ready), 1.22 watts (Sleep)
<b>Scanner Advanced Features</b>	OCR (Optical Character Recognition); Smart Taks shortcuts: 1-click customizable scan to cloud destinations, email, and print, create editable, searchable documents by scanning from phone or printer; Smart Tasks destinations: Dropbox, Google Drive, One drive, email recipients, print	<b>Acoustics</b>	<b>Acoustic Power Emissions:</b> 7.0 B(A) (printing at 21 ppm)
<b>Bit depth / Grayscale levels</b>	24-bit / 256	<b>Operating Environment</b>	<b>Operating Temperature Range:</b> 41 to 104°F; <b>Recommended Operating Temperature:</b> 59 to 90°F; <b>Storage Temperature Range:</b> -40 to 140°F; <b>Operating Humidity Range:</b> 20 to 80% RH; <b>Recommended Humidity Operating Range:</b> 25 to 75% RH
<b>Digital Sending Standard Features</b>	Scan-to E-mail; Scan to network folder; Scan to SharePoint; Scan to thumb drive	<b>Security Management</b>	SSL/TLS (HTTPS); IPP over TLS; WPA2-Enterprise wired; 802.1x wireless authentication (EAP-TLS, LEAP, and PEAP); Pre-Shared Key Authentication for Wireless (PSK); Firewall; Certificates Configuration, Control panel lock; Password protect EWS; Unused protocol and service disablement; Syslog; Signed firmware; Administrator settings; Secure boot with self healing; Automatic firmware update; Secure WiFi direct; Encrypted customer data; Secure Erase; Secure Digital send; Certificates Management;
<b>Copy Speed</b>	<b>Black (ISO):</b> Up to 23 cpm; <b>Color (ISO):</b> Up to 17 cpm; <b>Black (Draft):</b> Up to 39 cpm; <b>Color (Draft):</b> Up to 39 cpm	<b>Learn more at</b>	<b>hp.com</b>
<b>Copy Resolution</b>	<b>Black (text and graphics):</b> Up to 600 dpi; Up to 600 dpi; <b>Color (text and graphics):</b> Up to 600 dpi		
<b>Maximum Number Of Copies</b>	Up to 99 copies		
<b>Copier Resize</b>	25 to 400%		
<b>Copier Settings</b>	Copies; Two-Sided; Lighter/Darker; HP Copy Fix; ID Copy; Resize; Quality; Paper Size; Paper Type; Collate; Margin Shift; Crop; Copy Preview; Tray Select; Enhancements		
<b>Fax Speed</b>	<b>Up to:</b> 4 sec per page; <b>Letter:</b> 4 sec per page		
<b>Fax Resolution</b>	<b>Black (best):</b> Up to 300 x 300 dpi; <b>Color (best):</b> 200 x 200 dpi; <b>Black (standard):</b> 203 x 98 dpi; <b>Color (standard):</b> 200 x 200 dpi		
<b>Fax Smart Software Features</b>	Digital Fax - Fax to PC is available with Windows (Please use: Visit <a href="http://www.hp.com/support">http://www.hp.com/support</a> to download the latest software.)		
<b>Fax Features</b>	<b>Fax Memory:</b> Up to 100 pages; <b>Auto Fax Reduction Supported:</b> Yes; <b>Auto-Redialing:</b> Yes; <b>Fax Delayed Sending:</b> Yes; <b>Distinctive Ring Detection Supported:</b> Yes; <b>Fax Forwarding Supported:</b> Yes; <b>Fax Polling Supported:</b> No; <b>Fax Telephone Mode Supported:</b> No; <b>Junk Barrier Supported:</b> Yes, requires Caller ID; <b>Maximum Speed Dialing Numbers:</b> Up to 99; <b>PC Interface Supported:</b> Yes, HP Software support provided; <b>Remote Retrieval Capability Supported:</b> No; <b>Telephone Handset Supported:</b> No		
<b>Standard Connectivity</b>	1 USB 2.0; 1 Host USB (print from JPEG, TIFF, DPOF 1.1, Exif 2.3, PNG); 1 Ethernet; 1 Wireless 802.11b/g/n; 2 RJ-11 modem ports		
<b>Network Capabilities</b>	Yes, via built-in Ethernet, wireless 802.11b/g/n		
<b>Wireless Capability</b>	Yes		
<b>Mobile Printing Capability<sup>4</sup></b>	Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified; HP Smart		
<b>Memory</b>	<b>Standard:</b> 512 MB; <b>Maximum:</b> 512 MB		
<b>Processor Speed</b>	1.2 GHz		
<b>Duty Cycle<sup>7</sup></b>	<b>Monthly, letter:</b> Up to 30,000 pages		
<b>Recommended Monthly Page Volume</b>	Up to 2,000 pages		
<b>Media Types Supported</b>	Plain Paper, HP Photo Papers, HP Matte Brochure or Professional Paper, HP Matte Presentation Paper, HP Glossy Brochure or Professional Paper, Other Photo Inkjet Papers, Other Matte Inkjet Papers, Other Glossy Inkjet Papers, Thick Plain Paper, Light/Recycled Plain Paper, HP Tri-fold Brochure Paper, Glossy		
<b>Media Weight Supported</b>	16 to 28 lb (plain paper); 60 to 75 lb (photo); 20 to 24 lb (envelope); 90 to 110 lb (card)		

<sup>1</sup> Dimensions vary as per configuration <sup>2</sup> Weight varies as per configuration <sup>3</sup> Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. <sup>4</sup> Wireless performance is dependent upon physical environment and distance from the access point. Wireless operations are compatible with 2.4 GHz routers only, excludes wireless direct. Wireless direct may require driver or apps be installed and connected on wireless-enabled mobile device or PC. Wireless functionality may vary by computer and mobile operating systems, see <http://hpconnected.com>. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary. AirPrint supports OS X v10.11 El Capitan and devices running iOS 4.2 or later and requires the printer be connected to the same network as your OS X or iOS device. AirPrint, the AirPrint Logo, iPad, iPhone, and iPod touch are trademarks of Apple® Inc. Windows is a trademark of the Microsoft group of companies. <sup>5</sup> Speed specifications have been updated to reflect current industry testing methods. <sup>6</sup> Either after first page or after first set of ISO test pages. For details see <http://www.hp.com/go/printerclaims> <sup>7</sup> HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement <sup>8</sup> For more information about page yields for replacement cartridges see <http://hp.com/go/learnaboutsupplies> for setup cartridges click on Setup supplies link on the same page.

