

HP LaserJet Pro M404dw (W1A56A)



The HP LaserJet Pro M404 printer—focus your time where it's most effective—growing your business

Winning in business means working smarter. The HP LaserJet Pro M404 printer is designed to let you focus your time where it's most effective—helping to grow your business and staying ahead of the competition.



Built to keep you—and your business—moving forward

Help decrease the amount of paper used in the office by printing on both sides of the page.

Best -in-class security-detect and stop attacks[6]

A suite of embedded security features help protect your printer from being an entry point for attacks.[6]

Simply designed to uncomplicate your day

Set up this printer fast and easily manage device settings to help increase overall printing efficiency.

Featuring

Wi-Fi-Dual band

Enhanced security

Bluetooth Low-Energy for HP Roam

Energy efficient

Specifications

Print Resolution Technologies	HP FastRes1200, HP ProRes1200, Economode
Print quality black (best)	Fine Lines (1200 x 1200 dpi)
Print speed black (ISO, A4)	Up to 38 ppm
Print speed black (ISO, letter)	Up to 40 ppm
Print speed	Print speeds up to 38/40 ppm (A4/Ltr).
Functions	Print
Duplex printing	Automatic (default)
Duty cycle (monthly, A4)	Up to 80,000 pages
Duty cycle (monthly, letter)	Up to 80,000 pages ^[10]
Printer smart software features	Apple AirPrint™, Mopria certified, Google Cloud Print 2.0, Wi-Fi Direct printing, ROAM enabled for easy printing, HP ePrint, HP Auto-On/Auto-Off Technology, Job Storage with PIN printing, N-up printing, collation
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology
Replacement cartridges	AMS: For distribution and use in North America and Latin America only: HP 58A Black LaserJet Toner Cartridge (~3,000 pages), CF258A; HP 58X Black LaserJet Toner Cartridge (~10,000 pages), CF258X; EMEA: For distribution and use in Europe, Middle East, Russia, CIS, and Africa only: HP 59A Black LaserJet Toner Cartridge (~3,000 pages), CF259A; HP 59X Black LaserJet Toner Cartridge (~10,000 pages), CF259X; APJ: For distribution and use only in Asia Pacific - excluding China (PRC) and India: HP 76A Black LaserJet Toner Cartridge (~3,000 pages), CF276A; HP 76X Black LaserJet Toner Cartridge (~10,000 pages), CF276X ^[3]
Supplies feature	HP JetIntelligence Cartridge
Connectivity, standard	1 Hi-Speed USB 2.0; 1 host USB at rear side; Gigabit Ethernet 10/100/1000BASE-T network; 802.11b/g/n / 2.4 / 5 GHz Wi-Fi radio
Network capabilities	Built-in 10/100/1000Base-TX Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1X
Wireless capability	Yes, built-in dual-band Wi-Fi; Authentication via WEP, WPA/WPA2, WPA Enterprise; Encryption via AES or TKIP; WPS; Wi-Fi Direct; Bluetooth Low-Energy
Mobile printing capability	Apple AirPrint™; Google Cloud Print™; HP ePrint; HP Smart App; Mobile Apps; Mopria™ Certified; ROAM capable for easy printing; Wi-Fi® Direct printing
Network protocols, supported	TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, HP ePrint, Apple AirPrint™, Google Cloud Print 2.0, Mopria, IPP Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Statefull via DHCPv6), SSL Security and Certificate management; Management: SNMPv1, SNMPv2, SNMPv3, HTTP/HTTPS, Syslog, FTP FW Download
Software included	No software solutions are included in the Box, Download software at http://123.hp.com/laserjet or http://hp.com
Compatible Operating Systems	Windows Client OS (32/64 bit), Win10, Win8.1, Win 8 Basic, Win8 Pro, Win8 Enterprise, Win8 Enterprise N, Win7 Starter Edition SP1, UPD Win7 Ultimate, Mobile OS, iOS, Android, Mac, Apple® macOS Sierra v10.12, Apple® macOS High Sierra v10.13, Apple® macOS Mojave v10.14, Discrete PCL6 Printer Driver, For more information on the supported operating systems go to http://support.hp.com , Enter your product name and search, Click on User Guides and enter your product name and search for User Guide, Search for your (Product Name) User Guide, Search for the Supported Operating Systems section, UPD PCL6 / PS Printer Drivers, Supported Operating systems, For more information on the supported operating systems see http://www.hp.com/go/upd
Environmental	Mercury-free
ENERGY STAR® certified	Yes
Energy efficiency	EPEAT® Silver; CECP; ENERGY STAR® qualified; Blue Angel RAL-UZ 205 ^[13]
Blue Angel compliant	Yes, Blue Angel RAL-UZ 205
Display area (imperial)	1.79 x 0.53 in
Display area (metric)	4.55 x 1.35 cm
Display	2-line backlit LCD graphic display
Minimum dimensions (W x D x H)	381 x 357 x 216 mm (Without trays and covers not extended)
Minimum dimensions (W x D x H)	15 x 14.06 x 8.5 in (Without trays and covers not extended)
Weight	8.56 kg
Weight	18.87 lb
Power consumption	495 watts (active printing), 5.5 watts (ready), 0.5 watts (sleep), 0.5 watts (Auto Off/Wake on LAN, enabled at shipment), 0.05 watts (Auto-off/Manual-on), 0.05 (Manual Off) ^[2]

Power supply type	Internal (built-in) Power Supply
What's in the box	HP LaserJet Pro M404dw; Preinstalled HP Black LaserJet Toner Cartridge (59A for EMEA, 58A for AMS, 76A for AP, yield ~3,000 pages); Getting Started Guide; Support Flyer; Warranty Guide; Regulatory Flyer; Power cord; USB cable ^[14]
Services (Care Pack)	UB9T8E - HP 3y NBD LJ Pro M404 M405 M304 M305 SVC; UB9T9E - HP 4y NBD LJ Pro M404 M405 M304 M305 SVC; UB9U0E - HP 5y NBD LJ Pro M404 M405 M304 M305 SVC; UC0Q4E - HP3y4h9x5 LJ Pro M404 M405 M304 M305 SVC; UC0Q5E - HP4y4h9x5 LJ Pro M404 M405 M304 M305 SVC; UC0Q6E - HP5y4h9x5 LJ Pro M404 M405 M304 M305 SVC; UB9U1E - HP 3yNBDExchg LJPro M404M405M304M305 SVC; UB9U2E - HP 3y RTD LJ Pro M404 M405 M304 M305 SVC; UB9U3PE - HP 1yPWNBD LJPro M404 M405 M304 M305 SVC; UB9U4PE - HP 2yPWNBD LJPro M404 M405 M304 M305 SVC; UC0Q7PE - HP1yPW4h9x5LJPro M404 M405 M304 M305 SVC; UB9U5PE - HP1yPWNBDExchg LJProM404M405M304M305 SVC; UB9U6PE - HP 1yPWRTD LJPro M404 M405 M304 M305 SVC
Warranty	One-year Bench/Depot Repair warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 4E; wty ID A033)

Accessories and services

No Recommended Accessories and Services

Messaging Footnotes

[6] Based on HP review of 2019 published security features of competitive in-class printers. Only HP offers a combination of security features that can monitor to detect and automatically stop an attack then self-validate software integrity in a reboot. For a list of printers, visit <http://www.hp.com/go/PrintersThatProtect>. For more information: <http://www.hp.com/go/printersecurityclaims>

Technical Specifications Footnotes

[2] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device.

[3] Toner cartridges designed for distribution and use within a designated region only; will not work outside of designated region.

[10] Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups.

[13] EPEAT® registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

[14] In box cartridge yields 3,000 black pages based on ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see: <http://www.hp.com/go/learnaboutsupplies>. Pages may vary based on customer printing conditions and usage.

