

HP Color LaserJet Enterprise M751 dn (T3U44A)



Count on productivity, premium quality, maximum uptime, and the strongest security[1]

HP LaserJet printers power office productivity with a smart, streamlined design that's reliable and hassle-free. Count on premium quality, maximum uptime, and the strongest security[1]—all intended to drive successful organizations forward.



Professional color printing

Print premium, professional-quality documents with vivid color images and graphics.

Minimal interruptions. Maximum productivity.

Change the toner and drum in seconds. Both are easily accessible and come already installed out of the box.

The world's most secure printing[1]

Each printer in your fleet checks its operating code and repairs itself from attacks.

Featuring

Premium color using Enhanced print mode

Original HP toner and drums with JetIntelligence—and HP ColorSphere 3

Wide range of paper-handling accessories

Fast first-page printing with first page out as fast as 5.7 seconds

Fast, easy supplies replacement

Minimal maintenance with long-life supplies

Specifications

Print Resolution Technologies	HP ImageREt 4800, Enhanced (600x600 dpi), Fine Lines (1200x1200 dpi), Quickview (300x300 dpi)
Print quality black (best)	Up to 1200 x 1200 dpi
Print quality color (best)	Up to 1200 x 1200 dpi
Print speed black (ISO, A4)	Up to 41 ppm
Print speed black (ISO, letter)	Up to 40 ppm
Print Speed Color (ISO)	Up to 41 ppm
Print speed color (ISO)	Up to 40 ppm
Print speed	Print speed up to 40 ppm (black) and 40 ppm (color)
Functions	Print
Duplex printing	Automatic (standard)
Duty cycle (monthly, A4)	Up to 150,000 pages
Duty cycle (monthly, letter)	Up to 150,000 pages ^[9]
Printer smart software features	Print preview, duplex printing, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, easy-access USB
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology
Replacement cartridges	HP 658A Black LaserJet Toner Cartridge (~7,000 pages); HP 658A Cyan LaserJet Toner Cartridge (~6,000 pages); HP 658A Magenta LaserJet Toner Cartridge (~6,000 pages); HP 658A Yellow LaserJet Toner Cartridge (~6,000 pages); HP 658X Black LaserJet Toner Cartridge (~33,000 pages); HP 658X Cyan LaserJet Toner Cartridge (~28,000 pages); HP 658X Magenta LaserJet Toner Cartridge (~28,000 pages); HP 658X Yellow LaserJet Toner Cartridge (~28,000 pages); HP 660A Original LaserJet Imaging Drum (~65,000 pages, universal for all 4 colors) ^[6]
Supplies feature	HP JetIntelligence Cartridge
Connectivity, standard	1 Hi-Speed Device USB 2.0; 2 Hi-Speed USB 2.0 rear host ports; 1 walkup USB 2.0 host port; 1 Gigabit/Fast Ethernet 10/100/1000 Base-TX network port; 1 Hardware Integration Pocket 2nd generation (HIP2)
Connectivity, optional	HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A, (Dual band Wireless Station and Wi-Fi Direct functionality); HP Jetdirect 2900nw Print Server J8031A (Dual band Wireless Station)
Network capabilities	Yes, via HP Jetdirect Ethernet embedded print server (standard) supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); 802.11b/g/n wireless networking (optional)
Wireless capability	Optional, enabled with purchase of a wireless hardware accessory: HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A, (Dual band Wireless Station and Wi-Fi Direct functionality); HP Jetdirect 2900nw Print Server J8031A (Dual band Wireless Station)
Mobile printing capability	HP ePrint; Apple AirPrint™; Mopria™ Certified; Google Cloud Print™; HP Roam
Network protocols, supported	IPv4/IPv6: Apple Bonjour Compatible (Mac OS v10.2.4 or higher), SNMPv1/v2c/v3, HTTP, HTTPS, FTP, TFTP, Port 9100, LPD, WS Discovery, IPP, Secure-IPP, IPsec/Firewall; IPv6: DHCPv6, MLDv1, ICMPv6; IPv4: Auto-IP, SLP, Telnet, IGMPv2, BOOTP/DHCP, WINS, IP Direct Mode, WS Print
Software included	No software solutions are included in the Box, only on http://hp.com , http://123.hp.com ;
Compatible Operating Systems	Windows Client OS (32/64 bit), Windows 10, Windows 8.1, Windows 8 Basic, Windows 8 Pro, Windows 8 Enterprise, Windows 8 Enterprise N, Windows 7 Starter Edition SP1, UPD Windows 7 Ultimate, Mobile OS, iOS, Android, Mac, Apple® macOS Sierra v10.12, Apple® macOS High Sierra v10.13, Apple® macOS Mojave v10.14, Discrete PCL6 Printer Driver, For more information on the supported operating systems go to http://support.hp.com , Enter your product name and search, Click on User Guides and enter your product name and search for User Guide, Search for your (Product Name) - User Guide, Search for the Supported Operating Systems section, UPD PCL6 / PS Printer Drivers, Supported Operating systems, For more information on the supported operating systems see www.hp.com/go/upd ^[11]
Environmental	Mercury free
Energy star certified	Yes
Energy efficiency	ENERGY STAR® qualified; EPEAT® Silver; CECP ^[12]
Blue Angel compliant	Yes, Blue Angel DE-UZ 205—only ensured when using Original HP supplies
Display area (imperial)	2.7 in
Display area (metric)	6.86 cm
Display	2.7-in (6.86 cm) QVGA LCD (color graphics) rotating (adjustable angle) display with 24-key pad
Minimum dimensions (W x D x H)	556 x 589 x 399 mm (Without paper trays extended)
Minimum dimensions (W x D x H)	21.9 x 23.2 x 15.7 in (Without paper trays extended)

Weight	45.1 kg ^[3] (With print cartridges)
Weight	99.4 lb (With print cartridges)
Power consumption	870 watts (max. printing), 850 watts (typical printing) 48 watts (Ready), 0.6 watts (Sleep), 0.6 watts (HP Auto-Off/Auto On), 0.08 watts (Auto-Off), 0.08 watts (Off) ^[4]
Power supply type	Built-in 115V or 220V Power Supply
What's in the box	HP Color LaserJet Enterprise M751dn printer; Four preinstalled HP LaserJet toner cartridges; Four preinstalled HP Original LaserJet Imaging Drums (~65,000 pages each color); Guide (Getting started Guide); Power cord ^[1,6]
Services (Care Pack)	UB5C3E - HP 3y NBD w/DMR CLJ M751 SVC; UB5C4E - HP 4y NBD w/DMR CLJ M751 SVC; UB5C5E - HP 5y NBD w/DMR CLJ M751 SVC; UB5C6E - HP 3y 4h 9x5 w/DMR CLJ M751 SVC; UB5C7E - HP 4y 4h 9x5 w/DMR CLJ M751 SVC; UB5C8E - HP 5y 4h 9x5 w/DMR CLJ M751 SVC; UB5C9E - HP 3y ChnlPartsOnly CLJ M751 SVC; UB5D0E - HP 4y ChnlPartsOnly CLJ M751 SVC; UB5D1E - HP 5y ChnlPartsOnly CLJ M751 SVC; UB5D2PE - HP 1y PW NBD w/DMR CLJ M751 SVC; UB6X3PE - HP 2y PW NBD w/DMR CLJ M751 SVC; UB6X4PE - HP 1y PW w/DMR 4h 9x5 CLJ M751 SVC; UB6X5PE - HP 2y PW w/DMR 4h 9x5 CLJ M751 SVC; UB6X6PE - HP 1y PW ChnlPartsOnly CLJ M751 SVC; UB6X7PE - HP 2y PW ChnlPartsOnly CLJ M751 SVC
Warranty	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to hp.com/support to learn about HP award winning service and support options in your region. (Warranty Code 4G; Warranty ID A001)

Accessories and services

No Recommended Accessories and Services

Messaging Footnotes

[1] Based on HP review of 2018 published security features of competitive in-class printers. Only HP offers a combination of security features that can monitor to detect and automatically stop an attack then self-validate software integrity in a reboot. For a list of printers, visit <http://hp.com/go/PrintersThatProtect>. For more information: <http://hp.com/go/printersecurityclaims>

Technical Specifications Footnotes

[1] Standard cartridges included; yields 7,000 black and 6,000 color composite (C/M/Y) pages. Drums included; yields 65,000 black and color pages.

[3] With print cartridges.

[4] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device.

[6] Average black declared yields based on ISO/IEC 19752 and continuous printing. Average color composite (C/M/Y) declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/learnaboutsupplies>.

[9] Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups.

[11] Solution software available on 123.hp.com

[12] EPEAT® registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

