

# Receipt Printers

# K3

The K3 is the ideal product to print receipts, coupons, kitchen orders, invoices, or tickets. It is elegantly designed and conceived to suit any and all environments: be it high-end retail, fine dining, or warehousing. The K3 is equipped with the highest quality components allowing it to achieve unparalleled print speeds of up to 13" per second, while still maintaining industry leading product reliability.

Built in USB, Serial, and Ethernet along with optional Wi-Fi and Bluetooth ensure the proper interface for any installation. Support for larger than standard paper rolls greatly reduces the number paper swaps, resulting in less interruptions and savings on labor throughout the life of the printer.



**FAST PRINTING**

Output receipts at a rate of up to 13 inches per second (350mm) saving time with every transaction.



**COMPATIBILITY**

With the ability to connect via USB, Serial, or Ethernet right out of the box, the K3 is ready for any installation.



**WALL MOUNTABLE**

Convenient mounting capabilities allow for optimal printer placement.



**EASY PAPER LOADING**

An auto opening door and easy drop in loading makes roll changes a breeze.



**EXTRA LARGE PAPER ROLL**

A large then standard paper roll greatly increases time between roll changes saving both time and money.



<b>PART NUMBER</b>	911HM010800733	911HM010300B33
<b>INTERFACE SPECIFICATIONS</b>		
Interface Details	Serial RS232C/USB 2.0/Ethernet	Serial RS232C/USB 2.0/Ethernet/Wifi/Bluetooth
Emulation	ESC/POS Command Compatible, OPOS	
Print Method	Direct Thermal	
Printing Speed	13"/sec (350mm/sec)	
Print Resolution	200 DPI	
Printing Direction	Unidirectional with Friction Feed	
Sensors	Cover Open, Paper End	
Cash Drawer Port	1 Port, (24V/12V)	
Print Head Reliability	124 miles (200Km)	
Auto Cutter	2,000,000 cuts	

<b>PAPER</b>	
Type	Thermal Paper
Width	2.2" (58mm) - 3.15" (80mm)
Thickness	0.0024" (0.063mm) - 0.0033" (0.085mm)
Roll Diameter	Max 3.93" (100mm)
Roll Core Inner Diameter	25mm (+/- 1mm)
Paper Weight	55 to 90 g/m <sup>2</sup>
Barcodes Supported	All standard 1D and 2D barcodes

<b>AUTOCUTTER</b>	
Type	JamFree auto-retracting guillotine
Life	2,00,000 Cuts
Cutting Method	Full/Partial Cut

<b>PHYSICAL</b>	
Dimension (WxDxH)	5.5" x 8" x 5.8" (140mm x 206mm x 148mm)
Weight	4.3lbs (1.98kg)
Color	Black
Electrical	100-240 VAC 50/60 Hz (input) 24 VDC/1.5 A (output)

<b>ENVIRONMENTAL</b>	
Temperature	32°F to 122°F (0°C to 50°C) operating
Humidity	10% to 85% non condensing
Warranty	5-year warranty with free *2-day Advance Exchange Service
Certifications	UL, CE, FCC, NOM
Operating System	Win 7, Win 8, Win 10, OPOS drivers, OSX, iOS, Android

<b>WARRANTY EXTENSIONS AND UPGRADES</b>	
ZOE-CRW3	*3-Year Next Business Day Exchange
ZOE-CRW5	*5-Year Next Business Day Exchange

\*Available in the USA and Canada