

ThinkCentre Tiny-In-One 27 10YFRAR1US

Product
ThinkCentre Tiny-in-One 27

Color Gamut
99% sRGB

Region
US

View Angle (H / V)
178 / 178

Machine Type
10YF

Stand
Adjustable Stand

Color
Black

Power Consumption (Typical / Maximum)
37W / 57W

Display Size
27"

Power Supply
170W 88% Adapter

Multi-touch
None

Warranty
3-year

Resolution
2560x1440

Ann Date (mm/yy)
02/19

Aspect Ratio
16:9

Pixel Pitch
0.2331 mm

Dot / Pixel Per Inch
109 dpi

Notes:

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

Brightness
350 nits

Contrast Ratio
1000:1

Pixel Response Time
14ms (default), over drive to 4ms, 6ms



WWW.LENOVO.COM

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2019. All rights reserved.



Lenovo

Form factor	Tiny-in-One, offers a full All-In-One experience when optional Tiny slots into the back of TIO, clean cabling and effortless setup	<div style="border: 1px solid #ccc; padding: 10px; width: fit-content; margin: 0 auto;"> <div style="text-align: center;"> <p>Mechanical</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 33.33%;"></td><td style="width: 33.33%; text-align: center;">TIO without stand</td><td style="width: 33.33%; text-align: center;">TIO with stand</td></tr> <tr> <td>Dimensions (W x D x H mm / inch)</td><td>614.0 x 73.89 x 413.1 / 24.17 x 2.91 x 16.26</td><td>614.0 x 329.0 x 444.25 - 554.25 / 24.17 x 12.95 x 17.49 - 21.82</td></tr> <tr> <td>Weight (Approx.)</td><td>4.91 kg / 10.82 lb</td><td>7.95 kg / 17.53 lb</td></tr> </table> <p>Mounting features</p> <p>Adjustable stand</p> <p>Wall or desk mounting using the extend arm or third-party accessories meeting the VESA FPM PMI® (100mm mount)</p> <p><i>Tilt:</i> 35° back, -5° forward; <i>lift:</i> 4.3" (110mm); <i>swivel:</i> +/-45°; <i>Pivot:</i> clockwise -5° to 90°</p> <p>Power supply</p> <p>Power consumption</p> <p>Limited warranty</p> <p>VESA-compliant</p> <p>Ergonomics</p> <p>Emission standards</p> <p>Environmental</p> <p>Windows certifications</p> <p>Ship group</p> <p>Accessories</p> </div> </div>		TIO without stand	TIO with stand	Dimensions (W x D x H mm / inch)	614.0 x 73.89 x 413.1 / 24.17 x 2.91 x 16.26	614.0 x 329.0 x 444.25 - 554.25 / 24.17 x 12.95 x 17.49 - 21.82	Weight (Approx.)	4.91 kg / 10.82 lb	7.95 kg / 17.53 lb			
	TIO without stand	TIO with stand												
Dimensions (W x D x H mm / inch)	614.0 x 73.89 x 413.1 / 24.17 x 2.91 x 16.26	614.0 x 329.0 x 444.25 - 554.25 / 24.17 x 12.95 x 17.49 - 21.82												
Weight (Approx.)	4.91 kg / 10.82 lb	7.95 kg / 17.53 lb												
Compatible Tiny:	ThinkCentre Tiny, ThinkCentre Nano, and ThinkStation Tiny													
Panel	TFT-LCD, In-Plane Switching technology**, White LED backlight													
Viewable image size	**Notes: In-Plane Switching may refer to IPS, PLS, ADS, AHVA, and AA													
Max view area (W x H)	27" (685.8mm) diagonal													
Bezel Width	Top / Side: 2mm, Bottom: 23.3mm													
Native resolution	2560x1440													
Multi-touch	None													
Aspect ratio	16:9													
Pixel pitch (mm)	0.2331mm													
Dot/Pixel per Inch	109 dpi	<div style="border: 1px solid #ccc; padding: 10px; width: fit-content; margin: 0 auto;"> <div style="text-align: center;"> <p>ThinkCentre Tiny-in-One 27 Compatible Matrix</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 25%;">Model</td><td style="width: 25%; text-align: center;">P320 / P330 / M920(x) / M720 / M910(x) / M710 / M900(x) / M700 / M600 / M715 / M83 / M53 Tiny</td><td style="width: 25%; text-align: center;">M93/p Tiny, M73 Tiny</td><td style="width: 25%; text-align: center;">Chromebox</td></tr> <tr> <td>Turn on TIO and Tiny together via Alt + P on USB KB</td><td style="text-align: center;">All models</td><td style="text-align: center;">All models</td><td style="text-align: center;">Not support</td></tr> <tr> <td>Turn on TIO and Tiny together via TIO Power Button</td><td style="text-align: center;">All models</td><td style="text-align: center;">TIO models</td><td style="text-align: center;">All models</td></tr> </table> </div> </div>	Model	P320 / P330 / M920(x) / M720 / M910(x) / M710 / M900(x) / M700 / M600 / M715 / M83 / M53 Tiny	M93/p Tiny, M73 Tiny	Chromebox	Turn on TIO and Tiny together via Alt + P on USB KB	All models	All models	Not support	Turn on TIO and Tiny together via TIO Power Button	All models	TIO models	All models
Model	P320 / P330 / M920(x) / M720 / M910(x) / M710 / M900(x) / M700 / M600 / M715 / M83 / M53 Tiny	M93/p Tiny, M73 Tiny	Chromebox											
Turn on TIO and Tiny together via Alt + P on USB KB	All models	All models	Not support											
Turn on TIO and Tiny together via TIO Power Button	All models	TIO models	All models											
Brightness	350 nits or cd/m ² (typical)													
Contrast ratio	1000:1 (typical)													
Pixel response time	14ms (default), over drive to 4ms, 6ms													
Color gamut	99% sRGB													
Anti-glare	Yes (25%)													
Viewing angle at 10:1 CR	178° (+/- 89°) horizontal, 178° (+/- 89°) vertical													
Preset resolutions	640x350 @ 70Hz 640x480 @ 60Hz, 66Hz, 72Hz, 75Hz 720x400 @ 70Hz 800x600 @ 60Hz, 72Hz, 75Hz 1024x768 @ 60Hz, 70Hz, 75Hz 1152x864 @ 75Hz 1280x768 @ 60Hz 1280x800 @ 60Hz 1280x1024 @ 60Hz, 72Hz, 75Hz 1366x768 @ 60Hz 1440x900 @ 60Hz, 75Hz 1600x1200 @ 60Hz, 70Hz, 75Hz 1680x1050 @ 60Hz 1920x1080 @ 60Hz 2560x1440 @ 60Hz													
Presets / user settings	Presets: 27; user settings: 25													
On screen display	On screen display with digital user controls (8 languages)													
Control features	F1ont: Exit button, Left / Mode-switching button (TIO / monitor mode), Right / Brightness button, Enter / Menu button, Power button Bottom: Volume up button, Volume down button													
Tiny-in-One Power On	Pressing Alt + P on keyboard or pressing Power button positioned on TIO can turn on both TIO and Tiny (only some support, see Compatible Matrix)													
Side ports (TIO)	Two USB 3.1 Gen1 (downgrade to USB 2.0 when installing M73 or M53 or connecting USB 2.0 via USB upstream port), one headphone / microphone combo jack <i>Notes:</i> The USB ports are enabled by installing a Tiny or connecting USB upstream port; the audio port is enabled by installing a Tiny or connecting USB upstream, DisplayPort(in), or HDMI(in) port													
Side ports (Tiny)	Side ports offered by the installed Tiny (optional)													
Rear ports	One DisplayPort(in) port, one HDMI(in) port, one USB (Type-B) upstream port, one power connector													
3-in-1 Cable	Undetachable 3-in-1 cable, connecting to the power connector, one USB, and one DisplayPort of the installed Tiny (optional)													
Camera	RGBIR camera with dual microphone, supports Window Hello and Facial Recognition, Think Shutter for Privacy Security, LED indicator													
Internal Speaker	2 watt x2													
Security	Security keyhole for attachment of optional cable lock (Kensington® lock compatible), locks optional Tiny with TIO together, more security features offered by Tiny installed (optional)													

Lenovo

ThinkCentre Tiny-In-One 27

Lenovo

