

Lenovo 14w 81MQ001RUS

Product
Lenovo 14w

Machine Type
81MQ

Region
NA

Country
US

Processor
AMD A6-9220C (2C, 1.8 / 2.7GHz, 1MB)

Graphics
Integrated AMD Radeon R5 Graphics

Memory
4GB Soldered

Display
14" FHD (1920x1080) IPS

Multi-touch
10-point Multi-touch

Storage
128GB SSD

Optical
None

Ethernet
None

WLAN + Bluetooth
11ac, 2x2 + BT4.2

Color
Black

Camera
720p

Microphone
None

Keyboard
Non-backlit

Pen
None

Fingerprint Reader
None

Battery
57Wh

Power Adapter
45W USB-C

Operating System
Windows 10 Home 64

Warranty
1-year, Mail-in

Ann Date (mm/yy)
03/19

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences. <https://www.lenovo.com/hk/en/battery-info>

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>



WWW.LENOVO.COM

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication “as is” without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference. © Lenovo, 2019. All rights reserved.



Lenovo 14w Platform Specifications

Product Specifications Reference (PSREF)

Processor	AMD® A-Series APUs							Camera Audio support	720p HD, fixed focus, array microphone Maxim MAX98357A Dialog DA7219, Stereo speakers, 2Wx 2, combo headphone / microphone jack
	Processor Number	# of Cores	Base Frequency	Max Frequency	L2 Cache	Memory Type	Processor Graphics		
	A6-9220C	2	1.8 GHz	2.7 GHz	1MB	DDR4 1866	Radeon R5		
Graphics	AMD Radeon R5 Graphics in processor							Keyboard	6-row, Anti-pry Key Caps, spill-resistant, optional white LED backlight for US models One-piece touchpad
Chipset	AMD SoC (System on Chip) platform							Security	Power-on password, supervisor password, security keyhole
Memory	4GB or 8GB / 1600MHz DDR4 / soldered to systemboard							Security chip	TPM 2.0
Display	Some: 14.0" (355mm) FHD (1920x1080), anti-glare, LED backlight, 250 nits, 16:9 aspect ratio, IPS Some: 14.0" (355mm) FHD (1920x1080), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio							Fingerprint reader	None
Multi-touch (opt)	Support 10 fingers (IPS model only)							Battery	Integrated Li-ion 57Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W USB Type-C AC adapter
Storage	eMMC 5.1 (embedded Multi Media Card) flash memory or M.2 SSD on board							Max battery life	Up to 12hrs <i>* Battery life varies significantly with settings, usage, & other factors.</i>
Optical	None							AC adapter	45W or 65W USB Type-C AC adapter
Ethernet	None							Preload	Some: Windows 10 Pro in S mode Some: Windows 10 Pro (National Academic License) Some: Windows 10 Home 64 Some: Windows 10 Pro 64
WLAN	QCA 6174A, Wi-Fi 2x2 802.11ac + BT4.2, M.2 card							Limited warranty	<i>One of the following, configurable by model:</i> • 1-year depot repair service • 1-year mail-in repair service
WWAN	None							Mil-Spec test	MIL-STD-810G military certification
Bluetooth™	Bluetooth 4.2 wireless, integrated in Wi-Fi + Bluetooth combo adapter							Environment	EPEAT™ Silver; RoHS-compliant
Dimensions	WxDxH: 12.91" x 8.86" x 0.70"; 328mm x 225mm x 17.7mm								
Weight	1.54 kg (3.39 lb)								
Case color	Mineral Grey								
Case material	PC/ABS plastic								
Media reader	Micro SD								
Ports	One Type-C USB 3.0, two USB 3.0, combo audio jack <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed.</i>								

Note: The specifications above may not be available in all regions.

Lenovo
March 2019



Lenovo 14w

