

DS-2CE12DFT-F

2 MP Outdoor Full Time Color Bullet Camera



- 2 MP High Performance CMOS
- Up to 1920 x 1080 Resolution
- Full Time Color
- 3.6 mm and 6 mm Fixed Lens Options
- 3D DNR, 120dB True WDR
- Up to 130 ft (40 m) White Light Range
- Multiprotocol Output:
TVI/AHD/CVI/CVBS
- Up-the-Coax (HIKVISION-C)
- IP67 Protection

The Hikvision DS-2CE12DFT-F 2 MP Outdoor Full Time Color Bullet Camera provides high definition analog output. TurboHD means that the analog signal can be sent over existing coaxial cable, eliminating the need to run new cables for high definition video.

The ColorVu series of cameras is equipped with a white light that has a range of 130 feet (40 meters).

The 3.6 mm and 6 mm fixed lens options are optimized for viewing angles that fit any situation. 120dB True WDR (Wide Dynamic Range) ensures that ideal images are captured regardless of the lighting conditions.

Available models:
DS-2CE12DFT-F



Specifications

DS-2CE12DFT-F

Camera

Image Sensor	2 MP progressive scan CMOS
Resolution	1920 (H) × 1080 (V)
Frame Rate	1080p @ 30 fps
Minimum Illumination	Color: 0.0005 lux @ (f/1.0, AGC on), 0 lux with white light
Shutter Time	1/30 s to 1/50,000 s
Slow Shutter	Maximum 16x
Lens	3.6 mm and 6 mm fixed lens options
Horizontal Field of View	83.6° (3.6 mm), 52.8° (6 mm)
Lens Mount	M16
Day/Night	Color
Angle Adjustment	Pan: 0° to 360°; tilt: 0° to 180°; rotate: 0° to 360°
Synchronization	Internal synchronization
WDR	120dB

Menu

AGC	Yes
White Balance	Auto/manual
BLC	Yes
Privacy Mask	4 programmable privacy masks
Motion Detection	4 programmable areas
WDR	Yes
Functions	Brightness, sharpness, 3D DNR, mirror, smart light


Interface

Video Output	1 HD analog output
Switch Button	TVI/AHD/CVI/CVBS

General

Operating Conditions	-40° F to 140° F (-40° C to 60° C), humidity: 90% or less (non-condensation)
Power Supply	12 VDC ± 25%
Power Consumption	Maximum 4.2 W
Protection Level	IP67
Material	Metal
White Light Range	Up to 130 ft (40 m)
Communication	Up-the-Coax, protocol: HIKVISION-C (TVI output)
Dimensions	8.78" x 3.04" x 3.25" (223.1 mm x 77.1 mm x 82.6 mm)
Weight	Approximately 0.96 lbs (436 g)

Accessories



Dimensions

