

# HP LaserJet Enterprise M507dng (1PV89A)



## Handle business solutions securely, plus help conserve energy with HP EcoSmart toner

Choose an HP LaserJet Enterprise printer designed to handle business solutions securely and efficiently, and helps conserve energy with HP EcoSmart black toner. Keep up with the demands of growing business with a printer you can rely on.[8]



### **The world's most secure printing[1]**

Each printer in your fleet checks its operating code and repairs itself from attacks.

### **Low costs, low energy use**

Stay productive with reliable cartridges, and help save energy while printing with HP EcoSmart black toner.[8]

### **Your whole fleet. At your control.**

Centralize control of your printing environment with HP Web Jetadmin[4]—and help build business efficiency.

### **Featuring**

Low energy consumption

World's most secure printing [1]

Robust mobility

Enhanced user interface

Enterprise manageability

Enhanced workflows

## Specifications

<b>Print Resolution Technologies</b>	300 dpi, 600 dpi, HP FastRes 1200, HP ProRes 1200
<b>Print quality black (best)</b>	Up to 1200 x 1200 dpi
<b>Print speed black (ISO, A4)</b>	Up to 43 ppm
<b>Print speed black (ISO, letter)</b>	Up to 45 ppm
<b>Print speed</b>	Print speed up to 45 ppm (black)
<b>Functions</b>	Print
<b>Duplex printing</b>	Automatic (standard)
<b>Duty cycle (monthly, A4)</b>	Up to 150,000 pages
<b>Duty cycle (monthly, letter)</b>	Up to 150,000 pages <sup>[8]</sup>
<b>Printer smart software features</b>	Print preview, duplex printing, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, easy-access USB
<b>Energy savings feature technology</b>	HP Auto-On/Auto-Off Technology; Instant-on Technology
<b>Replacement cartridges</b>	HP 89A Black Original LaserJet Toner Cartridge (~5,000 pages) CF289A; HP89X High Yield Black Original LaserJet Toner Cartridge (~10,000 pages) CF289X; HP89Y Extra High Yield Black Original LaserJet Toner Cartridge (~20,000 pages) CF289Y
<b>Supplies feature</b>	HP JetIntelligence Cartridge
<b>Connectivity, standard</b>	1 Hi-Speed Device USB 2.0; 2 Hi-Speed USB 2.0 Host; 1 Gigabit Ethernet; 1 Hardware Integration Pocket
<b>Connectivity, optional</b>	Yes, via HP Jetdirect Ethernet embedded print server (standard) which supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); Optional 802.11a/b/g/n wireless networking and second Ethernet port
<b>Network capabilities</b>	HP Jetdirect 2900nw Print Server J8031A; HP Jetdirect 3000w NFC/Wireless Accessory J8030A; HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A
<b>Wireless capability</b>	Optional, enabled with purchase of a wireless hardware accessory. Single band Wireless Station and Wi-Fi Direct functionality available with HP Jetdirect 3000w NFC/Wireless Accessory J8030A, Dual band Wireless Station and Wi-Fi Direct functionality available with HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A, Dual band Wireless Station functionality available with HP Jetdirect 2900nw Print Server J8031A
<b>Mobile printing capability</b>	Apple AirPrint™; Google Cloud Print™; HP ePrint; Mopria™ Certified; ROAM optional for easy printing
<b>Network protocols, supported</b>	Via built-in networking solution: TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, IPP 2.0, Apple AirPrint™, HP ePrint, FTP Print, Google Cloud Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual, TFTP Config, ARP-Ping), IPv6 (Stateless Link-Local and via Router, Stateful via DHCPv6); Management: SNMPv2/v3, HTTP/HTTPS, Telnet, TFTP Config, Syslog; Security: SNMPv3, SSL Cert Management, IPsec/Firewall, ACL, 802.1x
<b>Software included</b>	No software solutions are included in the Box, only on <a href="http://hp.com">http://hp.com</a> , <a href="http://123.hp.com">http://123.hp.com</a>
<b>Compatible Operating Systems</b>	Windows Client OS (32/64 bit), Win10, Win8.1, Win 8 Basic, Win8 Pro, Win8 Enterprise, Win8 EnterpriseN, Win7 Starter Edition SP1, UPD Win7 Ultimate, Mobile OS, iOS, Android, Mac, Apple® macOS Sierra v10.12, Apple® macOS High Sierra v10.13, Apple® macOS Mojave v10.14, Discrete PCL6 Printer Driver, For more information on the supported operating systems go to <a href="http://support.hp.com">http://support.hp.com</a> , Enter your product name and search, Click on User Guides and enter your product name and search for User Guide, Search for your (Product Name) - User Guide, Search for the Supported Operating Systems section, UPD PCL6 / PS Printer Drivers, Supported Operating systems, For more information on the supported operating systems see <a href="http://www.hp.com/go/upd">http://www.hp.com/go/upd</a>
<b>Environmental</b>	Mercury free
<b>Energy star certified</b>	Yes
<b>Energy efficiency</b>	Blue Angel; CECP; EPEAT® Gold; ENERGY STAR® qualified <sup>[11]</sup>
<b>Blue Angel compliant</b>	No, please refer to the ECI (Ecolabel Comparison Information) document
<b>Display area (imperial)</b>	3.74 x 2.32 in
<b>Display area (metric)</b>	95.04 x 53.86 mm
<b>Display</b>	4.3-in (10.92 cm) Color Graphics Display (CGD) with touchscreen; rotating (adjustable angle)
<b>Minimum dimensions (W x D x H)</b>	418 x 376 x 326 mm
<b>Minimum dimensions (W x D x H)</b>	16.46 x 14.80 x 12.83 in
<b>Weight</b>	12.47 kg (With print cartridges)
<b>Weight</b>	27.7 lb (With print cartridges)

<b>Power consumption</b>	601 (Active Printing) 7.60 (Ready), 2.61 watts (Sleep), 0.06 watts (Auto-Off), 0.06 watts (Off), Auto Off/Wake on LAN 0.73 Watt <sup>[3]</sup>
<b>Power supply type</b>	Built-in 115V or 220V Power Supply
<b>What's in the box</b>	HP LaserJet Enterprise M507dng Printer; HP Original LaserJet Toner Cartridge (~5,000 pages); Regulatory flyer (CD replacement); Unpack Flyer; Installation Guide; Power cord; Warranty Cards; Support flyers/phone number list; USB-8ft cable (APJ region only) <sup>[1]</sup>
<b>Services (Care Pack)</b>	UB6Z2E: HP 3 years Next Business Date w/DMR LaserJet Enterprise M507 SVC; UB6Z3E: HP 4 years Next Business Date w/DMR LaserJet Enterprise M507 SVC; UB6Z4E: HP 5 years Next Business Date w/DMR LaserJet Enterprise M507 SVC; UB6Z5E: HP 3 years 4 hours 9x5 w/DMR LaserJet Enterprise M507 SVC; UB6Z6E: HP 4 years 4 hours 9x5 w/DMR LaserJet Enterprise M507 SVC; UB6Z7E: HP 5 years 4 hours 9x5 w/DMR LaserJet Enterprise M507 SVC; UB7A1E: HP 3 years ChnlPartsOnly LaserJet Enterprise M507 SVC; UB7A2E: HP 4 years ChnlPartsOnly LaserJet Enterprise M507 SVC; UB7A3E: HP 5 years ChnlPartsOnly LaserJet Enterprise M507 SVC; UB7A4PE: HP 1 year PageWide Next Business Date w/DMR LaserJet Enterprise M507 SVC; UB7A5PE: HP 2 years PageWide Next Business Date w/DMR LaserJet Enterprise M507 SVC; UB7A6PE: HP 1 year PageWide w/DMR 4 hours 9x5 LaserJet Enterprise M507 SVC; UB7A7PE: HP 2 years PageWide w/DMR 4 hours 9x5 LaserJet Enterprise M507 SVC; UB7B0PE: HP 1 year PageWide ChnlPartsOnly LaserJet Enterprise M507 SVC; UB7B1PE: HP 2 years PageWide ChnlPartsOnly LaserJet Enterprise M507 SVC
<b>Warranty</b>	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to <a href="http://hp.com/support">hp.com/support</a> to learn about HP award winning service and support options in your region. (wty code 4G; wty ID A001)

## Accessories and services

No Recommended Accessories and Services

## Messaging Footnotes

[1] Based on HP review of 2018 published security features of competitive in-class printers. Only HP offers a combination of security features that can monitor to detect and automatically stop an attack then self-validate software integrity in a reboot. For a list of printers, visit <http://www.hp.com/go/PrintersThatProtect>. For more information: <http://www.hp.com/go/printersecurityclaims>

[4] HP Web Jetadmin is available for download at no additional charge at <http://www.hp.com/go/webjetadmin>

[8] To enable HP Roam, some devices may require firmware to be upgraded and an optional accessory to add Bluetooth® Low Energy (BLE) beaconing capabilities. Subscription may be required. For more information, visit [hp.com/go/roam](http://hp.com/go/roam)

## Technical Specifications Footnotes

[1] In box cartridge yields 5,000 black pages based on ISO/IWC 19752 and continuous printing. Actual pages may vary considerably based on images printed and other factors. For more information, visit: <http://www.hp.com/go/learnaboutsupplies>.

[3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device.

[8] Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups.

[11] EPEAT® registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

---

© Copyright 2019 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ENERGY STAR and the ENERGY STAR logo are registered U.S. marks. Windows is a registered trademark of Microsoft Corporation. AirPrint, iPad, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.

