Lexmark[™] GO•Line[™]

Lexmark MC3224dwe

Small. Dependable. Secure.


Compact and lightweight, the Lexmark MC3224dwe multifunction brings color printing, scanning, copying and touchscreen convenience to small workgroups. It offers color output at up to 24 pages per minute* in a package that fits almost anywhere. There's Wi-Fi to support mobile users and Lexmark full-spectrum security is built in.

Compact color versatility

- Get color output at up to 24 pages per minute*, plus singlesheet scanning.
- Tackle your printing workload with the power of a 1-GHz processor and 512 MB of memory.
- Connect via standard Wi-Fi, ethernet and USB.
- Simplify mobile printing via Lexmark Mobile Print app, as well as Mopria® and AirPrint technologies.
- 2.8-inch (7.2 cm) touch screen offers built-in workflow capabilities like scan to network, scan to email and Lexmark's own Cloud Connector****.

Easy to set up, easy to keep going

- Compact dimensions of 12.1 inches high x 16.2 inches wide x 15.5 inches deep (306.9 mm high x 411.2 mm wide x 394.1 mm deep) helps it fit almost anywhere.
- Unison[™] Toner replacement cartridges deliver up to 1500 pages^{**} of high-quality output.
- Steel frame and lifetime imaging components mean long life and minimal maintenance.



Robust, built-in security

 Lexmark's full-spectrum security architecture helps keep your information safe—on the document, the device, over the network, and everywhere in between

Built for planet earth

- Built-in energy-saving mode goes from sleep to print to sleep with nothing to set.
- Printer is rated EPEAT® Silver*** and is ENERGY STAR® certified.
- Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).



- * Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.
- ** Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See www.lexmark.com/yields for more information.
- *** EPEAT ratings may vary by location. See www.epeat.net for registration status by country.

**** Cloud Connector feature will be available by end of 2019. Devices purchased prior to availability can get this feature via free firmware update at support.lexmark.com/firmware.

Product Specifications	Lexmark MC3224dwe
Printing	
Display	2.8 inch LCD touch panel
Print Speed	Up to: Black: 24 ppm ¹ (Letter) / Color: 24 ppm ¹ (Letter)
Time to First Page	As fast as: Black: 11 seconds / Color: 11 seconds
Print Resolution	Black: 4800 Color Quality, 600 x 600 dpi / Color: 600 x 600 dpi, 4800 Color Quality
Memory / Processor	Standard: 512 MB / Maximum: 512 MB / Dual Core Processor 1 GHz
Hard Disk	Not Available
Recommended Monthly Page Volume	600 - 1500 pages ²
Maximum Monthly Duty Cycle	Up to: 30000 pages per month ³
Copying	
Copy Speed	Up to: Black: 24 cpm ¹ (Letter) / Color: 24 cpm ¹ (Letter)
Time to First Copy	As fast as: Black: 11.2 seconds / Color: 11.2 seconds
Scanning	
Scanner Type	Flatbed scanner
Supplies ⁴	
Laser Cartridge Yields	up to: 1,500 ⁵ -page Black and Color (CMYK) Cartridges
Cartridge(s) Shipping with Product	750 ⁵ -page Black Starter Return Program Toner Cartridge, 500 ⁵ -page Color (CMY) Starter Return Program Toner Cartridge
Paper Handling	
Included Paper Handling	100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input
Paper Input Capacity	Up to: Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 250+1 pages 20 lb or 75 gsm bond
Paper Output Capacity	Up to: Standard: 100 pages 20 lb or 75 gsm bond / Maximum: 100 pages 20 lb or 75 gsm bond
Media Types Supported	Hagaki Card, Paper Labels, Card Stock, Plain Paper, Glossy Paper, Refer to the Paper & Specialty Media Guide
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope
General Information ⁶	
Standard Ports	802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100BaseTX (RJ-45)
Noise Level	Operating: 49 dBA (Print) / 49 dBA (Copy) / 40 dBA (Scan)
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity / Altitude: 0 - 3048 Meters (10,000 Feet) / Temperature: 10 to 32°C (50 to 90°F)
Limited Warranty	See Statement of Limited Warranty: Advanced Exchange, 3-5 Business Day Ground Shipment
Size / Weight	H x W x D: 12.1 x 16.2 x 15.5 in. / 40.2 lb.

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

¹ Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁵ Average continuous cartridge yield is stated number of standard pages as listed. Declared yield value in accordance with ISO/IEC 19798. ⁶ Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/

 $\ensuremath{\mathbb{C}}$ 2019 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Google Cloud Print[™] is a trademark of Google, LLC. Mopria®, the Mopria® Logo[™] and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. All other trademarks are the property of their respective owners. This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (http://www.openssl.org/).

