

# Lexmark C3326dw

## Small. Dependable. Secure.

Enhance small-workgroup productivity with color output up to 26 pages per minute\*, high-yield replacement toner cartridges and connectivity via Wi-Fi, USB and gigabit ethernet—all in the Lexmark C3326dw. Its 1-GHz multi-core processor lets you tackle big jobs, while Lexmark full-spectrum security helps protect your data.



### Compact color power

- ▶ Get color output at up to 26 pages per minute\*.
- ▶ Tackle your printing workload with the power of a 1-GHz processor and 512 MB of memory.
- ▶ Connect via standard Wi-Fi, gigabit ethernet and USB.
- ▶ Simplify mobile printing via Lexmark Mobile Print app, as well as Mopria® and AirPrint technologies.
- ▶ Two-line display lets you configure, interact and monitor vital system information.

### Easy to set up, easy to keep going

- ▶ Compact dimensions of 9.6 inches high x 16.2 inches wide x 15.5 inches deep (243.7 mm high x 411.2 mm wide x 394.1 mm deep) helps it fit almost anywhere.
- ▶ Unison™ Toner replacement cartridges deliver up to 2500 color pages\*\* and 3000 monochrome pages\*\* of high-quality output.
- ▶ Steel frame and lifetime imaging components mean long life and minimal maintenance.

### Robust, built-in security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—on the document, the device, over the network, and everywhere in between.

### Built for planet earth

- ▶ Built-in energy-saving mode goes from sleep to print to sleep with nothing to set.
- ▶ Printer is rated EPEAT® Silver\*\*\* and is ENERGY STAR® certified.
- ▶ Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).



\* Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

\*\* Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See [www.lexmark.com/yields](http://www.lexmark.com/yields) for more information.

\*\*\* EPEAT ratings may vary by location. See [www.epeat.net](http://www.epeat.net) for registration status by country.

| Product Specifications             |                                                                                                                                                                                                    | Lexmark C3326dw |
|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
| Printing                           |                                                                                                                                                                                                    |                 |
| Display                            | 2-line All Points Addressable (APA) monochrome LCD display                                                                                                                                         |                 |
| Print Speed                        | Up to: Black: 26 ppm <sup>1</sup> (Letter) / Color: 26 ppm <sup>1</sup> (Letter)                                                                                                                   |                 |
| Time to First Page                 | As fast as: Black: 10.9 seconds / Color: 10.9 seconds                                                                                                                                              |                 |
| Print Resolution                   | Black: 4800 Color Quality, 600 x 600 dpi / Color: 600 x 600 dpi, 4800 Color Quality                                                                                                                |                 |
| Memory / Processor                 | Standard: 512 MB / Maximum: 512 MB / Dual Core Processor 1 GHz                                                                                                                                     |                 |
| Hard Disk                          | Not Available                                                                                                                                                                                      |                 |
| Recommended Monthly Page Volume    | 600 - 2500 pages <sup>2</sup>                                                                                                                                                                      |                 |
| Maximum Monthly Duty Cycle         | Up to: 50000 pages per month <sup>3</sup>                                                                                                                                                          |                 |
| Supplies <sup>4</sup>              |                                                                                                                                                                                                    |                 |
| Laser Cartridge Yields             | up to: 2,500 <sup>5</sup> -page Color (CMY) High Yield Cartridges / up to: 3,000 <sup>5</sup> -page Black High Yield Cartridge / up to: 1,500 <sup>5</sup> -page Black and Color (CMYK) Cartridges |                 |
| Cartridge(s) Shipping with Product | 750 <sup>5</sup> -page Black Starter Return Program Toner Cartridge, 500 <sup>5</sup> -page Color (CMY) Starter Return Program Toner Cartridge                                                     |                 |
| Paper Handling                     |                                                                                                                                                                                                    |                 |
| Included Paper Handling            | 100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input                                                                                                                 |                 |
| Paper Input Capacity               | Up to: Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 250+1 pages 20 lb or 75 gsm bond                                                                                                      |                 |
| Paper Output Capacity              | Up to: Standard: 100 pages 20 lb or 75 gsm bond / Maximum: 100 pages 20 lb or 75 gsm bond                                                                                                          |                 |
| Media Types Supported              | Paper Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper, Refer to the Paper & Specialty Media Guide                                                                                         |                 |
| Media Sizes Supported              | A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope                     |                 |
| General Information <sup>6</sup>   |                                                                                                                                                                                                    |                 |
| Standard Ports                     | 802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100/1000 BaseTX (RJ-45)                                                                                       |                 |
| Noise Level                        | Operating: 52 dBA (Print)                                                                                                                                                                          |                 |
| Specified Operating Environment    | Humidity: 8 to 80% Relative Humidity / Altitude: 0 - 3048 Meters (10,000 Feet) / Temperature: 10 to 32°C (50 to 90°F)                                                                              |                 |
| Limited Warranty                   | See Statement of Limited Warranty: 1-Advanced Exchange, 3-5 Business Day Ground Shipment                                                                                                           |                 |
| Size / Weight                      | H x W x D: 9.6 x 16.2 x 15.5 in. / 35.5 lb.                                                                                                                                                        |                 |

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

<sup>1</sup> Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

<sup>2</sup> "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. <sup>3</sup> "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. <sup>4</sup> Product functions only with replacement cartridges designed for use in a specific geographical region. See [www.lexmark.com/regions](http://www.lexmark.com/regions) for more details. <sup>5</sup> Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798. <sup>6</sup> Printers are sold subject to certain license/agreement conditions. See [www.lexmark.com/printerlicense](http://www.lexmark.com/printerlicense) for details.

© 2019 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Google Cloud Print™ is a trademark of Google, LLC. Mopria®, the Mopria® Logo™ and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. All other trademarks are the property of their respective owners. This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).



[lexmark.com](http://lexmark.com)