


HD-TVI 2MP Intensifier® T Indoor Mini-Board Camera with True WDR

HTINT40T 3.6mm fixed lens, black housing



Features

- Sony CMOS Sensor, 2MP
- Full HD 1080p @ 30fps (over coax)
- True WDR functionality
- Superior low-light performance
- Amplify existing light with no distance limitation
- Full OSD operation through onboard control and UTC (TVI)
- With presets for different scenarios
- Additional analog output for 960H
- 12VDC voltage operation
- 5 year warranty

Specifications

Image Sensor	Sony CMOS Sensor, 2MP
Resolution.....	1920 x 1080
Minimum Illumination.....	0.01 lux
Effective Pixels	1985 (H) x 1105 (V)
Total Pixels	2001 (H) x 1121 (V)
TV System.....	NTSC
Scanning System.....	Progressive
S/N Ratio	More than 50dB
Frame rate.....	Max 50P/60P
Video Output	1.0Vp-p / 75 ohms
Lens.....	Manual
Electronic Shutter Speed.....	Auto / Manual (1/60 sec. - 1/60,000 sec.) / Flicker
WDR.....	On (Low / Middle / High) / Off
Digital WDR.....	On (Low / Middle / High) / Off
Day/Night.....	Color / BW / Auto / Ext
White Balance	Auto / Auto Ext / AWC – SET / Manual
Brightness.....	0 - 20 (level adjustable)

AGC.....	0 - 20 (level adjustable)
Sense-Up.....	x2 ~ x32
Motion Tracking	On / Off
Motion Detection.....	On / Off (4 zones)
Privacy.....	On / Off (16 zones)
Mirror / V-Flip.....	On / Off
Sharpness	0 - 20 (level adjustable)
Lens Shading Compensation	On / Off
3DNR.....	Off / Low / Middle / High
Defog.....	On (Auto / Manual) / Off
DIS.....	On / Off
Power Supply	12VDC power supply (power supply not included)
Power Consumption	12VDC, 100mA
Operating Temperature.....	-4° F – 140° F
Dimensions.....	1.34" (W) x 1.34" (H) x 1.18" (Dia.)
Weight	10.56 oz.

Optional Accessories



PSW5
12VDC
Power Supply



TVIUTPPT
HD Video
Transceiver with
Pigtail (Balun)



TVIUPT
HD Video
Transceiver