

XENON EXTREME PERFORMANCE (XP) 1952g

Cordless Area-Imaging Scanner

Delivering excellent customer service is your mission, and providing lasting impressions for your loyal customers driven by fast, accurate, and friendly checkout experiences is critical.

Empower your cashiers to deliver on your mission and commitment to provide excellent customer service experiences with the Honeywell Xenon™ Extreme Performance (XP) series. The Xenon XP 1952g scanner offers superior scan performance, easily capturing even the most difficult-to-read or damaged barcodes.

Engineered to 50 drops at 1.8 m (6 ft) and 2,000 tumbles at 0.5 m (1.6 ft), and with an IP41 ingress rating for water and dust, the Xenon XP 1952g scanner delivers class-leading durability. This significantly reduces scanner downtime and service costs, leading to a longer lifecycle and a lower total cost of ownership.

Freedom of movement around POS terminals, conveyors, and customers is a continued challenge for today's retail associates. As more technology is packed into the streamlined modern-day POS station, free space is at a premium. The Xenon XP 1952g cordless scanner ensures that your associates' attention is kept on maximizing customer experience by eliminating wasted time managing cables.

Designed for stores that need high-accuracy scanning, even from a distance, the Xenon XP 1952g scanner reduces strain on the associate – decreasing the need to bend to reach barcodes on the bottom shelf or bottom of the basket.



The Xenon XP 1952g scanner is purpose-built for retailers who know the costs of long checkout times: lost sales due to abandoned carts, and decreased customer loyalty and revenue over time.

FEATURES AND BENEFITS



Superior scanning performance, even on damaged and poor-quality barcodes, eliminates wasted seconds from every transaction.



Engineered to withstand 2,000 0.5 m (1.6 ft) tumbles and 50 1.8 m (6 ft) drops, the scanner brings class-leading durability and reliability to any environment.



The scanner is optimized for scanning both digital codes off customer smartphones and merchandise codes by the cashier at the register.



Honeywell Operational Intelligence software delivers on-demand scan insights, enabling higher employee productivity and throughput.



The Honeywell Scanner Management Utility (SMU) creates a holistic solution that automates how you deploy and update the scanners in your environment.

Honeywell

Xenon Extreme Performance (XP) 1952g Technical Specifications

WIRELESS

Radio/Range: 2.4 GHz (ISM Band) Adaptive Frequency Hopping Bluetooth v4.2; Class 2: 10 m (33 ft) line of sight

Power Options:

Battery: 2400 mAh Li-ion minimum

Number of Scans: Up to 50,000 scans per charge

Expected Duration of Operation: 14 hours

Expected Charge Time: 4.5 hours

User Indicators: Good Decode LEDs, Rear View LEDs, Beeper (adjustable tone and volume), Vibration (adjustable), Charge Status Indicator

MECHANICAL/ELECTRICAL

Dimensions (L x W x H):

Scanner: 99 mm x 64 mm x 165 mm (3.9 in x 2.5 in x 6.5 in)

Presentation Base: 132 mm x 101 mm x 81 mm (5.2 in x 4.0 in x 3.2 in)

Desktop/Wall Mount Base: 231 mm x 89 mm x 83 mm (9.1 in x 3.5 in x 3.3 in)

Weight:

Scanner: 220 g (7.8 oz)

Presentation Base: 179 g (6.3 oz)

Desktop/Wall Mount Base: 260 g (9.2 oz)

Operating Power (Charging) Bases: 2.5 W (500 mA @ 5V DC)

Non-Charging Power (Bases): 0.75 W (150 mA @ 5V DC)

Host System Interfaces : USB, Keyboard Wedge, RS-232, IBM 46xx (RS485)

ENVIRONMENTAL

Operating Temperature:

Scanner: 0°C to 50°C (32°F to 122°F)

Bases:

Charging: 5°C to 40°C (41°F to 104°F)

Non-Charging: 0°C to 50°C (32°F to 122°F)

Storage Temperature: -40°C to 70°C (-40°F to 158°F)

Electrostatic Discharge (ESD) (Scanners and Cradles): ±8 kV indirect coupling plane, ±15 kV direct air

Humidity: 0 to 95% relative humidity, non-condensing

Tumble Spec: 2,000 0.5 m (1.6 ft) tumbles (impacts)

Drop: Engineered to withstand 50 1.8 m (6 ft) drops to concrete

Environmental Sealing (Scanner): IP41

Light Levels: 0 to 100,000 lux (9,290 foot-candles)

SCAN PERFORMANCE

Scan Pattern: Area Image (1240 x 800 pixel array)

Motion Tolerance: Up to 400 cm/s (157 in/s) for 13 mil UPC at optimal focus

Scan Angle:

HD: Horizontal: 48°; Vertical: 30°

SR: Horizontal: 48°; Vertical: 30°

Print Contrast: 20% minimum reflectance difference

Roll, Pitch, Skew: ±360°, ±45°, ±65°

Decode Capabilities: Reads standard 1D, PDF, 2D, Postal Digimarc, DOT Code, and OCR symbologies

(Note: Decode capabilities dependent on configuration.)

Warranty: Three-year factory warranty (Note: Battery Pack warranty is one year.)

For a complete listing of all compliance approvals and certifications, please visit www.honeywellaidc.com/compliance.

For a complete listing of all supported barcode symbologies, please visit www.honeywellaidc.com/symbologies.

Xenon is a trademark or registered trademark of Honeywell International Inc.

All other trademarks are the property of their respective owners.

DECODE RANGES (DoF)

TYPICAL PERFORMANCE*	STANDARD RANGE (SR)	HIGH DENSITY (HD)
NARROW WIDTH		
3 mil Code 128	56 mm – 132 mm (2.2 in – 5.2 in)	27 mm – 131 mm (1.1 in – 5.1 in)
5 mil Code 39	28 mm – 242 mm (1.1 in – 9.5 in)	14 mm – 219 mm (0.6 in – 8.6 in)
10 mil Code 39	0 mm – 443 mm (0 in – 17.4 in)	0 mm – 389 mm (0 in – 15.3 in)
13 mil UPC	0 mm – 490 mm (0 in – 19.3 in)	0 mm – 368 mm (0 in – 14.5 in)
15 mil Code 128	0 mm – 543 mm (0 in – 21.4 in)	0 mm – 417 mm (0 in – 16.4 in)
20 mil Code 39	4 mm – 822 mm (0.1 in – 32.4 in)	6 mm – 604 mm (0.2 in – 23.8 in)
5 mil PDF417	54 mm – 160 mm (2.1 in – 6.3 in)	30 mm – 155 mm (1.2 in – 6.1 in)
6.7 mil PDF417	34 mm – 220 mm (1.4 in – 8.7 in)	17 mm – 211 mm (0.7 in – 8.3 in)
7.5 mil DM**	49 mm – 172 mm (1.9 in – 6.8 in)	27 mm – 160 mm (1.0 in – 6.3 in)
10 mil DM**	29 mm – 245 mm (1.1 in – 9.7 in)	12 mm – 211 mm (0.5 in – 8.3 in)
20 mil QR	0 mm – 438 mm (0 in – 17.2 in)	0 mm – 331 mm (0 in – 13.0 in)

* Performance may be impacted by barcode quality and environmental conditions.

** Data Matrix (DM)

For more information

www.honeywellaidc.com

Honeywell Safety and Productivity Solutions

9680 Old Baires Road

Fort Mill, SC 29707

800-582-4263

www.honeywell.com

Xenon XP 1952g Data Sheet | Rev A | 05/19
© 2019 Honeywell International Inc.

**THE
FUTURE
IS
WHAT
WE
MAKE IT**

Honeywell