

Phone: 802-874-0123 Fax: 703-991-8770

Email: sales@tsitouch.com


tsitouch.com

## **Philips 55" Infrared Touch Solution**



## **PHILIPS**

## **Signage**Solutions



**Specifications** 

### **Advanced Interactive Collaboration Solution**

The TSItouch overlay is an Infrared (IR) based solution, which allows for a high accuracy interactive experience. The usage of IR technology allows for virtually any input to be detected (pen/stylus, user's fingers, palms, gloved fingers). The TSItouch overlay is a full steel chassis integrated with anti-reflective tempered cover glass, which increases durability and optical clarity, while protecting the display.



# Multi-Touch Screen True multi-touch support with up to six simultaneous touch points for all major operating systems



Easy Integration Unrivaled simplicity makes installation easier and faster



#### Ultra-Fast Response Time Allows for split second reactions between touch point and screen



HID Compliant
Maximum compatibly with
numerous operating
systems, plug-and-play



#### Superior Design

Full steel chassis combined with anti-reflective tempered glass provides additional protection to the LCD panel



Customizable
Custom colors and silk
screening available

Display Compatible	55BDL4050D
Part Number	TSI55NPPXR6CRZZ
Protective Glass	1/8" Anti-Reflective Tempered Glass
Frame Material	Black Powder Coated Cold Rolled Steel
Touch Technology	IR
Touch Points	6 Point
Response Time	6 - 16ms
Touch Accuracy	+/- 2mm (Over 99% Area)
Interface	Type A USB/M
Communication	USB 2.0
Power Supply Mode	USB
Width/Height/Depth Including Monitor	49.95" x 29.35" x 2.53"
Weight (Without Monitor)	TBD
Boxed Weight	TBD
Boxed Dimensions	53.00" x 33.00" x 7.50"
OS Support	Windows, Google Chrome, Android, Mac, Linux