


Phone: 802-874-0123 Fax: 703-991-8770 Email: sales@tsitouch.com tsitouch.com

## **Philips 65" Infrared Touch Solution**



## PHILIPS

## **Signage**Solutions



Specifications

## **Advanced Interactive Collaboration Solution**

The TSItouch overlay is an Infrared (IR) based solution, which allows for a high accuracy interactive experience. The usage of IR technology allows for virtually any input to be detected (pen/stylus, user's fingers, palms, gloved fingers). The TSItouch overlay is a full steel chassis integrated with anti-reflective tempered cover glass, which increases durability and optical clarity, while protecting the display.



Multi-Touch Screen True multi-touch support with up to six simultaneous touch points for all major operating systems





**Ultra-Fast Response Time** Allows for split second reactions between touch point and screen



**Superior Design** Full steel chassis combined with anti-reflective tempered glass provides additional protection to the LCD panel



Maximum compatibly with numerous operating systems, plug-and-play



Customizable Custom colors and silk screening available

Specifications	
Display Compatible	65BDL4050D
Part Number	TSI65NPNTT6CRZZ
Protective Glass	3/16" Anti-Reflective Tempered Glass
Frame Material	Black Powder Coated Cold Rolled Steel
Touch Technology	IR
Touch Points	6 Point
Response Time	6 - 16ms
Touch Accuracy	+/- 2mm (Over 99% Area)
Interface	Type A USB/M
Communication	USB 2.0
Power Supply Mode	USB
Width/Height/Depth Including Monitor	58.46" x 34.09" x 3.21"
Weight (Without Monitor)	TBD
Boxed Weight	TBD
Boxed Dimensions	64.00" x 40.00" x 8.00"
OS Support	Windows, Google Chrome, Android, Mac, Linux