


Samsung 55" Infrared Touch Screen Interface



Samsung Authorized Solution

SAMSUNG



Advanced Interactive Collaboration Solution

The TSItouch interface is an Infrared (IR) based solution, which allows for a high accuracy interactive experience. The usage of IR technology allows for virtually any input to be detected (pen/stylus, user's fingers, palms, gloved fingers). The TSItouch interface is a full steel chassis integrated with anti-reflective tempered cover glass, which increases durability and optical clarity, while protecting the display.



Multi-Touch Screen
 True multi-touch support with up to six simultaneous touch points for all major operating systems



Easy Integration
 Unrivaled simplicity makes installation easier and faster



Ultra-Fast Response Time
 Allows for split second reactions between touch point and screen



HID Compliant
 Maximum compatibility with numerous operating systems, plug-and-play



Superior Design
 Full steel chassis combined with anti-reflective tempered glass provides additional protection to the LCD panel



Customizable
 Custom colors and silk screening available

Specifications

Display Compatible	PM55F, PH55F, PH55F-P
Part Number	TSI55NSNPT6CRZZ
Protective Glass	1/8" Anti-Reflective Tempered Glass
Frame Material	Black Powder Coated Cold Rolled Steel
Touch Technology	IR
Touch Points	6 Point (10 Point Optional)
Response Time	6 - 16ms
Touch Accuracy	+/- 2mm (Over 99% Area)
Interface	Type A USB/M
Communication	USB 2.0
Remote Control Receiver	Extender Not Needed
Receiver Extender	N/A
Power Supply Mode	USB
Width/Height/Depth Including Monitor	49.84" x 29.02" x 1.93"
Weight (Without Monitor)	29.76 lbs
Boxed Weight	36.40 lbs
Boxed Dimensions	53.00" x 33.00" x 7.50"
OS Support	Windows, Google Chrome, Android, Mac, Linux