



SL700U STANDBY UPS SYSTEM

Offers energy savings, battery backup and surge protection.



The CyberPower SL700U uninterruptible power supply (UPS) system provides surge protection for lightning-induced surges and other power events that can damage electronic equipment. This unit delivers enough battery backup to connected devices during a utility power failure, so you can perform a graceful shutdown to protect against the loss of data and damage to valuable electronics including computers, gaming consoles, and home networking equipment.

The SL700U has two Type A USB charging ports with 2.4A shared total output which gives you a faster charging time and can be used while on battery backup power. The slim profile and full-motion power cord allows for discrete installation and keyhole mounting slots allow for wall-mount applications as well.

With a \$100,000 connected equipment guarantee and a three-year warranty, you can trust CyberPower's commitment to the quality of the SL700U.

TYPICAL APPLICATIONS

- Desktop Computers
- Home Networking/VoIP
- Personal Electronics

FEATURES

- 700 VA/370 W
- Standby Topology
- GreenPower UPS™
- ENERGY STAR® Certified
- Full-time Surge Protection and Battery Backup
- Slim Line Form Factor
- 8 Outlets
- EMI/RFI Filters
- Three-Year Warranty

SPECIFICATIONS

GENERAL

UPS Topology	Standby
Energy Saving	GreenPower UPS™ High-Efficiency
ENERGY STAR® Certified	Yes

INPUT

Input Voltage Range	96 - 140V
Input Frequency	50/60 Hz ±3 Hz
Circuit Breaker	15 Amp
Plug Type	NEMA 5-15P
Cord Length (ft)	5

OUTPUT

VA	700
Watts	370
On Battery Voltage	120Vac ± 5%
On Battery Frequency	50Hz/60Hz ± 1% (auto-sensing)
On Battery Waveform	Simulated Sine Wave
Outlets - Total	8
Outlets - Type	NEMA 5-15R
Outlets - Battery & Surge Protected	5
Outlets - Surge-Only Protected	3
Outlets - Widely-Spaced	2

SL700U STANDBY UPS SYSTEM



SPECIFICATIONS CONT.

OUTPUT CONT.

USB Charge Ports	2 x Type A @ 2.4A (Shared)
Overload Protection	Internal Circuitry Limiting/ Circuit Breaker
Transfer Time	Typical 8ms

BATTERY

Runtime at Half Load (min)	9
Runtime at Full Load (min)	2
Battery Type	Sealed Lead-Acid
Battery Size	12V/5.5Ah
Battery Quantity	1
Typical Recharge Time	8 hours

SURGE PROTECTION & FILTERING

Surge Suppression	890
EMI/RFI Filtration	Yes

MANAGEMENT & COMMUNICATIONS

HID Compliant USB Port	Yes
Management Cable	USB cable
LED Indicators	Power On, Wiring Fault

MANAGEMENT & COMMUNICATIONS CONT.

Audible Alarms	On Battery, Low Battery, Overload, Fault
Software	PowerPanel® Personal

PHYSICAL

Color	Black
Form Factor	Slim line
Keyhole Mounting Slots	Yes, 2 x 2-direction slots
Dimensions - WxHxD (in)	12.76 x 5.4 x 2.76

ENVIRONMENTAL

Operating Temperature	32°F to 104°F/0°C to 40°C
Operating Relative Humidity	0%-95% (Non-condensing)

CERTIFICATIONS

Safety	UL1778, cUL, FCC DOC Class B, CEC
Environmental	RoHS Compliant

WARRANTY

Product Warranty	Three-Years Limited
Connected Equipment Guarantee	Lifetime
CEG Amount	\$100,000