

HSM Powerline FA 500.3 1/4" x 1 9/16" - 2 1/16"



Article Number	000000000001990117	Container volume / collecting	140.01 gal
EAN	4026631037334	Cutting speed	41.34 ft/min
Cutting width	0.24 in	Noise level (idle operation)	65 dB(A)
Particle length	1.57 in	Voltage	208 V
Cutting type	Particle cut	Frequency	60 Hz
Security level DIN 66399 (ISO/IEC 21964)	O-2, P-3, T-3, E-2	Width x Height x Depth	45.98 x 70.55 x 70.75 in
Cutting capacity in sheets 80g/m²	340-380	Weight	1741.63 lb
Cutting capacity in sheets 70g/m²	400-450	Colour	anthracite, light grey
Shredder material	Floppy disk, Paper, Computer listings, Crumpled paper, Credit card, Folders, CD/DVD, Staples and paper clips	Security level (DIN 32757)	3
Intake width	19.53 in		