



PREMIER PRO MICROSDXC/SDHC UHS-I U3 CLASS 10

YOUR GO-ANYWHERE MEMORY CARD

Premier Pro microSDXC/SDHC UHS-I Memory Card

Premier Pro microSDXC/SDHC UHS-I memory cards are designed for dash recorders and motion cameras, perfect for repeated write/overwrite tasks such as daily in-car recording. They also meet the A2 standard for quicker and smoother execution of APPs. Being V30 (Video Speed Class) qualified, they can record at a minimum speed of 30MB per second. To ensure consistent high quality, Premier Pro microSDXC/SDHC UHS-I memory cards are waterproof, shockproof, X-ray proof, and extreme temperature resistant, accompanying you on journeys even in harsh environments.

Roam freely with all-round protective design

Premier Pro microSDXC/SDHC UHS-I memory cards support automatic error correcting code (ECC). They also pass rigorous waterproof, shockproof, X-ray proof, anti-static, and extreme temperature testing for rugged durability and reliable protection.



UHS-I U3 meets V30 for faster video recording

- Supports high definition Full HD, 3D, and 4K Ultra HD video recording
- Meet V30 (Video Speed Class) specs: record a minimum 30MB of video per second
- Ideal for dash recorders and motion cameras



A2 qualified - for faster app performance

If you are an Android smartphone/tablet user, A2-qualified Premier Pro microSDXC/SDHC UHS-I memory cards (*64GB-512GB) can help to install and run apps faster. With Android 6.0/7.0, users are able to choose microSD cards as adaptable storage not just for static content such as photos and video, but also for apps. This helps expand smartphone internal storage for more exciting mobile usage.

Features

- Comply with new UHS-I U3 specifications
- A2 qualified – help to install and run APPs faster
- V30 video speed class: can record a minimum 30MB of video per second
- High compatibility across multiple devices: smartphones, tablets, digital cameras, and video recorders
- Support Full HD 1080p and Ultra HD 4K recording and playback
- Rugged durability: waterproof, shockproof, anti-static, X-ray proof, and wide temperature support (-25°C to 85°C)

Specifications

- Capacity: 64GB/128GB/256GB/512GB
- Standard: SD 6.0
- R/W performance:
 - up to 100/80 MB/s (64GB)
 - up to 100/85 MB/s (128GB/256GB/512GB)
- Speed Class: UHS-I Class 10 / V30 / A2
- Dimensions (L x W x H): 15 x 11 x 1mm
- Weight: 0.25g
- Warranty: Lifetime

Large Capacity for Non-Stop Capture

These robust high performance cards are available in 64GB, 128GB, 256GB and 512GB. They can store up to 3830 minutes of Full HD video, providing you with great coverage for extended trips and other recording or photographic capture needs.

Ordering Information

Capacity	Model Number	EAN Code
64GB*	AUSDX64GUI3V30SA2-RA1	4710273771328
128GB*	AUSDX128GUI3V30SA2-RA1	4710273771335
256GB*	AUSDX256GUI3V30SA2-RA1	4710273771342
512GB*	AUSDX512GUI3V30SA2-RA1	4710273771359

*with adapter

