



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Cable length	1.83 m
Colour	White
Depth	5 cm
Height	32.6 cm
Net weight	0.87 kg
Width	4.4 cm

Input

Input power	1800 W
Maximum line current	15 A
Network frequency	50/60 Hz
Plug standard	NEMA 5-15P
Maximum input current	15 A
Switching current capacity	15 A
Input voltage	120 V

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

Product certifications	CULus
------------------------	-------

Standards	UL 498 UL 1310 UL 1449
-----------	------------------------------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Surge Protection and Filtering

Response time	1 ns common mode
Common mode rejection	40 dB
Peak current	48 kA common mode 24 kA normal mode
Surge energy rate	1080 J

Packing Units

Package 1 Weight	0.9 kg
Package 1 Height	36.5 cm
Package 1 width	10.5 cm
Package 1 Length	5.7 cm
SCC14	10731304343704
Number of Units in Package 2	6
Package 2 Weight	5.71 kg
Package 2 Height	381.00 mm
Package 2 width	177.80 mm
Package 2 Length	228.60 mm
Number of Units in Package 3	300

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information