



## Overview

Lead time	Usually in Stock
-----------	------------------

## Physical

Cable length	1.83 m
Colour	Black
Depth	5 cm
Height	32.6 cm
Net weight	0.87 kg
Width	4.4 cm

## Input

Input power	1800 W
Maximum line current	15 A
Network frequency	50/60 Hz
Plug standard	NEMA 5-15P
Maximum input current	15 A
Switching current capacity	15 A
Input voltage	120 V

## Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

## Conformance

Product certifications	CULus
------------------------	-------

Standards	UL 498 UL 1310 UL 1449
-----------	------------------------------

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

## Surge Protection and Filtering

Response time	1 ns common mode
Common mode rejection	40 dB
Peak current	48 kA common mode 24 kA normal mode
Surge energy rate	1080 J

## Packing Units

Package 1 Weight	0.9 kg
Package 1 Height	36.5 cm
Package 1 width	10.5 cm
Package 1 Length	5.7 cm
SCC14	10731304343698
Number of Units in Package 2	6
Package 2 Weight	5.71 kg
Package 2 Height	381.00 mm
Package 2 width	177.80 mm
Package 2 Length	228.60 mm
Number of Units in Package 3	300

## Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>