Cyber Power

PR2200RT2UN SMART APP SINEWAVE UPS

Protect corporate and network servers, telecom installations, and VoIP systems.



The PR2200RT2UN is a Smart App Sinewave rack/tower convertible UPS with line-interactive topology, surge protection, and battery backup. CyberPower's Smart App Sinewave series creates a sine wave output devoid of power gaps which could cause unexpected shutdowns of sensitive equipment.

The Smart App Sinewave PR2200RT2UN improves battery life through battery equalization technology and Automatic Voltage Regulation (AVR), which corrects minor power fluctuations without switching to battery power. The enhanced chassis design with an easy-to-access toolless front panel, captive screws for battery panel access, and color-coded rear panel make battery changes and installations simple and fast. The PR2200RT2UN also has an innovative LCD panel that rotates 90°, tilts for a better viewing angle, and provides information on 47 different settings including UPS stats, UPS setup and control management, and testing options.

This model includes pre-installed RMCARD205 network management card for remote management and control via a standard web browser or network management system.

TYPICAL APPLICATIONS

- Department Servers
- · Storage Devices
- VoIP Installations
- Network Devices
- Corporate Servers
- · Telecom Installations

FEATURES

- 2200VA/2200W
- Line-Interactive Topology
- GreenPower UPS™
- Communication: USB, Serial SNMP, Relay, EPO
- PowerPanel® Business Edition Management Software
- Remote Management
- · Energy Star® Certified
- Three Year Warranty

SPECIFICATIONS

GENERAL	
UPS Topology	Line-Interactive
Energy Saving	GreenPower UPS™ Bypass Technology
ENERGY STAR® Certified	Yes
Active PFC Compatible	Yes
INPUT	
Voltage	100 - 120 VAC
Frequency	47 - 63 Hz
Input Voltage Range	75 - 149 VAC
Plug Type	NEMA L5-30P
Plug Style	Straight, Twist Lock
Cord Length	10 ft.

OUPUT	
2200	
2200	
Double Boost, Single Buck	
100/110/120Vac ± 5%	
50/60 Hz ± 1%	
Sine Wave	
8	
NEMA 5-20R	
4	
8	

PR2200RT2UN SMART APP SINEWAVE UPS



SPECIFICATIONS CONT.

OUTPUT CONT.		
Rated Power Factor	1	
Overload Protection	Internal Circuitry Limiting/ Circuit Breaker	
Transfer Time	4 ms typical	
BATTERY		
Runtime at Half Load (min)	11.8	
Runtime at Full Load (min)	3.2	
Battery Type	Sealed Lead-Acid	
Battery Size	12V / 9AH	
Hot-Swappable	Yes	
Replacement Battery	RB1290X4J	
Battery Quantity	4	
User Replaceable	Yes	
Typical Recharge Time	3 hrs	
External Battery Pack Option	No	
SURGE PROTECTION & FILTERING		
Network Protection RJ45	1 - In, 1 - Out	
Surge Suppression	2,430 Joules	
EMI/RFI Filtration	Yes	
MANAGEMENT & COMMUNICATIONS		
Multifunction LCD Panel	47 Settings (27 Setup and Control Items + 20 Status Updates and Log Menus)	
HID Compliant USB Port	Yes	
Serial Port	Yes	
EPO Port	Yes	
Contact Closure	Yes	
Management Cable	USB Cable, EPO Cable	

MANAGEMENT & COMMUNICATIONS		
LED Indicators	Power On, Line Mode, Battery Mode, Fault, Night Mode, Wiring Fault	
Audible Alarms	Battery Mode, Low Battery, Overload, Overcharge, Overheat	
Software	PowerPanel® Business Edition	
SNMP/HTTP Remote Monitoring	Yes - pre-installed RMCARD205	
PHYSICAL		
Rack Size	2U	
Form Factor	Rack/Tower	
Dimensions (WxHxD) (in.)	17.1 x 3.4 x 16.2	
Weight (lbs.)	59.8	
Shipping Dimensions (WxHxD) (in.)	22.1 x 10.8 x 20.9	
Shipping Weight (lbs.)	67.7	
ENVIRONMENTAL		
Operating Temperature	32°F to 104°F (0°C to 40°C)	
Operating Relative Humidity	0 - 95% (Non-Condensing)	
Storage Temperature	5°F to 113°F (-15°C to 45°C)	
Maximum Operating Elevation	10,000 ft (3,000 m)	
Maximum Storage Elevation	50,000 ft (15,000 m)	
AC Mode Thermal Dissipation	116 BTU/hr	
CERTIFICATIONS		
Safety	UL1778, VCCI, FCC Class A	
Environmental	RoHS Compliant	
WARRANTY		
WARRANTY		
WARRANTY Product Warranty	Three-Years Limited	
	Three-Years Limited Lifetime	