

Lenovo V330-14IKB 81B0016RCF

Product

Lenovo V330-14IKB

Region

NA

Country/Region

Canada

Machine Type

81B0

TopSeller

TopSeller

Processor

Intel Core i5-8250U (4C / 8T, 1.6 / 3.4GHz, 6MB)

Graphics

Integrated Intel UHD Graphics 620

Chipset

Intel SoC Platform

Memory

4GB Soldered DDR4-2400 + 4GB SO-DIMM DDR4-2400

Storage

500GB HDD 7200rpm 2.5" + APS support for HDD

Optane Memory

None

Display

14" HD (1366x768) TN 220nits Anti-glare

Touchscreen

None

Optical

None

Media Reader

4-in-1 Card Reader

Optional Ports

1x USB-C 3.1 Gen 1 (Full Function) + 1x Internal USB 2.0 + 1x USB 3.1 Gen 1 (Always On)

Ethernet

100/1000M

WLAN + Bluetooth

11ac, 2x2 + BT4.2

Case Material

PC / ABS

Camera

720p

Microphone

Mono

Color

Iron Grey

Keyboard

Non-backlit, English / French

Fingerprint Reader

Touch Style

TPM

FW TPM 2.0

Battery

Integrated 30Wh + Ultrabay Battery 39Wh

Power Adapter

45W Slim Tip

Operating System

None

Bundled Software

None

Base Warranty

1-year, Depot

Bundled Service

None

EAN / UPC / JAN

193638298342

End of Support

2025-07-04

Announce Date

2019-06-05

Recommended Services**Best**

3Y Premium Care with Onsite upgrade from 1Y Depot/CCI (5WS0U55751)

Better

3Y Onsite upgrade from 1Y Depot/CCI delivery (5WS0Q81865)

Good

3Y Depot/CCI upgrade from 1Y Depot/CCI delivery (5WS0Q81869)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo V330-14IKB Platform Specifications

Product Specifications Reference (PSREF)

Processor	7th Generation Intel® Core™ i5 Processor or								Dimensions Weight	WxDxH: 13.5" x 9.72" x 0.79"; 343mm x 247mm x 20.3mm				
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics		Models	Max w/o 2nd battery	Max w/ 2nd battery		
	i3-7020U	2	4	2.3 GHz	-	3MB	DDR4-2133	Intel HD Graphics 620		Max Weights				
	i3-7130U			2.7 GHz	-					1.70 kg / 3.75 lb	1.85 kg / 4.07 lb			
	i5-7300U			2.6 GHz	3.5 GHz									
i5-7200U	2.5 GHz			3.1 GHz										
8th Generation Intel Core i3 / i5 / i7 Processor														
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics						
	i3-8130U	2	4	2.2 GHz	3.4 GHz	4MB	DDR4-2400	Intel UHD Graphics 620						
	i5-8250U	4	8	1.6 GHz	3.4 GHz	6MB								
	i7-8550U			1.8 GHz	4.0 GHz	8MB								
Graphics	Intel HD Graphics 620 or UHD Graphics 620 in processor only or, Intel HD Graphics 620 or UHD Graphics 620 in processor and AMD Radeon™ 530, 2GB GDDR5 VRAM; support external digital monitor via HDMI or VGA; supports three independent displays; Max resolution: 3840x2160@30Hz (HDMI); 1920x1200@60Hz (VGA)								Case color	Iron grey, mineral grey				
Chipset	Intel SoC (System on Chip) platform								Case material	PC/ABS plastic				
Memory	20GB max / 2133MHz DDR4 (7th Gen Core model), 20GB max / 2400MHz DDR4 (8th Gen Core model), 4GB memory soldered to systemboard, one DDR4 SO-DIMM socket								Media reader	4-in-1 reader (MMC, SD, SDHC, SDXC)				
Display	Some: 14.0" (356mm) HD (1366x768), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio								Ports	Two USB 3.1 Gen 1 (one with optional Always On), one USB 3.1 Type-C Gen 1, one optional USB 3.1 Type-C Gen 1 (with the function of DP and PowerDelivery), one optional USB 2.0 in Ultra-bay, VGA, HDMI, Ethernet (RJ-45), 4-in-1 reader (MMC, SD, SDHC, SDXC), security keyhole				
Multi-touch	None									* Depending on many factors, actual data transfer speed may be lower than theoretical speed.				
Storage	Up to 2 drives (one HDD and one M.2 SSD): • M.2 SSD / SATA 6.0Gb/s • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2, 16Gb/s • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4, 32Gb/s • HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high, optional Active Protection System (APS)								Camera	One of the following, configurable by model: • 0.3MP with monaural microphone, fixed focus, physical camera shutter • 720p with monaural or dual-array microphone, fixed focus, physical camera shutter				
Optane Memory	Optional: Intel Optane™ Memory, 16GB, M.2								Audio support	HD Audio, stereo speakers with Dolby Audio™, 2W x 2, monaural or dual-array microphone, combo audio/microphone jack				
SATA controller	Serial ATA, SATA 6.0Gb/s support, integrated in processor								Keyboard	6-row, multimedia Fn keys, spill resistant, optional backlit				
UltraBay	One modular bay for interchangeable devices, bottom access								Touchpad	One-piece touchpad, multi-touch				
Ethernet	Gigabit Ethernet connection								Security	Power-on password, hard disk password, supervisor password, security keyhole, optional Active Protection System (APS)				
WLAN+	One of the following, configurable by model:								Security chip	Firmware TPM 2.0, integrated in chipset				
Bluetooth™	• 11ac, 1x1 + BT4.2: 11ac, 1x1, Wi-Fi + Bluetooth combo adapter, M.2 Card								Fingerprint reader	Optional: Touch-type fingerprint reader on the palm rest				
	• 11ac, 2x2 + BT4.2: 11ac, 2x2, Wi-Fi + Bluetooth combo adapter, M.2 Card								Internal battery	Integrated Li-Polymer 2-cell (30Wh or 39Wh)				
									UltraBay battery	Optional: Li-Polymer 2-cell (39Wh)				
									Max battery life (MobileMark® 2014)	Models	2-cell 30Wh	2-cell 39Wh	2-cell 30Wh + 2-cell 39Wh	2-cell 39Wh + 2-cell 39Wh
										Max battery life	6 hr	8 hr	14 hr	16 hr
										* Battery life varies significantly with settings, usage, & other factors.				
									AC adapter	45W or 65W slim tip AC adapter				
									Preload	Some: Windows® 10 Home 64				
										Some: Windows 10 Pro 64				
										• Lenovo Companion				
										• Lenovo Setting				
										• Microsoft Office preloaded;				
										purchase a product key to activate				
										• McAfee® LiveSafe™ (30-day trial)				
									Limited warranty	One of the following, configurable by model:				
										• 1-year mail-in repair service				
										• 1-year depot repair service				
										• 2-year/1-yr battery depot repair service				
									Environment	EPEAT™ Silver; ENERGY STAR® 6.1; RoHS-compliant				

Note: The specifications above may not be available in all regions.

Lenovo
March 2020

Lenovo™

Lenovo V330-14IKB

Lenovo™

