

Key Features

- Wireless screen mirroring and Wi-Fi connection to App store
- Dual integrated Harman Kardon Bluetooth speakers
- Smart Stand for 360 degree projection
- USB Type-C Connectivity
- iF Award winning design



Product Description

The ViewSonic M1+ is an ultra-portable WVGA LED projector that delivers convenient entertainment in any room. With a built-in battery and over 30,000 hours of operational life, this projector will deliver years of multimedia entertainment wherever it goes. Weighing less than 1kg, the M1+'s compact and lightweight design makes it ideal for moving from room to room, or for indoor/outdoor usage. The projector's smart stand provides for simple 360-degree setup, while also doubling as a lens cover. Once the lens is uncovered, the projector automatically powers on with full brightness for instant entertainment. The lens also features a safety auto-off feature that powers down the projector when objects are detected too close to the lens. Dual Harman Kardon Bluetooth speakers provide crisp and clear sound for multimedia content, while a short throw lens can display large images in small spaces. Integrated Wi-Fi connectivity lets you stream from your favourite content providers – making the M1+ a great option for sharing and displaying videos and other multimedia content. The M1+'s versatile connectivity options include a MicroSD card slot, USB Type-A, and USB Type-C connections.



Visit Us www.viewsonic.com

SPECIFICATION		INPUT		OPTIONAL ACCESSORY	
Projection System:	0.2" WVGA	HDMI:	1 (HDMI 1.4/ HDCP 1.4)	Carry Bag:	PJ-CASE-010
Native Resolution:	854x480	SD Card:	Micro SD (32GB, SDHC)		
Brightness (LED Lumens):	300 LED Lumens	USB Type C:	1 (5V/ 2A)		
Contrast Ratio:	120000:1	USB Type A:	1 (USB2.0 Reader, share with power)		
Display Colour:	1.07 Billion Colours	Wifi Input:	1 (5Gn)		
Light Source Type:	LED	Bluetooth Input:	1		
Light Source Life (Normal):	up to 30000	OUTPUT			
Lamp Watt:	RGB LED	Audio out (3.5mm):	1		
Lens:	F= 1.7, f=5.5mm	Speaker:	3W Cube x2		
Projection Offset:	100% +/-5%	USB Type A (Power):	1 (USB2.0 - 5V/ 1A, share with USB reader)		
Throw Ratio:	1.2	OTHERS			
Optical Zoom:	Fixed	Power Supply Voltage:	Power adaptor: Input: 100~240V Output: 19VDC / 3.42A		
Image Size:	24"-100"	Battery:	Battery: 11.1V / 4000mAh		
Throw Distance:	0.64m-2.66m (38" @1m)	Power Consumption:	Normal: 45W Standby: <0.5W		
Keystone:	+/- 40° (V)	Operating Temperature:	0~40°C		
Audible Noise (Normal):	26dB	Net Weight:	0.75kg		
Audible Noise (Eco):	25dB	Dimensions (WxDxH) with Adjustment Foot:	146x126x40mm		
Local Storage:	Total 16GB (12GB available storage)	OSD Language:	English, French, Spanish, Thai, Korean, German, Italian, Russian, Swedish, Dutch, Polish, Czech, T-Chinese, S-Chinese, Japanese, Turkish, Portuguese, Finnish, Indonesian, India, Arabic, Vietnamese, Greek, Total 23 languages		
Input Lag:	33 ms	STANDARD ACCESSORY			
Resolution Support:	VGA(640 x 480) to FullHD(1920 x 1080)	Power Cord:	1		
HDTV Compatibility:	480i, 480p, 576i, 576p, 720p, 1080i, 1080p	Remote Control:	1		
Horizontal Frequency:	15h-135kHz	QSG:	1		
Vertical Scan Rate:	23-120Hz	USB-C Cable:	1 (1m)		