

ThinkVision T25m-10 61DCRAR1US

Product

ThinkVision T25m-10

Machine Type

61DC

Region

NA

Display Size

25"

View Area

535.45x338.76 mm

Panel

In-Plane Switching

Aspect Ratio

16:10

Resolution

1920x1200

Pixel Pitch

0.2789x0.2823 mm

Dot / Pixel Per Inch

91 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

Refresh Rate

60 Hz

Brightness

300 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Multiple Input

HDMI, DP, USB 3.1 Type-C(DP1.2 Alt Mode)

USB Port

4 x USB 3.1 Gen1 (1 BC)

Camera

None

Speaker

3W x 2

Power Consumption (Typical / Maximum)

30W / 150W

Power Adapter

Integrated

Stand

Tilt, Swivel, Height Adjust Stand

Color

Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

399.5x548.7x260.4 mm

Weight (Including Stand)

12.13 lb / 5.5 kg

Monitor Cable

USB Type-C to Type-C

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort

Eye Comfort

Base Warranty

3-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

21/20

On Screen Display

OSD, 8 Languages

Sync Technology

None

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Announce Date

2019-06-26

Notes:

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

 <https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



ThinkVision T25m-10

DISPLAY	CONNECTIVITY	ENERGY STAR (E _{TEC})	Smart Power*	CERTIFICATIONS
Panel Size 25.0 inches	Video Input Signals HDMI 1.4 + DP 1.2 + USB 3.1 Type-C (DP 1.2 Alt Mode)	63.12kWh	Yes	ENERGY STAR Rating 8.0
Screen Dimensions (H x V) 535.45 x 338.76mm	Video Cables Supplied USB 3.1 Type-C	Power Voltage 100-240VAC (50/60Hz)	ThinkCentre Tiny Support Yes	EU RoHS Yes
Panel Type In-Plane Switching	Video Cable Length 1.8m	DIMENSIONS	Optional Soundbar Support Yes	CCC Yes
Backlight WLED	USB Hub Yes	Size Packed (D x H x W) 706 x 450 x 160mm/ 27.79 x 17.72 x 6.30 inches	Internal Speakers Yes (3W x 2)	TCO TCO 8.0/TCO Edge 2.0
Aspect Ratio 16:10	USB Upstream 1 x USB 3.1 Gen1 (by USB Type-C)	Size Unpacked w/stand (D x H x W) (mm/inch) (Lowest position) 260.4 x 399.5 x 548.7mm/ 10.25 x 15.73 x 21.60 inches	MECHANICAL	EPEAT Silver
Resolution 1920 x 1200 pixels	USB Downstream 4 x USB 3.1 Gen1 (with 1 BC)	Size Unpacked w/stand (D x H x W) (mm/inch) (Highest position) 260.4 x 509.5 x 548.7mm/ 10.25 x 20.06 x 21.60 inches	Tilt Angle (front/back) -5°/30°	Windows Certification Windows 7, Windows 10
Pixel Pitch (H x V) 0.2789 x 0.2823mm	Audio Out Yes (3.5mm)	Size Unpacked w/o stand (D x H x W) (mm/inch) (Head Only) 43.0 x 369.1 x 548.7mm/ 1.69 x 14.53 x 21.60 inches	Swivel Angle (left/right) +/-45°	China Energy Efficiency Standard Tier 2
Viewing Angle (H x V) 178°/178°	POWER	Weight Packed 7.8kg/17.20lbs.	Lift Yes (110mm)	TÜV Eye Comfort Yes
Response Time (gray to gray) 4ms (extreme mode) 6ms (normal mode)	Power Consumption (Typical/Max) 30W/150W	Weight Unpacked 5.5kg/12.13lbs.	Pivot +/-90°	
Contrast Ratio (typical) 1000:1	Power Consumption Sleep/Off Mode <0.5W	Weight (Monitor Head Only) 3.58kg/7.89lbs.	VESA Mount Capability Yes (100 x 100mm)	
Dynamic Contrast Ratio (typical) 3M:1	Power Consumption Switch Off-Mode <0.3W	SPECIAL FEATURES	Kensington™ Lock Slot Yes	
Brightness (typical) 300 cd/m ²	Power Supply Internal	Anti-glare Yes	Bezel Width (Side) 2.0mm	
Color Gamut sRGB (CIE 1931) 99%	ENERGY STAR (P_{on}) 17.05W		Bezel Width (top/bottom) 2.0/22.2mm	
Color Support 16.7M			WHAT'S IN THE BOX	
			Monitor with stand 1 x Power Cable 1 x USB Type-C to Type-C cable Quick Setup Guide	

*The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to other devices. 75W power delivery by USB Type-C can be achieved when downstream USB ports are not connected and OSD brightness setting is <31.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.



ThinkVision T25m-10

Lenovo™

