

32UL750

32" Class 4K UHD LED Monitor with VESA Display HDR 600
(31.5" Diagonal)

EAN CODE: 8806098487493

32"

KEY FEATURES

- 32" 4K (3840 x 2160) Display
- VESA Display HDR 600
- DCI-P3 95%
- USB Type-C with PD (~60W)
- Radeon FreeSync™ Technology
- On Screen Control / Screen Split



For more information
www.lg.com/uk/monitors

PRODUCT FEATURES

DISPLAY

Size (Inch)	31.5 Inch
Size (cm)	80.1 cm
Resolution	3840 x 2160
Panel Type	VA
Aspect Ratio	16:9
Pixel Pitch	0.181x 0.181 mm
Brightness (Min.)	350 cd/m ²
Brightness (Typ.)	400 cd/m ²
Color Gamut (Min.)	DCI-P3 90% (CIE1976)
Color Gamut (Typ.)	DCI-P3 95% (CIE1976)
Color Depth (Number of Colors)	1.07B
Contrast Ratio (Min.)	2000:1
Contrast Ratio (Typ.)	3000:1
Response Time	4ms (GtG at Faster)
Viewing Angle (CR≥10)	178°(R/L), 178°(U/D)
Surface Treatment	Anti-Glare 3H
Curved	NO

SOUND

Speaker	YES
Speaker_Output (unit)	5W
Speaker_Channel	2ch
Bluetooth Connectivity	NO
Maxx Audio	NO
Rich Bass	NO

POWER

Type	External Power(Adapter)
AC Input	100~240V (50/60Hz)
Power Consumption (Typ.)	70W
Power Consumption (Max.)	180W
Power Consumption (Energy Star)	39.8W
Power Consumption (Sleep Mode)	Less than 0.5W(HDMI,DP)
Power Consumption (DC Off)	Less than 0.3W

CONNECTIVITY

D-Sub	NO
D-Sub (Max. Resolution at Hz)	N/A
DVI	NO
DVI (Max Resolution at Hz)	N/A
HDMI	YES(2ea)
HDMI (Max. Resolution at Hz)	3840x2160@60Hz
DisplayPort	YES(1ea)
DP Version	1.4
DP (Max. Resolution at Hz)	3840x2160@60Hz
Mini DisplayPort	NO
mDP Version	N/A
mDP (Max. Resolution at Hz)	N/A
Thunderbolt	NO
Thunderbolt(USB-C Compatiblity)	NO
Thunderbolt (Max. Resolution at Hz)	N/A
Thunderbolt (Data Trassmission)	NO
Thunderbolt (Power Delivery)	N/A
USB-C	YES(1ea)
USB-C (Max. Resolution at Hz)	3840x2160@60Hz
USB-C (DP Alternate Mode)	YES
USB-C (Data Trassmission)	YES
USB-C (Power Delivery)	60W
Daisy Chain	NO
USB Upstream Port	NO
USB Downstream Port	YES(2ea/ver3.0)
Audio In	NO
Mic In	NO
Headphone out	YES
Line out	NO

32UL750

32" Class 4K UHD LED Monitor with VESA Display HDR 600
(31.5" Diagonal)

EAN CODE: 8806098487493

32"

KEY FEATURES

- 32" 4K (3840 x 2160) Display
- VESA Display HDR 600
- DCI-P3 95%
- USB Type-C with PD (~60W)
- Radeon FreeSync™ Technology
- On Screen Control / Screen Split



For more information
www.lg.com/uk/monitors

PRODUCT FEATURES

FEATURES

HDR 10	YES
VESA DisplayHDR™	DisplayHDR™ 600
HDR Effect	YES
Nano IPS™ Technology	NO
Wide Color Gamut	YES
Color Calibrated	YES
HW Calibration	NO
Auto Brightness	NO
Flicker safe	NO
Reader Mode	YES
Color Weakness	YES
Super Resolution+	YES
1ms Motion Blur Reduction	NO
NVIDIA G-Sync™	NO
RADEON FreeSync™	YES
FreeSync (Low Frame Compensation)	NO
Black Stabilizer	YES
Dynamic Action Sync	YES
Crosshair	NO
Sphere Lighting	NO
PBP	NO
PIP	NO
Smart Energy Saving	YES
Camera	NO
Mic	NO
Others (Feature)	

DIMENSIONS/WEIGHT

Dimension with Stand (W x H x D)	728.1 x 601.7 x 230 mm (Up) 728.1 x 491.7 x 230 mm (Down)
Dimension without Stand (W x H x D)	728.1 x 424.6 x 49.9 mm
Dimension in Shipping (W x H x D)	825 x 507 x 226 mm
Weight with Stand	7.3 kg
Weight without Stand	5.6 kg
Weight in Shipping	11.1 kg

MECHANICAL

Display Position Adjustments	Tilt/Height
Wall Mountable	100 x 100 mm

SW APPLICATION

True Color Pro	NO
Dual Controller	YES
OnScreen Control (LG Screen Manager)	YES

ACCESSORY

D-Sub	NO
DVI-D	NO
HDMI	YES
Display Port	YES
mDP to DP	NO
Thunderbolt	NO
USB Type C	YES
USB Type C to A Gender	NO
USB A to B	NO
USB3.0 Upstream Cable	NO
PC Audio	NO
Remote Controller	NO
Others (Accessory)	