

EPA6220 Speed Dome Camera


AHD 1080p IR / IP66 Outdoor Speed Dome
20x Optical Zoom, True Day / Night, WDR



Features

- AHD 1080p Sony CMOS sensor
- 20x optical zoom lens
- Supports UTC & RS-485 communication
- True day/Night (IR-cut filter removable)
- Supports D-WDR
- Supports 220 preset positions
- Supports 8 tours (16 positions each tour)
- IP66-rated with metal housing
- Supports OSD menu

Dimensions



*All images presented in this document are for example only. Product models may vary in different countries. Please visit EverFocus regional Websites for detailed ordering information.

*Information contained in this document is subject to change without notice.

Specification

Model No.	EPA6220		
Pickup Device	1/2.7" Sony CMOS sensor	Auto Flip	Horizontal 180°, Vertical 93°
Output Pixels	1920 x 1080	Preset Points	220 preset points (dwell time 01-60s)
Lens	20x optical zoom, 4.7~94mm	A-B Scan	User programmable (scan speed 1-64)
Video Format	AHD / TVI / CVI / CVBS switchable	Tour	8 tours (max.16 preset points each tour)
System Format	NTSC / PAL switchable	PWR on Action	Action (Memory), Off, AB Scan, 360, Home, Tour1, Pattern1
Min. Illumination	Color: 0.01Lux ; B/W: 0.001Lux	Park Mode	Off, AB Scan, 360, Home, Tour1, Pattern1 (park time 1-60m)
S/N Ratio	≥50dB	Pattern Scan	4 patterns (max.15 minutes, max.512 commands)
Zoom Ratio	Max. 20x (optical)	Time Scheduling	6 tasks (AB Scan, 360 Pan, Tour 1-4, Pattern 1-4)
True Day / Night	Supported	Rotation Range	Pan: 0° ~ 360°, Tilt: 0° ~ 93°
BLC	On / Off	Rotation Speed	Pan: 0~480°/s, Tilt:0~240°/s
WDR	D-WDR (auto)	Communication	RS-485, Coaxial
AGC	Auto	Communication Speed	1200 / 2400 / 4800 / 9600bps
WB	Auto	Built-in Protocols	Pelco-P / Pelco-D
Motion Detection	Not supported	Address Editable	Supported (OSD switch)
Defog	Not supported	ID Address	0 ~ 255
Privacy Mask	Not supported	Power Source	12VDC, 4A / 24VAC~, 3A
Alarm	Not supported	Power Consumption	≤ 25W
Focus Control	Auto / Manual	Weather Resistance	IP66
OSD Menu	Supported	Operating Temperature	-40°C ~ 60°C ≤ 95% / -40°F ~ 140°F ≤ 95%
Video Output	1Vp-p, 75Ω	Package Size (W x D x H)	310 x 310 x 440mm / 12.2" x 12.2" x 17.32"
IR LED	8 units	Weight	12VDC: 6.1kg / 13.45lb 24VAC~: 7.15kg / 15.76lb
IR Range	150m / 492ft.	Certificates	CE, FCC

Find Out More At:

EverFocus Taiwan HQ:
TEL: +886 2 2662 2338
www.everfocus.com.tw
marketing@everfocus.com.tw

EverFocus USA - California:
TEL: +1 626 844 8888
www.everfocus.com
sales@everfocus.com

International Branch Offices:
China, Japan

