

## 10 ft. (3 m) USB KVM Cable for StarTech.com Rackmount Consoles

Product ID: RKCONSUV10



This 10 ft. (3 m) USB KVM Cable enables your StarTech.com Rackmount LCD console and KVM switch kit to conveniently operate your VGA and USB-equipped server.

This line of KVM cables are available in variable lengths, and are the only cables engineered for guaranteed compatibility with the StarTech.com line of RKCONS series of Rackmount Consoles and KVM switches. Supported models of Rackmount LCD Consoles are: [RKCONS1701](#), [RKCONS17HD](#), [RKCONS1708K](#), [RKCONS1716K](#), [RKCONS1901](#), [RKCONS1908K](#), [RKCONS1916K](#).

### Engineered to Keep Your Server Room Tidy

This KVM cable has been specifically designed for the StarTech.com line of Rackmount KVM and Console kit. The USB and VGA KVM cord is wired with a unique schematic that enables a single connector on the KVM to interface with both VGA and USB on your server. This space-saving design dramatically reduces cable-clutter in your server rack, and ensures a tidy, professional server room.

## Crystal-Clear Picture Quality

When connected to an HD rackmount console, the 10 foot KVM cable supports HD resolutions up to 1920x1200 including 1080p, maintaining the quality of your server's video card to deliver every detail in high-definition.

## Available in Different Lengths

To support the complexities and demands of your data center, this 10 foot (3 meter) KVM cable is also available as a [6 foot \(1.8 meter KVM Cable \(RKCONSUV6\)\)](#), and a [15 foot \(4.8 meter\) KVM cable \(RKCONSUV15\)](#).

The RKCONSUV10 is backed by a StarTech.com Lifetime warranty and free technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect servers to your StarTech.com Rackmount KVM console
- Keep replacement cables on hand to ensure continuous control of your mission critical servers

### Features

- Maintain your clutter-free server room with a VGA and USB KVM cable that combines into a single connector on the KVM side
- Get crystal-clear picture quality with support for HD resolutions up to 1920x1200 or 1080p
- Accommodate variable rack configurations, with cables available in different lengths

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Connector(s)</b>	Connector A	1 - VGA (14 pin, High Density D-Sub) Male
	Connector B	1 - USB Type-A (4 pin) USB 2.0 Male
		1 - VGA (15 pin, High Density D-Sub) Male
<b>Physical Characteristics</b>	Product Height	0.6 in [1.5 cm]
	Product Length	10 ft [3 m]
	Product Width	1.2 in [3 cm]
	Weight of Product	8.1 oz [230 g]
<b>Packaging Information</b>	Package Height	7.9 in [200 mm]
	Package Length	8.7 in [22 cm]
	Package Width	0.4 in [1 cm]
	Shipping (Package) Weight	8.3 oz [235 g]
<b>What's in the Box</b>	Included in Package	1 - KVM Cable

Product appearance and specifications are subject to change without notice.