

ThinkPad P73 20QR0026GE

Product

ThinkPad P73

Region

WE

Country/Region

Germany

Machine Type

20QR

TopSeller

TopSeller

Processor

Core i7-9750H (6C / 12T, 2.6 / 4.5GHz, 12MB)

Graphics

NVIDIA Quadro T2000 4GB GDDR5

Chipset

Intel CM246

Memory

2x 8GB DIMM DDR4-2666 non-ECC

Display

17.3" FHD (1920x1080) IPS 300nits Anti-glare

Multi-touch

None

Storage

512GB SSD M.2 2280 PCIe NVMe Opal2

Optane Memory

None

RAID

No

Optical

None

WLAN + Bluetooth

Intel AX200 11ax, 2x2 + BT5.0

WWAN

None

SIM Card

None

Smart Card Reader

Smart Card Reader

Monitor Cable

None

Bundled Accessories

None

Color

Black

Camera

720p + IR

Keyboard

Backlit

Pen

None

Fingerprint Reader

Fingerprint Reader

NFC

None

Color Calibrator

None

TPM

Discrete TPM 2.0

Battery

Integrated 99Wh

Power Adapter

170W Slim Tip

System Management

None

Operating System

Windows 10 Pro 64

Bundled Software

None

Base Warranty

3-year, Depot

Upsell Service Bundles

3Y Onsite upgrade from 3Y Depot/CCI (5WS0V07088)

End of Support

2025-09-13

Announce Date

2019-08-13

Recommended Services**Best**

5Y Premier Support Upgrade from 3Y Depot/CCI (5WS0V07061)

Better

4Y Premier Support Upgrade from 3Y Depot/CCI (5WS0V07067)

Good

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0V07092)

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2019. All rights reserved.



Lenovo™

ThinkPad P73 Platform Specifications

Product Specifications Reference (PSREF)



Processor	9th Generation Intel® Core™ i5 / i7 / i9 Processor or Intel Xeon® E Processor									Dimensions WxDxH: 16.38" x 11.06" x 1.02-1.22"; 416mm x 281mm x 25.9-31mm Weight Starting at 7.5 lb (3.4kg) Case color Black Case material Display cover: GFRP + PPS; Bottom: Magnesium/Aluminum
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics		
	i5-9400H	4	8	2.5 GHz	4.3 GHz	8MB	DDR4-2666	Intel UHD Graphics 630		
	i7-9750H	6	12	2.6 GHz	4.5 GHz	12MB		Intel UHD Graphics 630		
	i7-9850H	6	12	2.6 GHz	4.6 GHz	12MB		Intel UHD Graphics 630		
i9-9880H	8	16	2.3 GHz	4.8 GHz	16MB	Intel UHD Graphics 630				
E-2276M	6	12	2.8 GHz	4.7 GHz	12MB	Intel UHD Graphics P630				
Graphics	Intel UHD Graphics 630 or P630 in processor and NVIDIA Quadro® P620 (4GB GDDR5), T2000 (4GB GDDR5), RTX 3000 (6GB GDDR6, VR ready), RTX 4000 Max-Q (8GB GDDR6, VR ready), or RTX 5000 Max-Q (16GB GDDR6, VR ready); supports external digital monitor via HDMI or Thunderbolt™; supports five independent displays; Max resolution: 5K@60Hz (Thunderbolt); 4K@60Hz (USB-C or HDMI)									Smart card reader Optional: Smart card reader ExpressCard None Media reader 4-in-1 reader (MMC, SD, SDHC, SDXC), supports UHS-II SD card Ports Three USB 3.1 Gen 1 (one Always On), one USB 3.1 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), two USB 3.1 Type-C Gen 2 / Thunderbolt 3 (with the function of PD and DP), HDMI 2.0, Ethernet (RJ-45), headphone / microphone combo jack, optional smart card reader, 4-in-1 reader (MMC, SD, SDHC, SDXC), security keyhole * Power Delivery only supports power-out for charging peripherals * Depending on many factors, actual data transfer speed may be lower than theoretical speed Monitor cable (optional) HDMI to VGA: Lenovo HDMI to VGA Monitor Adapter USB-C to VGA: Lenovo USB-C to VGA Adapter USB-C to DP: Lenovo USB-C to DisplayPort Adapter None Camera (optional) One of the following, configurable by model: • HD720p camera with ThinkShutter camera privacy, fixed focus • IR camera and HD720p camera with ThinkShutter camera privacy, fixed focus Audio support HD Audio, Synaptic® CX11880 codec / stereo speakers, 2W x 2 / dual array far-field microphone, headphone / microphone combo jack, Dolby Atmos® sound system Keyboard 6-row, spill-resistant, multimedia Fn keys, numeric keypad, LED backlight UltraNav™ 3-button TrackPoint® pointing device and 3-button Mylar surface multi-touch touchpad Security Power-on password, hard disk password, supervisor password, security keyhole Security chip Discrete TPM 2.0, TCG Certified vPro (optional) Intel vPro Technology Fingerprint reader Touch style match on chip fingerprint reader on the palm rest Color calibration Optional: X-Rite Pantone factory color calibration (UHD model only) NFC (optional) Near Field Communication Battery Integrated Li-ion 99Wh battery, supports Rapid Charge (charge up to 80% in 1hr) Max battery life Discrete mode: 7 hr; Hybrid mode: 10 hr (MobileMark® 2014) * Battery life varies significantly with settings, usage, & other factors AC adapter 170W or 230W slim tip AC adapter Operating system One of the following, configurable by model: • Windows® 10 Home 64 • Windows 10 Pro 64 • Windows 10 Pro 64 for Workstations Limited warranty One of the following, configurable by model: • 1-year depot repair service • 3-year/1-yr battery depot repair service • 3-year/1-yr battery limited onsite service Mil-Spec test MIL-STD-810G military testing Environment EPEAT™ Silver; ENERGY STAR® 7.1; RoHS-compliant
Chipset	Mobile Intel CM246 Chipset									
Memory	128GB max / 2666MHz DDR4 (ECC function supported only on Xeon processor), dual-channel capable, four DDR4 SO-DIMM sockets * Installed DIMMs are actually 2666MHz but run at 2400MHz due to Intel limitation									
Display	Size	Resolution	Type	Surface	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	
	17.3"	FHD (1920x1080)	IPS	Anti-glare	300 nits	16:9	700:1	72%	160°	
Multi-touch	None									
	Pen	None								
Storage	Up to 3 drives (two M.2 SSD and one HDD) • HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high, Active Protection System™ • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4									
Optane™ memory	Optional: Intel Optane memory, PCIe NVMe, PCIe 3.0 x 4									
RAID (optional)	RAID 0/1 support									
Optical	None									
Ethernet	Non-vPro model: Intel Ethernet Connection I219-V (Jacksonville) vPro model: Intel Ethernet Connection I219-LM (Jacksonville)									
WLAN	Intel Wi-Fi 6 AX200, Wi-Fi 2x2 802.11ax + Bluetooth 5.0									
Bluetooth™	Bluetooth 5.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter									
WWAN	None									
SIM card	None									

Note: The specifications above may not be available in all regions.

Lenovo
August 2019

ThinkPad P73

